



EC7AW SERIES 10 WATT 4:1 INPUT ISOLATED DC-DC CONVERTER

Features

- Efficiency up to 89%
- Fixed Switching Frequency
- Regulated Outputs
- Remote On/Off
- Low No Load Power Consumption
- Fully Protected (OCP/OVP/UVLO)
- 3000Vdc I/O Isolation
- No Tantalum Capacitor Inside
- DIP-24 Metal Package
- Meets Industrial Standard 1.25"x0.80"x0.40"
- Safety Meets IEC/EN/UL 62368-1
- EMI Meets EN55032 Class A
Without External Component



MODEL NUMBER	INPUT VOLTAGE	OUTPUT VOLTAGE	OUTPUT CURRENT		INPUT CURRENT		% EFF.		CAPACITOR LOAD MAX.
			MIN.	MAX.	NO LOAD	FULL LOAD	(1)	(2)	
EC7AW-24S33	9-36 VDC	3.3 VDC	0 mA	2000 mA	6 mA	340 mA	81	81.5	2000uF
EC7AW-24S05	9-36 VDC	5 VDC	0 mA	2000 mA	6 mA	487 mA	85.5	86	2000uF
EC7AW-24S12	9-36 VDC	12 VDC	0 mA	833 mA	6 mA	471 mA	88.5	89	833uF
EC7AW-24S15	9-36 VDC	15 VDC	0 mA	666 mA	7 mA	468 mA	89	89.5	666uF
EC7AW-24D12	9-36 VDC	±12 VDC	0 mA	±417 mA	8 mA	474 mA	88	88.5	417uF
EC7AW-24D15	9-36 VDC	±15 VDC	0 mA	±333 mA	10 mA	473 mA	88	89	333uF
EC7AW-48S33	18-74 VDC	3.3 VDC	0 mA	2000 mA	6 mA	171 mA	80.5	81.5	2000uF
EC7AW-48S05	18-74 VDC	5 VDC	0 mA	2000 mA	6 mA	244 mA	85.5	86	2000uF
EC7AW-48S12	18-74 VDC	12 VDC	0 mA	833 mA	6 mA	235 mA	88.5	90	833uF
EC7AW-48S15	18-74 VDC	15 VDC	0 mA	666 mA	6 mA	234 mA	89	89.5	666uF
EC7AW-48D12	18-74 VDC	±12 VDC	0 mA	±417 mA	6 mA	237 mA	88	89.5	417uF
EC7AW-48D15	18-74 VDC	±15 VDC	0 mA	±333 mA	7 mA	237 mA	88	89.5	333uF

NOTE:

1. Nominal Input Voltage 24 or 48 VDC
2. Measured at 12VDC for 24Vin, 24VDC for 48Vin

PART NUMBER

Series	Nominal Input Voltage	Number of Outputs	Nominal Output Voltage	Remote On/Off Logic
EC7AW-	II	O	XX	L
EC7AW	24: 24VDC	S: Single D: Dual	33: 3.3VDC	None: Positive N: Negative
			05: 5.0VDC	
	48: 48VDC		12: 12VDC	
			15: 15VDC	

Part Number Example:

EC7AW-24S12N: 1.25"x0.8", 10W, 4:1 9-36Vdc Input, Single 12Vdc Output, Negative Logic



EC7AW Series

TECHNICAL SPECIFICATIONS

(All specifications are typical at nominal input, full load at 25°C unless otherwise noted.)

ABSOLUTE MAXIMUM RATINGS

PARAMETER	NOTES and CONDITIONS	Device	Min.	Typ.	Max.	Units
Input Voltage	Continuous	24Vin 48Vin	-0.3 -0.3		36 74	V _{dc}
Input Surge Voltage	100ms max.	24Vin 48Vin			50 100	V _{dc}
Operating Case Temperature	At the Center Part of Case Plate	All	-40		105	°C
Storage Temperature		All	-55		125	°C

INPUT CHARACTERISTICS

PARAMETER	NOTES and CONDITIONS	Device	Min.	Typ.	Max.	Units
Operating Input Voltage		24Vin 48Vin	9 18	24 48	36 74	V _{dc}
Input Under Voltage Lockout						
Turn-On Voltage Threshold	100% Load	24Vin 48Vin	8 16.5	8.5 17	8.8 17.5	V _{dc}
Turn-Off Voltage Threshold	100% Load	24Vin 48Vin	7.5 15.5	8 16	8.3 16.5	V _{dc}
Lockout Hysteresis Voltage	100% Load	24Vin 48Vin		0.5 1		V _{dc}
Maximum Input Current	V _{in} =9V, Full Load V _{in} =18V, Full Load	24Vin 48Vin		1.4 0.7		A
No-Load Input Current	V _{in} =Nominal, I _o =0A	See Model Number Table				mA
Input Filter	Pi filter	All				
Inrush Current (I ² t)	As per ETS300 132-2	All			0.1	A ² s
Input Reflected Ripple Current	P-P thru 12uH inductor, 5Hz to 20MHz	All		30		mA

OUTPUT CHARACTERISTICS

PARAMETER	NOTES and CONDITIONS	Device	Min.	Typ.	Max.	Units
Voltage Set Point Accuracy	V _{in} =Nominal, Full Load, T _c =25°C	All	-1.0		+1.0	%
Output Voltage Balance	V _{in} =Nominal, Full Load, T _c =25°C	Dual	-1.0		+1.0	%
Output Voltage Regulation						
Load Regulation	Full Load to No Load	All			±1.0	%
Line Regulation	V _{in} =High Line to Low Line, Full Load	All			±0.2	%
Temperature Coefficient	T _c = -40°C to 85°C	All			±0.02	%/°C
Output Voltage Ripple and Noise (5Hz to 20MHz bandwidth)						
Peak-to-Peak	Full load, 1.0uF ceramic capacitors	3.3Vo 5Vo 12Vo 15Vo			100 100 120 150	mV
Output Current Range	V _{in} =Nominal,	See Model Number Table				A
Over Current Protection	Hiccup Mode. Auto Recovery	All	110	140	170	%
Short Circuit Protection		All	Continuous, Auto Recovery			
External Load Capacitance	Full load (resistive)	See Model Number Table				uF
Over Voltage Protection	Zener Clamp	3.3Vo 5Vo 12Vo 15Vo ±12Vo ±15Vo		3.9 6.2 15 18 ±15 ±18		V _{dc}



EC7AW Series

EFFICIENCY

PARAMETER	NOTES and CONDITIONS	Device	Min.	Typ.	Max.	Units
100% Load	V_{in} =Nominal, Full Load, $T_c=25^{\circ}\text{C}$	See Model Number Table				%

DYNAMIC CHARACTERISTICS

PARAMETER	NOTES and CONDITIONS	Device	Min.	Typ.	Max.	Units
Output Voltage Current Transient						
Error Band	75% to 100% of I_{o_max} step load change $dI/dt=0.1\text{A}/\mu\text{s}$ (within 1% V_{out} nominal)	All			± 5	%
Recovery Time		All			250	μs
Turn-On Delay and Rise Time	Full load (Constant resistive load)					
Turn-On Delay Time, From On/Off Control	$V_{on/off}$ to 10% V_{o_set} , Remote On	All		5		ms
Turn-On Delay Time, From Input	V_{in_min} to 10% V_{o_set} , Power Up	All		5		ms
Output Voltage Rise Time	10% V_{o_set} to 90% V_{o_set}	5Vo		10		ms
		Others		5		

ISOLATION CHARACTERISTICS

PARAMETER	NOTES and CONDITIONS	Device	Min.	Typ.	Max.	Units
Isolation Voltage (100% factory Hi-Pot tested @2sec.)	1 minute; Input to Output,	All			2000 3000	V_{ac} V_{dc}
Isolation Resistance	Input to Output	All	1000			M Ω
Isolation Capacitance	Input to Output (10KHz, 0.25V)	All		1000		pF

FEATURE CHARACTERISTICS

PARAMETER	NOTES and CONDITIONS	Device	Min.	Typ.	Max.	Units
Switching Frequency	Output Ripple Frequency	All	477	530	583	KHz
On/Off Control, Positive Remote On/Off logic, Refer to $-V_{in}$ pin.						
Logic Low (Module Off)	$V_{on/off}$ at $I_{on/off}=1.0\text{mA}$	All	0		1.2	V
Logic High (Module On)	$V_{on/off}$ at $I_{on/off}=0.0\mu\text{A}$, Pin open=On	All	3.5 or Open Circuit		74	V
On/Off Control, Negative Remote On/Off logic, Refer to $-V_{in}$ pin						
Logic High (Module Off)	$V_{on/off}$ at $I_{on/off}=0.0\mu\text{A}$, Pin open=Off	All	3.5 or Open Circuit		74	V
Logic Low (Module On)	$V_{on/off}$ at $I_{on/off}=1.0\text{mA}$	All	0		1.2	V
On/Off Current (for both remote on/off logic)	$I_{on/off}$ at $V_{on/off}=0\text{V}$	All		0.4	1	mA
Leakage Current (for both remote on/off logic)	Logic High, $V_{on/off}=15\text{V}$	All			30	μA
Off Converter Input Current	Shutdown input idle current	All		3	5	mA

GENERAL SPECIFICATIONS

PARAMETER	NOTES and CONDITIONS	Device	Min.	Typ.	Max.	Units
MTBF	$I_o=100\%$ of I_{o_max} ; MIL-HDBK - 217F_Notice 1, GB, 25°C	24S33		1727		K hours
		24S05		1520		
		24S12		1634		
		24S15		1711		
		24D12		1466		
		24D15		1579		




EC7AW Series



PARAMETER	NOTES and CONDITIONS	Device	Min.	Typ.	Max.	Units
MTBF	$I_o=100\%$ of $I_{o,max}$; MIL-HDBK - 217F_Note 1, GB, 25°C	48S33 48S05 48S12 48S15 48D12 48D15		1725 1605 1583 1715 1453 1585		K hours
Weight		All		18.4		grams
Case Material	Black Coated Copper					
Base plate Material	Non-Conductive Base					
Potting Material	UL 94V-0					
Pin Material	Base: Copper with Steel Plating: Barrel Tin					
Shock/Vibration	MIL-STD-810F Compliant					
Humidity	95% RH max. Non Condensing					
Altitude	2000m Operating Altitude					
Thermal Shock	MIL-STD-810F					
Application Note Link			EC7AW Series App Notes			
Packaging Information Link			Packaging Information			

CHARACTERISTIC CURVE

Power Derating Curve




Performance Data






EC7AW Series


EC7AW-24S05
Eff Vs Io @25 Deg. C




EC7AW-24S05
Pd Vs Po @25 Deg. C




EC7AW-24S12
Eff Vs Io @25 Deg. C




EC7AW-24S12
Pd Vs Po @25 Deg. C




EC7AW-24S15
Eff Vs Io @25 Deg. C




EC7AW-24S15
Pd Vs Po @25 Deg. C



EC7AW-24D12
Eff Vs Io @25 Deg. C




EC7AW-24D12
Pd Vs Po @25 Deg. C






EC7AW Series


EC7AW-24D15
Eff Vs Io @25 Deg. C




EC7AW-24D15
Pd Vs Po @25 Deg. C




EC7AW-48S33
Eff Vs Io @25 Deg. C




EC7AW-48S33
Pd Vs Po @25 Deg. C




EC7AW-48S05
Eff Vs Io @25 Deg. C




EC7AW-48S05
Pd Vs Po @25 Deg. C



EC7AW-48S12
Eff Vs Io @25 Deg. C




EC7AW-48S12
Pd Vs Po @25 Deg. C






EC7AW Series


EC7AW-48S15
Eff Vs Io @25 Deg. C




EC7AW-48S15
Pd Vs Po @25 Deg. C




EC7AW-48D12
Eff Vs Io @25 Deg. C




EC7AW-48D12
Pd Vs Po @25 Deg. C



EC7AW-48D15
Eff Vs Io @25 Deg. C




EC7AW-48D15
Pd Vs Po @25 Deg. C





EC7AW Series

MECHANICAL SPECIFICATION



NOTE: Pin Size is 0.02±0.002 Inch (0.5±0.05 mm) DIA
All Dimensions In Inches (mm)
Tolerances Inches: X.XX= ±0.02 , X.XXX= ±0.010
Millimeters: X.X= ±0.5 , X.XX=±0.25

PIN CONNECTION		
Pin	Single Output	Dual Output
1	Remote on/off	Remote on/off
2,3	-V Input	-V Input
9	NP	Common
11	NC	-V Output
14	+V Output	+V Output
16	-V Output	Common
22,23	+V Input	+V Input

* NC-NO CONNECTION WITH PIN
* NP-NO PIN

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Cincon:

[EC7AW-24D12](#) [EC7AW-24D12N](#) [EC7AW-24D15](#) [EC7AW-24D15N](#) [EC7AW-24S05](#) [EC7AW-24S05N](#) [EC7AW-48S12](#) [EC7AW-48S12N](#) [EC7AW-48S15](#) [EC7AW-48S15N](#) [EC7AW-48S33](#) [EC7AW-48S33N](#) [EC7AW-48D12](#) [EC7AW-48D12N](#) [EC7AW-48D15](#) [EC7AW-48D15N](#) [EC7AW-48S05](#) [EC7AW-48S05N](#) [EC7AW-24S12](#) [EC7AW-24S12N](#) [EC7AW-24S15](#) [EC7AW-24S15N](#) [EC7AW-24S33](#) [EC7AW-24S33N](#)