



CQB150W14 SERIES 150 WATT 14:1 INPUT ISOLATED DC-DC CONVERTER

Features

- Efficiency up to 90.5%
- Fixed Switching Frequency
- 14:1 Input Range
- Regulated Outputs
- Remote On/Off
- Low No Load Power Consumption
- Fully protected (OTP/OCP/OVP/UVLO)
- 3000Vac I/O Isolation
- Operating Case Temperature -40 to +105°C
- Quarter Brick Size Meet Industrial Standard 2.28"x1.45"x0.5"
- CB Test Certificate IEC 62368-1
- EN 55032/EN 55035/EN 50155 Compliant with External Circuits
- UL 62368-1 3rd (Reinforce Insulation) Approval
- Shock & Vibration EN 50155 (EN 61373) Compliant
- Fire & Smoke EN 45545-2 Compliant
- 5000m Operating Altitude
- Option Model with Bus & External UVLO Function



MODEL NUMBER	INPUT VOLTAGE	OUTPUT VOLTAGE	OUTPUT CURRENT		INPUT CURRENT		% EFF.		CAPACITOR LOAD MAX.
			MIN.	MAX.	NO LOAD	FULL LOAD	(1)	(2)	
CQB150W14-72S05	12-160 VDC	5 VDC	0 mA	25000 mA	25 mA	1929 mA	90	90	25000uF
CQB150W14-72S12	12-160 VDC	12 VDC	0 mA	12500 mA	25 mA	2315 mA	90	89	12500uF
CQB150W14-72S15	12-160 VDC	15 VDC	0 mA	10000 mA	25 mA	2302 mA	90.5	90	10000uF
CQB150W14-72S24	12-160 VDC	24 VDC	0 mA	6300 mA	22 mA	2360 mA	89	88	6300uF
CQB150W14-72S28	12-160 VDC	28 VDC	0 mA	5400 mA	22 mA	2334 mA	90	89	5400uF
CQB150W14-72S54	12-160 VDC	54 VDC	0 mA	2800 mA	22 mA	2321 mA	90.5	89.5	1500uF

NOTE:

1. Nominal Input Voltage 72 VDC.
2. Measured at Input Voltage 110VDC.
3. An External Input Capacitor 470uF for All Models are Recommended to Reduce Input Ripple Voltage.

PART NUMBER

Series	Nominal Input Voltage	Number of Outputs	Nominal Output Voltage	Remote On/Off Logic	Mounting Inserts
CQB150W14-	II	O	XX	L	-Y (Option)
CQB150W14	72 : 72 VDC	S : Single	05 : 05VDC 12 : 12VDC 15 : 15VDC 24 : 24VDC 28 : 28VDC 54 : 54VDC	None : Positive N : Negative	None : M3x0.5 Mounting Inserts -C : Clear Mounting Insert (3.2mm DIA.) -B : With Bus & External UVLO Function -C-B : Clear Mounting Insert (3.2mm DIA.) and with Bus & External UVLO Function

Part Number Example:

CQB150W14-72S12N-C: Quarter Brick, 150W, 14:1 12-160Vdc Input, Single 12Vdc Output, Negative Logic, Clear Mounting Insert



CQB150W14 Series

TECHNICAL SPECIFICATIONS

(All specifications are typical at nominal input, full load at 25°C unless otherwise noted.)

ABSOLUTE MAXIMUM RATINGS

PARAMETER	NOTES and CONDITIONS	Device	Min.	Typ.	Max.	Units
Input Voltage	Continuous	All	-0.3		160	V _{dc}
Input Surge Voltage	1000ms max.	All			185	V _{dc}
Operating Case Temperature	At the center part of case plate	All	-40		105	°C
Storage Temperature		All	-55		125	°C

INPUT CHARACTERISTICS

PARAMETER	NOTES and CONDITIONS	Device	Min.	Typ.	Max.	Units
Operating Input Voltage		All	12	72	160	V _{dc}
Input Under Voltage Lockout						
Turn-On Voltage Threshold	80% Load	All	10.7	11	11.7	V _{dc}
Turn-Off Voltage Threshold	80% Load	All	9.7	10	10.7	V _{dc}
Lockout Hysteresis Voltage	80% Load	All		1.0		V _{dc}
BUS pin Output Voltage	V _{in} = 24 to 160V	-B Only		24	26	V _{dc}
Maximum Input Current	V _{in} =16V to 160V, Full load V _{in} =12V to 16V, 80% Load	All			12.5	A
No-Load Input Current	V _{in} =72V, I _o =0A	See Model Number Table				mA
Input Filter	Pi filter.	All				
Inrush Current (I ² t)	As per ETS300 132-2.	All			0.1	A ² s
Input Reflected Ripple Current	P-P thru 12uH inductor, 5Hz to 20MHz.	All		30		mA

OUTPUT CHARACTERISTICS

PARAMETER	NOTES and CONDITIONS	Device	Min.	Typ.	Max.	Units
Voltage Set Point Accuracy	V _{in} =72V, Full load, T _c =25°C	All	-1.0		+1.0	%
Output Voltage Regulation						
Load Regulation	Full load to no load	All			±0.2	%
Line Regulation	V _{in} =High line to low line, full load	All			±0.2	%
Temperature Coefficient	T _c =-40°C to 105°C	All			±0.02	%/°C
Output Voltage Ripple and Noise (5Hz to 20MHz bandwidth)						
Peak-to-Peak	Full load, 10uF polymer tantalum and 1uF ceramic capacitors	5V _o	150			mV
		12V _o	150			
		15V _o	150			
		24V _o	240			
		28V _o	240			
		54V _o	480			
RMS.		5V _o	80			mV
		12V _o	80			
		15V _o	80			
		24V _o	120			
		28V _o	120			
		54V _o	220			
Output Current Range	V _{in} = 12 to 16V V _{in} = 16 to 160V	See Power Derating Curve See Model Number Table				A
Over Current Protection	Hiccup Mode. Auto recovery	All	110	150	180	%
Short Circuit Protection		All	Continuous, Auto Recovery.			
External Load Capacitance	Full load (resistive)	See Model Number Table				uF



CQB150W14 Series

PARAMETER	NOTES and CONDITIONS	Device	Min.	Typ.	Max.	Units
Output Voltage Trim Range	$P_o \leq \text{max. rated power, } I_o \leq I_{o_max.}$	Others 54Vo	-20 -20		+15 +10	%
Output Voltage Remote Sense Range	$P_o \leq \text{max. rated power, } I_o \leq I_{o_max.}$ % of nominal V_o	Others 54Vo			+15 +10	%
Over Voltage Protection	Limited Voltage, % of Nominal V_o	Others 54Vo	117 112	125 117	140 140	%

EFFICIENCY

PARAMETER	NOTES and CONDITIONS	Device	Min.	Typ.	Max.	Units
100% Load	$V_{in}=72V, 110V$	See Model Number Table				%

DYNAMIC CHARACTERISTICS

PARAMETER	NOTES and CONDITIONS	Device	Min.	Typ.	Max.	Units
Output Voltage Current Transient						
Error Band	75% to 100% of I_{o_max} step load change $dI/dt=0.1A/us$ (within 1% V_{out} nominal)	All			± 5	%
Recovery Time		All			250	us
Turn-On Delay and Rise Time	Full load (Constant resistive load)					
Turn-On Delay Time, From On/Off Control	$V_{on/off}$ to 10% V_{o_set} , Remote on	All		50		ms
Turn-On Delay Time, From Input	$V_{in_min.}$ to 10% V_{o_set} , Power up	All		50		ms
Output Voltage Rise Time	10% V_{o_set} to 90% V_{o_set}	All		50		ms

ISOLATION CHARACTERISTICS

PARAMETER	NOTES and CONDITIONS	Device	Min.	Typ.	Max.	Units
Isolation Voltage (100% factory Hi-Pot tested @2 sec.)	1 Minute; input to output	All			3000 4200	V_{ac} V_{dc}
	1 Minute; input to case (base plate)	All			2100 3000	V_{ac} V_{dc}
	1 Minute; output to case (base plate)	All			1500 2100	V_{ac} V_{dc}
Isolation Resistance	Input to output	All	100			M Ω
Isolation Capacitance	Input to output	All		1100		pF

FEATURE CHARACTERISTICS

PARAMETER	NOTES and CONDITIONS	Device	Min.	Typ.	Max.	Units
Switching Frequency	Output ripple frequency	All	180	200	220	KHz
On/Off Control, Positive Remote On/Off Logic, Refer to -Vin Pin						
Logic Low (Module Off)	$V_{on/off}$ at $I_{on/off}=1.0mA$	All	0		1.2	V
Logic High (Module On)	$V_{on/off}$ at $I_{on/off}=0.0uA$, Pin open=on	All	3.5 or Open Circuit		160	V
On/Off Control, Negative Remote On/Off Logic, Refer to -Vin Pin						
Logic High (Module Off)	$V_{on/off}$ at $I_{on/off}=0.0uA$, Pin open=off	All	3.5 or Open Circuit		160	V
Logic Low (Module On)	$V_{on/off}$ at $I_{on/off}=1.0mA$	All	0		1.2	V
On/Off Current (for Both Remote On/Off Logic)	$I_{on/off}$ at $V_{on/off}=0V$	All		0.4	1	mA
Leakage Current (for Both Remote On/Off Logic)	Logic high, $V_{on/off}=15V$	All			30	uA
Off Converter Input Current	Shutdown input idle current	-B Others		6 4	12 10	mA
Over Temperature Shutdown	Temperature at the center part of case, non-latching	All		110		°C
Over Temperature Recovery		All		100		°C



CQB150W14 Series

GENERAL SPECIFICATIONS

PARAMETER	NOTES and CONDITIONS	Device	Min.	Typ.	Max.	Units
MTBF	$I_o=100\%$ of I_{o_max} ; MIL-HDBK - 217F_Note 1, GB, 25°C	05Vo 12Vo 15Vo 24Vo 28Vo 54Vo		560 620 765 900 845 990		K hours
Weight		All		66		grams
Potting Material	UL 94V-0					
Case Material	Plastic, DAP, UL 94V-0					
Base plate Material	Aluminum Base Plate					
Shock/Vibration	MIL-STD-810F/EN 61373 Compliant					
Humidity	95% RH max. Non Condensing					
Altitude	5000m Operating Altitude, 12000m Transport Altitude					
Thermal Shock	MIL-STD-810F					
Fire & Smoke	EN 45545-2 Compliant					
EMI	Meets EN 55032 & EN 50155 Compliant (with external filter)					Class A
ESD	EN 61000-4-2 Level 3: Air ± 8 kV, Contact ± 6 kV					Perf. Criteria A
Radiated immunity	EN 61000-4-3 Level 3: 80~1000MHz, 20V/m					Perf. Criteria A
Fast Transient	EN 61000-4-4 Level 3: On power input port, ± 2 kV, external input capacitor required (EN 50155)					Perf. Criteria A
Surge	EN 61000-4-5 Level 4: Line to earth, ± 4 kV, Line to line, ± 2 kV (EN 50155)					Perf. Criteria A
Conducted immunity	EN 61000-4-6 Level 3: 0.15~80MHz, 10V					Perf. Criteria A
Interruptions of Voltage Supply	EN 50155 Class S2: 10ms interruptions					Perf. Criteria A
Supply Change Over	EN 50155 Class C2: During a supply break of 30 ms					Perf. Criteria A
Application Note Link			CQB150W14 Series App Notes			
Packaging Information Link			Packaging Information			



CQB150W14 Series

Immunity to Environmental Conditions

Phenomenon	EN50155; 2017 Reference Clause(s)	Reference Standard	Test Conditions	Result
Low Temperature Test	13.4.4	EN 60068-2-1	Class OT6 Temperature: -40°C Duration: 2 hrs	Pass
Dry Heat Test	13.4.5	EN 60068-2-2	Class OT6(Cycle A) Temperature: 85°C Duration: 6 hrs	Pass
Low Temperature Storage Test	13.4.6	EN 60068-2-1	Temperature: -40°C Duration: 16 hrs	Pass
Cyclic Damp Heat Test	13.4.7	EN 60068-2-30	Temperature: +25°C and +55°C Humidity: 90% RH Duration: 48 hrs	Pass
Random Vibration Test	13.4.11	EN 61373	Temperature: 25±10°C Humidity: 50% ±25% RH Frequency range: 5 ~ 150 Hz Vertical: 0.988 m/s^2 Transverse: 0.441 m/s^2 Longitudinal: 0.683 m/s^2 Duration: 10 min / axis	Pass
Simulated Long Life Test at Increased Random Vibration Levels	13.4.11	EN 61373	Temperature: 25°C±10°C Humidity: 50% +/-25% RH Frequency range: 5 ~ 150 Hz Vertical: 5.59 m/s^2 Transverse: 2.49 m/s^2 Longitudinal: 3.87 m/s^2 Duration: 5 hrs / axis	Pass
Shock Test	13.4.11	EN 61373	Temperature: 25°C±10°C Humidity: 50% +/-25% RH Frequency range: 5 ~ 150 Hz ±Vertical: 30 m/s^2 ±Transverse: 30 m/s^2 ±Longitudinal: 50 m/s^2 Duration: 30ms x18 (Each axis 3 shocks)	Pass

EN45545-2 Fire & Smoke Test Conditions

Item		Standard	Hazard Level
R22	Oxygen Index Test	EN 45545-2: 2013 EN ISO 4589-2: 2006	HL1, HL2, HL3
	Smoke Density Test	EN 45545-2: 2013 EN ISO 5659-2: 2013	HL1, HL2, HL3
	Smoke Toxicity Test	EN 45545-2: 2013 NF X70-100: 2006	HL1, HL2, HL3
R23	Oxygen Index Test	EN 45545-2: 2013 EN ISO 4589-2: 2006	HL1, HL2, HL3
	Smoke Density Test	EN 45545-2: 2013 EN ISO 5659-2: 2013	HL1, HL2, HL3
	Smoke Toxicity Test	EN 45545-2: 2013 NF X70-100: 2006	HL1, HL2, HL3
R24	Oxygen Index Test	EN45545-2: 2013 EN ISO 4589-2	HL1, HL2, HL3
R25	Glow - Wire Test	EN 45545-2:2013 EN 60695-2-11:2001	HL1, HL2, HL3
R26	Vertical Flame Test	EN 45545-2: 2013 EN 60695-11-10: 2013	HL1, HL2, HL3




CQB150W14 Series


CHARACTERISTIC CURVE

Power Derating Curve


CQB150W14-72S05 Derating Curve
without Heatsink (Vin=72V)




CQB150W14-72S12, 15, 28, 54 Derating Curve
without Heatsink (Vin=72V)




CQB150W14-72S24 Derating Curve
without Heatsink (Vin=72V)




CQB150W14-72S05 Derating Curve
with Heatsink QBL127 (Vin=72V)



CQB150W14-72S12, 15, 28, 54 Derating Curve
with Heatsink QBL127 (Vin=72V)




CQB150W14-72S24 Derating Curve
with Heatsink QBL127 (Vin=72V)






CQB150W14 Series


CQB150W14-72S05 Derating Curve with Heatsink QBT210 (Vin=72V)




CQB150W14-72S12, 15, 28, 54 Derating Curve with Heatsink QBT210 (Vin=72V)



CQB150W14-72S24 Derating Curve with Heatsink QBT210 (Vin=72V)




Typical Derating Curve VS Input Voltage




Performance Data


CQB150W14-72S05 Eff Vs Io @25 Deg. C




CQB150W14-72S05 Pd Vs Po @25 Deg. C



CQB150W14-72S12 Eff Vs Io @25 Deg. C




CQB150W14-72S12 Pd Vs Po @25 Deg. C






CQB150W14 Series


CQB150W14-72S15
Eff Vs Io @25 Deg. C




CQB150W14-72S15
Pd Vs Po @25 Deg. C




CQB150W14-72S24
Eff Vs Io @25 Deg. C




CQB150W14-72S24
Pd Vs Po @25 Deg. C




CQB150W14-72S28
Eff Vs Io @25 Deg. C




CQB150W14-72S28
Pd Vs Po @25 Deg. C



CQB150W14-72S54
Eff Vs Io @25 Deg. C




CQB150W14-72S54
Pd Vs Po @25 Deg. C






CQB150W14 Series


CQB150W14-72S05
Eff Vs Vin @25 Deg. C




CQB150W14-72S12
Eff Vs Vin @25 Deg. C




CQB150W14-72S15
Eff Vs Vin @25 Deg. C




CQB150W14-72S24
Eff Vs Vin @25 Deg. C



CQB150W14-72S28
Eff Vs Vin @25 Deg. C



CQB150W14-72S54
Eff Vs Vin @25 Deg. C




Note: 12Vin Efficiency at 80% Full Load



CQB150W14 Series

MECHANICAL SPECIFICATION



PIN CONNECTION		
PIN	STANDARD	OPTION -B
	Function	
1	+V Input	+V Input
2	On / Off	On / Off
3	-V Input	-V Input
4	-V Output	-V Output
5	-Sense	-Sense
6	Trim	Trim
7	+Sense	+Sense
8	+V Output	+V Output
9	NP	Bus(Option)
10	NP	UVLO(Option)

*NP-NO PIN

All Dimensions In Inches[mm]
Tolerances Inches: X.XX= ± 0.02 , X.XXX= ± 0.010
Millimeters: X.X= ± 0.5 , X.XX= ± 0.25

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Cincon:

[CQB150W14-72S05](#) [CQB150W14-72S05-B](#) [CQB150W14-72S05-C](#) [CQB150W14-72S05-C-B](#) [CQB150W14-72S05N](#)
[CQB150W14-72S05N-B](#) [CQB150W14-72S12](#) [CQB150W14-72S12-B](#) [CQB150W14-72S12-C](#) [CQB150W14-72S12-](#)
[C-B](#) [CQB150W14-72S12N](#) [CQB150W14-72S12N-B](#) [CQB150W14-72S15](#) [CQB150W14-72S15-B](#) [CQB150W14-](#)
[72S15-C](#) [CQB150W14-72S15-C-B](#) [CQB150W14-72S15N](#) [CQB150W14-72S15N-B](#) [CQB150W14-72S24](#)
[CQB150W14-72S24-B](#) [CQB150W14-72S24-C](#) [CQB150W14-72S24-C-B](#) [CQB150W14-72S24N](#) [CQB150W14-](#)
[72S24N-B](#) [CQB150W14-72S28](#) [CQB150W14-72S28-B](#) [CQB150W14-72S28-C](#) [CQB150W14-72S28-C-B](#)
[CQB150W14-72S28N](#) [CQB150W14-72S28N-B](#) [CQB150W14-72S54](#) [CQB150W14-72S54-B](#) [CQB150W14-72S54-C](#)
[CQB150W14-72S54-C-B](#) [CQB150W14-72S54N](#) [CQB150W14-72S54N-B](#)