



CFM500S SERIES

500 WATT AC-DC

POWER SUPPLY WITH PFC

Features

- Universal Input Range 80~264Vac
- High Efficiency up to 94.5%
- 3"x 5" Compact Size
- High Power Density Up to 20.96W/Inch³
- 390W Natural, 470 ~ 500W Conduction Convection
- No Load Power Consumption<0.5W
- Over Temperature Protection
- PS On/Off Remote Control
- Power Good & Power Fail Signal
- +5V Stand-by, 12V Fan Output
- Low Inrush Current
- Active PFC Meets EN61000-3-2
- Meets EN55032 Class B
- Meets IEC/EN60335-1
- Class I



MODEL NUMBER	OUTPUT VOLTAGE	OUTPUT CURRENT NOTE1			VOLTAGE ACCURACY NOTE2	RIPPLE &NOISE NOTE3	VOLTAGE ADJ. RANCE	LINE REGULATION NOTE4	LOAD REGULATION NOTE5	%EFF. (Typ)
		With Fan	Without Fan							
			Cover	Open						
CFM500S120	12 V	41.67A	27.5A	25A	±1%	1%	11.4~12.6 V	±0.5%	±1%	91.5%
CFM500S180	18 V	27.78A	18.33A	16.67A	±1%	1%	17.1~18.9 V	±0.5%	±1%	92.5%
CFM500S240	24 V	20.83A	17.08A	15.83A	±1%	1%	22.8~25.2 V	±0.5%	±1%	93%
CFM500S360	36 V	13.89A	11.39A	10.56A	±1%	1%	34.2~37.8 V	±0.5%	±1%	94.5%
CFM500S480	48 V	10.42A	8.54A	7.92A	±1%	1%	45.6~50.4 V	±0.5%	±1%	94%
Stand-by Output Voltage										
All	+5V	1A			±3%	1%	---	±1%	±5%	---
Fan Output Voltage										
All	+12V	0.5A (NOTE 6)			---	---	---	---	---	---

Note:

1. Forced air Convection with 21CFM Fan.
2. Voltage Accuracy is Set at Full Load and 25°C Ta.
3. Add a 0.1uF Ceramic Capacitor and a 10uF E.L. Capacitor to Output for Ripple & Noise Measuring @20MHz B.W.
4. Line Regulation is Measured from High Line to Low Line with Rated Load.
5. Load Regulation is Measured from Full Load to 10% Rated Load.
6. Fan Output Can Only Operate Normal When the Stand-by Output is Above 0.5A.

PART NUMBER

Series	Number of Outputs	Nominal Output Voltage	Type
CFM500	O	XXX	Y (Option)
CFM500	S: Medical	120: 12VDC	None: Open frame C: With Cover
		180: 18VDC	
		240: 24VDC	
		360: 36VDC	
		480: 48VDC	

Part Number Example:

CFM500S120: Open Frame, 500W, 12Vdc Output

CFM500S120C: With Case, 500W, 12Vdc Output

www.cincon.com



CFM500S Series

TECHNICAL SPECIFICATIONS

(All specifications are typical at nominal input, full load at 25°C unless otherwise noted.)

ABSOLUTE MAXIMUM RATINGS

PARAMETER	NOTES and CONDITIONS	Device	Min.	Typ.	Max.	Units
Input Voltage	Safety approvals only to the AC input	All	80		264	V_{ac} V_{dc}
Operating Case Temperature	See Derating Curve	All	-40		85	°C
Storage Temperature		All	-40		85	°C
Operating Altitude		All			5000	m

INPUT CHARACTERISTICS

PARAMETER	NOTES and CONDITIONS	Device	Min.	Typ.	Max.	Units
Operating Voltage Range		All	100		240	V_{ac}
Input Frequency Range		All	47		63	Hz
Maximum Input Current	100% Load, $V_{in}=100V_{ac}$	All			6	A
Leakage Current		All			3.5	mA
Inrush Current	$V_{in}=240V_{ac}$, Cold Start at 25°C.	All		8.5		A

OUTPUT CHARACTERISTICS

PARAMETER	NOTES and CONDITIONS	Device	Min.	Typ.	Max.	Units
Output Voltage Set Point	V_{in} =Nominal V_{in} , $I_o=I_o$ max., $T_c=25^\circ C$.	CFM500S120	11.88	12	12.12	V_{dc}
		CFM500S180	17.82	18	18.18	
		CFM500S240	23.76	24	24.24	
		CFM500S360	35.64	36	36.36	
		CFM500S480	47.52	48	48.48	
Operating Output Current Range		CFM500S120			41.67	A
		CFM500S180			27.78	
		CFM500S240			20.83	
		CFM500S360			13.89	
		CFM500S480			10.42	
Holdup Time	$V_{in}=115V_{ac}$	All		16		ms
Output Voltage Regulation						
Load Regulation	10% Load to Full Load	All			± 1.0	%
Line Regulation	V_{in} =High Line to Low Line	All			± 0.5	%
Over Voltage Protection	Latch Off (AC Recycle to Reset)	CFM500S120			16	V_{dc}
		CFM500S180			30	
		CFM500S240			35	
		CFM500S360			50	
		CFM500S480			63	
Over Current Protection	Auto Recovery	All	120		190	%
Short Circuit Protection	Auto Recovery	All				
Output Ripple and Noise	1. Add a 0.1uF Ceramic Capacitor and a 10uF Aluminum Electrolytic Capacitor to Output. 2. Oscilloscope is 20MHz Band Width. 3. Ambient Temperature=25°C	CFM500S120			120	mV
		CFM500S180			150	
		CFM500S240			150	
		CFM500S360			200	
		CFM500S480			250	
Load Capacitance	1. Ambient Temperature=25°C 2. Input Voltage is 115VAC and 230VAC 3. Output is max. Load	CFM500S120			42900	uF
		CFM500S180			28600	
		CFM500S240			20800	
		CFM500S360			14000	
		CFM500S480			10800	



CFM500S Series

PARAMETER	NOTES and CONDITIONS	Device	Min.	Typ.	Max.	Units
Efficiency	Output is Rated Load Ambient Temperature=25°C @ Input Voltage is 230VAC	CFM500S120 CFM500S180 CFM500S240 CFM500S360 CFM500S480		91.5 92.5 93 94.5 94		%
PS-On Signal	Power on	All	0		2	Vdc
	Power off (PS-ON and GND open)			4		
	Power on (PS-ON and GND short)			10		mA
	Power-off (PS-ON and GND open)			0		
Power Good (PG)	1. Input voltage is 90VAC~264VAC 2. Output is max. load 3. The TTL goes high after power set up	All	100		500	ms
Power Fail (PF)	1. Input voltage is 90VAC~264VAC 2. Output is max. load 3. The TTL goes low before Vo below 90% rated value	All	1	10		ms

ISOLATION CHARACTERISTICS

PARAMETER	NOTES and CONDITIONS	Device	Min.	Typ.	Max.	Units
Input to Output	1 minute	All			4000	V _{ac}
Isolation Resistance	Input to Output	All	100			MΩ

FEATURE CHARACTERISTICS

PARAMETER	NOTES and CONDITIONS	Device	Min.	Typ.	Max.	Units
Switching Frequency	P _{out} =max. rated power	All		65		kHz
Output Voltage adjustment		All	-5		+5	%

GENERAL SPECIFICATIONS

PARAMETER	NOTES and CONDITIONS	Device	Min.	Typ.	Max.	Units
MTBF	I _o =100%; T _a =25℃ per MIL-HDBK-217F	All		200		K hours
Humidity	Nom-condensing	All			93	% RH
Shock	Meet MIL-STD-810F Table 516.5,Table 516.5-1 10ms, each axis 3 times(±X、±Y、±Z axis)	All		75		g
Vibration	Meet MIL-STD-810F Table 514.5C-VIII,15~2000Hz, X·Y·Z axis, 1 hour (each axis),. Total 3 hrs.	All		4		g
Weight	Open Frame Versions	All		515		g
	Covered Versions			635		
Dimensions	Open Frame	All	5.000x3.000x1.540 Inches (127.00x76.20x39.10mm)			
	C (with Cover)	All	5.354x3.425x1.673 Inches (136.00x87.00x42.50mm)			
Safety	Class I, IEC/EN/UL62368-1					
EMC Emission	EN55032:2015+AC:2016, EN61204-3:2000, EN61000-6-3:2007+A1:2011+AC:2012, EN61000-6-4:2007+A1:2011, 47 CFR FCC Part 15 Subpart B (Class B)					Class B
Conducted Disturbance	EN55032, 47 CFR FCC Part 15 Subpart B (Class B)					Class B
Radiated Disturbance	EN55032, 47 CFR FCC Part 15 Subpart B (Class B)					Class B
Harmonic Current Emissions	EN61000-3-2:2014					Class A,C,D
Voltage Fluctuations & Flicker	EN61000-3-3:2013					
EMC Immunity	EN55035:2017, EN61204-3:2000, EN61000-6-1:2019+CRGD:2019, EN61000-6-2:2019					
Electrostatic Discharge (ESD)	IEC61000-4-2:2008, Air Discharge: ±8kV, Contact Discharge: ±4kV					Criterion A
Radio-Frequency, Continuous Radiated Disturbance	IEC61000-4-3:2006+A1:2007+A2:2010					Criterion A
Electrical Fast Transient (EFT)	IEC61000-4-4:2012, ±1kV, ±2kV					Criterion A
Surge	IEC61000-4-5:2014+A1:2017, L-N: ±0.5kV, ±1kV, L-E(Ground): ±0.5kV, ±1kV, ±2kV					Criterion A



CFM500S Series

GENERAL SPECIFICATIONS


Conducted Disturbances, Induced by RF Fields	IEC61000-4-6:2013+COR1:2015	Criterion A
Power Frequency Magnetic Field	IEC61000-4-8:2009	Criterion A
Voltage Dips	IEC61000-4-11:2004+A1:2017, Dip: 30% Reduction, Dip >95% Reduction	Criterion A
Voltage Interruptions	IEC61000-4-11:2017+A1:2017, >95% Reduction	Criterion B
Application Note Link		CFM500S Series App Notes

CHARACTERISTIC CURVE

Power Derating Curve


Forced Air Flow

Output power & Input voltage




Forced Air Flow

Output power vs Ambient Temperature




Natural Convection

Output power & Input Voltage




Natural Convection


Output power vs Ambient Temperature



Output power & Input Voltage




Output power vs Ambient Temperature






Conduction Convection with External Baseplate
(48x24.8x0.12cm)


Output power & Input Voltage




Output power vs Ambient Temperature



Output power & Input Voltage




Output power vs Ambient Temperature




Performance Data


CFM500S120 (Eff Vs Io)




CFM500S180 (Eff Vs Io)




CFM500S240 (Eff Vs Io)






CFM500S360 (Eff Vs Io)



CFM500S480 (Eff Vs Io)






MECHANICAL SPECIFICATION





CFM500S Series



CN1: PIN CONNECTION

Pin	Function
1	ACL
2	-
3	ACN

CN2: PIN CONNECTION

Pin	Function
1	GND
2	+5VSB
3	GND
4	+12V-FAN

CN3: PIN CONNECTION

Pin	Function
1	GND
2	PF
3	FAN-EN
4	PS-ON
5	-Sense
6	+Sense
7	OPTION

All Dimensions In Inches[mm]
Tolerance Inches:x.xxx = ± 0.02
Millimeters: x.xx = ± 0.5

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Cincon:

[CFM500S120](#) [CFM500S120C](#) [CFM500S180](#) [CFM500S180C](#) [CFM500S240](#) [CFM500S240C](#) [CFM500S360](#)
[CFM500S360C](#) [CFM500S480](#) [CFM500S480C](#)