

CQB100W SERIES 100WATT 4:1 INPUT DC-DC CONVERTERS

FEATURES

- *100W Isolated Output
- * Quarter-Brick Package
- * 4:1 Input Range
- * Efficiency to 88%
- * Regulated Output
- * Input Under Voltage Protection
- * Over Temperature Protection
- * Over Voltage/Current Protection
- * Remote On/Off
- * 1500VDC Isolation
- * Safety Meets IEC/EN/UL 62368-1



MODEL INPUT		OUTPUT	OUTPUT CURRENT		INPUT CURRENT		%	CAPACITOR
NUMBER	VOLTAGE	VOLTAGE	MIN.	MAX.	NO LOAD	FULL LOAD	EFF.	LOAD MAX.
CQB100W-24S3V3	9-36 VDC	3.3 VDC	0 mA	30 A	120 mA	4797 mA	86	10000µF
CQB100W-24S05	9-36 VDC	5.0 VDC	0 mA	20 A	120 mA	4817 mA	86.5	10000µF
CQB100W-24S12	9-36 VDC	12 VDC	0 mA	8.3 A	80 mA	4798 mA	86.5	2200µF
CQB100W-24S15	9-36 VDC	15 VDC	0 mA	6.7 A	80 mA	4841 mA	86.5	2200µF
CQB100W-24S24	9-36 VDC	24 VDC	0 mA	4.17 A	80 mA	4793 mA	87	2200µF
CQB100W-48S3V3	18-75 VDC	3.3 VDC	0 mA	30 A	60 mA	2344 mA	88	10000µF
CQB100W-48S05	18-75 VDC	5.0 VDC	0 mA	20 A	60 mA	2367 mA	88	10000µF
CQB100W-48S12	18-75 VDC	12 VDC	0 mA	8.3 A	30 mA	2358 mA	88	2200µF
CQB100W-48S15	18-75 VDC	15 VDC	0 mA	6.7 A	30 mA	2379 mA	88	2200µF
CQB100W-48S24	18-75 VDC	24 VDC	0 mA	4.17 A	30 mA	2369 mA	88	2200µF

NOTE: 1. Nominal Input Voltage 24, 48VDC

SPECIFICATIONS

All Specifications Typical at Nominal Line, Full Load, and 25°C Unless Otherwise Noted

INPUT SPECIFICATIONS:

Input Voltage Range	24V 9 - 36V					
	48V 18 - 75V					
Input Surge Voltage (100ms max.)	24V 50Vdc max.					
	48V 100Vdc max.					
Under voltage lockout	24Vin power up 8.8V typ.					
	power down 8V typ.					
	48Vin power up 17V typ.					
	power down 16V typ.					
Input Filter	Pi Type					
Positive Logic Remote On/Off (note4&5)						
OUTPUT SPECIFICATIONS:						
Voltage Accuracy	±1.0% max.					
Transient Response: 75% to 100% Step Load Change						
Error Band	3.3V±7% Vout, Others ±5% Vout					
Recover Time .	<500us					
External Trim Adj. Range (note6) ±10%						
	±10%					
Ripple and Noise, 20MHz BW (note3						
Ripple and Noise, 20MHz BW (note3 3.3V & 5V	3). 40mV RMS, 100mV pk-pk max.					
Ripple and Noise, 20MHz BW (note3 3.3V & 5V 12V & 15V	3). 40mV RMS, 100mV pk-pk max. 60mV RMS, 150mV pk-pk max.					
Ripple and Noise, 20MHz BW (note3 3.3V & 5V	3). 40mV RMS, 100mV pk-pk max. 60mV RMS, 150mV pk-pk max. 100mV RMS, 240mV pk-pk max.					
Ripple and Noise, 20MHz BW (note3 3.3V & 5V	3). 40mV RMS, 100mV pk-pk max. 60mV RMS, 150mV pk-pk max.					
Ripple and Noise, 20MHz BW (note: 3.3V & 5V	3). 40mV RMS, 100mV pk-pk max. 60mV RMS, 150mV pk-pk max. 100mV RMS, 240mV pk-pk max. ±0.03%°C max.					
Ripple and Noise, 20MHz BW (note: 3.3V & 5V	3). 40mV RMS, 100mV pk-pk max. 60mV RMS, 150mV pk-pk max. 100mV RMS, 240mV pk-pk max. 					
Ripple and Noise, 20MHz BW (note: 3.3V & 5V	3) 40mV RMS, 100mV pk-pk max 60mV RMS, 150mV pk-pk max 100mV RMS, 240mV pk-pk max ±0.03%°C max Continuous ±0.2% max.					


GENERAL SPECIFICATIONS:


Efficiency	See Table				
Isolation Voltage Input/Output, Input/Case, Output/Case 1500VDC mir					
Isolation Resistance	10 ⁷ Ohms min.				
Isolation Capacitance	1000pF typ.				
Switching Frequency	48Vin 250KHz typ.				
	24Vin 220KHz typ.				
Operating Case Temperature	40°C to 100°C				
Storage Temperature Range	40°C to +105°C				
Thermal Shutdown, Case Temp	110°C typ.				
Humidity	95% RH max. Non Condensing				
MTBF MIL-HDBK-217F, GB	3, 25°C, Full Load 600Khrs typ.				
Case Material Al	uminum Base-Plate with Plastic Case				
Dimensions 1.45 x 2.28	x 0.50 inche s(36.8 x 57.9 x 12.7 mm)				
Weight	66g				

NOTE:

- 1. Measured from high line to low line.
- 2. Measured from full load to min. load.
- The output noise is measured with 10uF tantalum capacitor and 1uF ceramic capacitor across output.

- 6. Trim-up connect a resistor between the trim pin and +Sense Trim-down connect a resistor between the trim pin and -Sense
- 7. Suffix "-C" to the Model Number with Clear Mounting Insert (3.2mm DIA.)
- 8. An external input capacitor 47uF for 48Vin models and 100uF for 24Vin models are recommended to reduce input ripple voltage.





Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Cincon:

CQB100W-48S3V3 CQB100W-48S24N CQB100W-48S12N CQB100W-48S3V3N CQB100W-48S12 CQB100W-48S24 CQB100W-48S15 CQB100W-48S05N CQB100W-48S15N CQB100W-48S05 CQB100W-24S24-DIN CQB100W-24S05N-DIN CQB100W-24S12-DIN CQB100W-48S05-DIN CQB100W-48S15N-CM CQB100W-48S05N-DIN CQB100W-24S05N-CM CQB100W-24S3V3-CM CQB100W-48S3V3-DIN CQB100W-24S15N-DIN CQB100W-48S12-CM CQB100W-48S24N-DIN CQB100W-48S05-CM CQB100W-24S05-DIN CQB100W-48S24N-CM CQB100W-48S12N-CM CQB100W-24S15-DIN CQB100W-48S15N-DIN CQB100W-24S05-CM CQB100W-24S24N-CM CQB100W-24S3V3-DIN CQB100W-48S15-DIN CQB100W-24S12N-CM CQB100W-48S3V3N-DIN CQB100W-48S05N-CM CQB100W-48S12-DIN CQB100W-48S3V3-CM CQB100W-24S12N-DIN CQB100W-24S3V3N-DIN CQB100W-48S15-CM CQB100W-48S3V3N-CM CQB100W-48S12N-DIN CQB100W-24S24-CM CQB100W-48S24-DIN CQB100W-24S15N-CM CQB100W-24S3V3N-CM CQB100W-48S24-CM CQB100W-24S24N-DIN CQB100W-24S12-CM CQB100W-24S15-CM CQB100W-110S05-CMFC CQB100W-110S05-CMFD CQB100W-110S05N-CMFC CQB100W-110S05N-CMFD CQB100W-110S12-CMFC CQB100W-110S12-CMFD CQB100W-110S28N-CMFC CQB100W-110S28N-CMFD CQB100W-110S48-CMFC CQB100W-110S48-CMFD CQB100W-110S48N-CMFC CQB100W-110S48N-CMFD CQB100W-110S24-CMFC CQB100W-110S24-CMFD CQB100W-110S24N-CMFC CQB100W-110S24N-CMFD CQB100W-110S28-CMFC CQB100W-110S28-CMFD CQB100W-110S12N-CMFC CQB100W-110S12N-CMFD CQB100W-110S15-CMFC CQB100W-110S15-CMFD CQB100W-110S15N-CMFC CQB100W-110S15N-CMFD CQB100W-24S12 CQB100W-24S15 CQB100W-24S24 CQB100W-24S3V3