




EC3B SERIES

7.5 WATT 2:1 INPUT RANGE

DC-DC CONVERTERS

FEATURES

- * 7.5W Isolated Output
- * Efficiency to 82%
- * 2" x 1" Case
- * Regulated Outputs
- * Pi Input Filter
- * Continuous Short Circuit Protection



Not Recommended for New Designs

MODEL NUMBER	INPUT VOLTAGE	OUTPUT VOLTAGE	OUTPUT CURRENT	INPUT CURRENT		% EFF.	SIZE
				NO LOAD	FULL LOAD		
EC3B01	9-18 VDC	5 VDC	1500 mA	7.5 mA	820 mA	76	2"x1"
EC3B02	9-18 VDC	12 VDC	625 mA	7.5 mA	780 mA	80	2"x1"
EC3B03	9-18 VDC	15 VDC	500 mA	7.5 mA	780 mA	80	2"x1"
EC3B04	9-18 VDC	±12 VDC	±310 mA	12 mA	775 mA	80	2"x1"
EC3B05	9-18 VDC	±15 VDC	±250 mA	12 mA	780 mA	80	2"x1"
EC3B06	9-18 VDC	±5 VDC	±750 mA	7.5 mA	820 mA	76	2"x1"
EC3B07	9-18 VDC	3.3 VDC	1500 mA	7.5 mA	557 mA	74	2"x1"
EC3B11	18-36 VDC	5 VDC	1500 mA	5 mA	400 mA	78	2"x1"
EC3B12	18-36 VDC	12 VDC	625 mA	5 mA	380 mA	82	2"x1"
EC3B13	18-36 VDC	15 VDC	500 mA	5 mA	380 mA	82	2"x1"
EC3B14	18-36 VDC	±12 VDC	±310 mA	7.5 mA	385 mA	81	2"x1"
EC3B15	18-36 VDC	±15 VDC	±250 mA	7.5 mA	385 mA	81	2"x1"
EC3B16	18-36 VDC	±5 VDC	±750 mA	7.5 mA	400 mA	78	2"x1"
EC3B17	18-36 VDC	3.3 VDC	1500 mA	5 mA	271 mA	76	2"x1"
EC3B21	36-72 VDC	5 VDC	1500 mA	2 mA	200 mA	78	2"x1"
EC3B22	36-72 VDC	12 VDC	625 mA	2 mA	192 mA	81	2"x1"
EC3B23	36-72 VDC	15 VDC	500 mA	2 mA	192 mA	81	2"x1"
EC3B24	36-72 VDC	±12 VDC	±310 mA	3 mA	192 mA	81	2"x1"
EC3B25	36-72 VDC	±15 VDC	±250 mA	3 mA	192 mA	81	2"x1"
EC3B26	36-72 VDC	±5 VDC	±750 mA	3 mA	200 mA	78	2"x1"
EC3B27	36-72 VDC	3.3 VDC	1500 mA	3 mA	136 mA	76	2"x1"

NOTE: 1. Nominal Input Voltage 12, 24 or 48VDC

SPECIFICATIONS

All Specifications Typical At Nominal Line, Full Load, and 25°C Unless Otherwise Noted

INPUT SPECIFICATIONS:

Input Voltage Range	12V	9-18V
	24V	18-36V
	48V	36-72V
Input Filter	Pi Type	

OUTPUT SPECIFICATIONS:

Voltage Accuracy	±2.0% max.	
Voltage Balance (Dual)	±1.0% max.	
Temperature Coefficient	+0.05%/°C	
Ripple & Noise, 20MHz BW	3.3V/5V	100mV p-p max.
	12V/15V	1%p-p max.
Short Circuit Protection	Continuous	
Line Regulation Single/Dual (note 1)	±0.5% max.	
Load Regulation Single (note 2)	±0.5% max.	
	Dual (note 3)	±1.0% max.

GENERAL SPECIFICATIONS:


Efficiency	See Table
Isolation Voltage	1500 VDC min.
Isolation Resistance	10 ⁹ ohms
Switching Frequency	100KHz min.

Operating Ambient Temperature Range	-25°C to +71°C
De-rating. Above 71°C	Linearly to Zero power at 100°C
Case Temperature (note 4)	100°C max.
Cooling	Natural Convection
Storage Temperature Range	-40°C to +100°C
Dimensions	2.00×1.00×0.40 inches (50.8×25.4×10.2mm)
Case Material	Black Coated Copper With Non-Conductive Base
Weight	35g

NOTE:


1. Measured from high line to low line.
2. Measured from full load to 10% load.
3. Measured from full load to 1/4 load.
4. Maximum case temperature under any operating condition should not be exceeded 100°C.

Typical Derating curve for Natural Convection



Case B Dimensions:

All Dimensions In Inches (mm)
 Tolerances Inches: X.XX= ±0.04, X.XXX= ±0.010
 Millimeters: X.X= ±1, X.XX= ±0.25



PIN CONNECTION	
Pin	Function
1.	+Input
2.	-Input
3.	+Output
4.	Common/NP
5.	-Output

*NP-NO PIN ON SINGLE OUTPUT

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Cincon:

[EC3B01](#) [EC3B02](#) [EC3B03](#) [EC3B04](#) [EC3B05](#) [EC3B06](#) [EC3B07](#) [EC3B11](#) [EC3B12](#) [EC3B14](#) [EC3B15](#) [EC3B16](#)
[EC3B17](#) [EC3B21](#) [EC3B22](#) [EC3B23](#) [EC3B24](#) [EC3B25](#) [EC3B26](#) [EC3B27](#)