

## Solder Wire Sn60/Pb40 No-Clean with 2.2% Flux Core 1oz Spool

### Product Highlights

#### No-Clean Synthetic Flux Core

The clear, non-corrosive, non-conductive residue is meant to be left on the board.

2.2% flux core

Halogen content: None

### Specifications

Alloy:	Sn60/Pb40
Wire Diameter:	0.015" (0.38mm)
Flux Type:	No-Clean Synthetic
Flux Classification:	ROL0
Melting Point:	183-188°C (361-370°F)
Packaging:	1 oz spool
Shelf Life:	>60 months



### Test Results

Test J-STD-004 or other requirements as stated	Test Requirement	Result
Copper Mirror	IPC-TM-650: 2.3.32	L: No breakthrough
Corrosion	IPC-TM-650: 2.6.15	L: No corrosion
Quantitative Halides	IPC-TM-650: 2.3.28.1	L: <0.05%
Electrochemical Migration	IPC-TM-650: 2.6.14.1	L: <1 decade drop (No-clean)
Surface Insulation Resistance 85°C, 85% RH @ 168 Hours	IPC-TM-650: 2.6.3.7	L: ≥100MΩ (No-clean)
Visual	IPC-TM-650: 3.4.2.5	Clear and free from precipitation
Conflict Minerals Compliance	Electronic Industry Citizenship Coalition (EICC)	Compliant
REACH Compliance	Articles 33 and 67 of Regulation (EC) No 1907/2006	Contains Lead (Pb) CAS# 7439-92-1 No other SVHC present

### Conforms to the following Industry Standards:

J-STD-004B, Amendment 1 (Solder Fluxes):	Yes
J-STD-006C, Amendments 1 & 2 (Solder Alloys and Fluxed/Non-Fluxed Solders):	Yes
RoHS 3 Directive (EU) 2015/863:	No

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Chip Quik:](#)

[NC2SW.015 1OZ](#)