

Stained Glass Soldering Tacky Flux - Water-Soluble 10g/10cc Syringe

Product Highlights

- **Lead-Free / RoHS 3 Compliant / REACH Compliant**
- **Water-Soluble** Tacky Flux for Stained Glass Soldering
- Low viscosity
- Stays put where applied, will not run all over work piece

Specifications

Flux Type:	Synthetic Water-Soluble for Stained Glass Soldering
Flux Classification:	Water-Soluble (Residue should be water-washed off after soldering, use hot water 60°C+)
Flux Activation Temperature:	140°C (284°F)
Packaging:	10cc/10g Luer Lock Syringe w/ plunger & tips

Shelf Life

>24 months

Storage and Handling

Store refrigerated or at room temperature 3-25°C (37-77°F). Do not freeze. Allow 4 hours for flux to reach an operating temperature of 20-25°C (68-77°F) before use.

Transportation

This product has no shipping restrictions. Shipping below 0°C (32°F) or above 25°C (77°F) for normal transit times by ground or air will not impact this product's stated shelf life.



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Chip Quik:
SGF991-10CC