



EC4A SERIES


5-6 WATT 2:1 INPUT RANGE

DC-DC CONVERTERS



FEATURES

- * 5-6W Isolated Output
- * 24-Pin DIP Package
- * Efficiency to 84%
- * 2:1 Input Range
- * Regulated Outputs
- * Pi Input Filter
- * Continuous Short Circuit Protection
- * UL60950-1 Approval for H/HM Versions only



MODEL NUMBER	INPUT VOLTAGE ⁽¹⁾	OUTPUT VOLTAGE	OUTPUT CURRENT	INPUT CURRENT		% EFF. ⁽²⁾	CAPACITOR LOAD MAX.
				NO LOAD	FULL LOAD		
EC4A01	9-18 VDC	5 VDC	1000 mA	7.5 mA	541 mA	77	4700uF
EC4A02	9-18 VDC	12 VDC	470 mA	7.5 mA	573 mA	82	4700uF
EC4A03	9-18 VDC	15 VDC	400 mA	7.5 mA	625 mA	80	4700uF
EC4A04	9-18 VDC	±12 VDC	±230 mA	12 mA	554 mA	83	2200uF
EC4A05	9-18 VDC	±15 VDC	±190 mA	12 mA	556 mA	81	2200uF
EC4A06	9-18 VDC	±5 VDC	±500 mA	12 mA	541 mA	77	2200uF
EC4A07	9-18 VDC	3.3 VDC	1000 mA	7.5 mA	382 mA	72	4700uF
EC4A11	18-36 VDC	5 VDC	1000 mA	5 mA	260 mA	80	4700uF
EC4A12	18-36 VDC	12 VDC	470 mA	5 mA	280 mA	84	4700uF
EC4A13	18-36 VDC	15 VDC	400 mA	5 mA	298 mA	84	4700uF
EC4A14	18-36 VDC	±12 VDC	±230 mA	7.5 mA	280 mA	82	2200uF
EC4A15	18-36 VDC	±15 VDC	±190 mA	7.5 mA	293 mA	81	2200uF
EC4A16	18-36 VDC	±5 VDC	±500 mA	7.5 mA	260 mA	80	2200uF
EC4A17	18-36 VDC	3.3 VDC	1000 mA	5 mA	186 mA	74	4700uF
EC4A21	36-72 VDC	5 VDC	1000 mA	2 mA	132 mA	79	4700uF
EC4A22	36-72 VDC	12 VDC	470 mA	2 mA	142 mA	83	4700uF
EC4A23	36-72 VDC	15 VDC	400 mA	2 mA	154 mA	81	4700uF
EC4A24	36-72 VDC	±12 VDC	±230 mA	3 mA	142 mA	81	2200uF
EC4A25	36-72 VDC	±15 VDC	±190 mA	3 mA	147 mA	81	2200uF
EC4A26	36-72 VDC	±5 VDC	±500 mA	3 mA	130 mA	80	2200uF
EC4A27	36-72 VDC	3.3 VDC	1000 mA	2 mA	93 mA	74	4700uF

NOTE:

1. Nominal Input Voltage is 12, 24 or 48 VDC.
2. Typical value at nominal input voltage and full load.

SPECIFICATIONS

All Specifications Typical At Nominal Line, Full Load, and 25°C Unless Otherwise Noted

INPUT SPECIFICATIONS:

Input Voltage Range	12V	9-18V
	24V	18-36V
	48V	36-72V
Input Surge Voltage (100ms max.)	12V	25Vdc max.
	24V	50Vdc max.
	48V	100Vdc max.
Input Filter	Pi Type	

OUTPUT SPECIFICATIONS:

Voltage Accuracy	±2.0% max.	
Voltage Balance (Dual)	±1.0% max.	
Temperature Coefficient	±0.05%/°C	
Ripple & Noise, 20MHz BW	3.3V/5V	100mV pk-pk, max
	12V/15V	1% pk-pk max.
Short Circuit Protection	Continuous	
Line Regulation	Single/Dual (note1)	±0.5% max.
Load Regulation	Single (note2)	±0.5% max.
	Dual (note3)	±1.0% max.

NOTE:


1. Measured From High Line to Low Line.
2. Measured From Full Load to 10% Load.
3. Measured From Full Load to 1/4 Load.
4. Maximum case temperature under any operating condition should not be exceed 95°C (Plastic Case), 100°C (Copper Case).

GENERAL SPECIFICATIONS:

Efficiency	See Table	
Isolation Voltage:	500 VDC min.	Standard Models
	3K VDC min. ... (Non-Conductive Black Plastic Only)	Suffix "H" Models
	1.5K VDC min.	Suffix "HM" Models
Isolation Resistance	10 ⁹ ohm min.	
Switching Frequency	100KHz min.	
Operating Ambient Temperature Range	-25°C to +71°C	
Power de-rating Curve	see Figure1	
Case Temperature (note4) ... Plastic/Copper case...	95°C/100°C max.	
Cooling	Natural Convection	
Storage Temperature Range	-40°C to +100°C	
Humidity	95% RH max. Non condensing	
MTBF	MIL-STD-217F	2000Khrs typ.
Dimensions	DIP	1.25×0.80×0.40 inches(31.8×20.3×10.2 mm)
	SMD	1.25×0.80×0.45 inches(31.8×20.3×11.4 mm)
Case Material:		
Standard Models	Non-Conductive Black Plastic	
Suffix "M" Models	Black Coated Copper with Non-conductive Base	
Suffix "S" Models	SMD package	
Weight	12.5g	


Case A Dimensions:

NOTE: Pin Size is 0.02 ±0.002 Inch (0.5±0.05 mm) DIA
 All Dimensions In Inches (mm)
 Tolerances Inches: X.XX= ±0.02 , X.XXX= ±0.010
 Millimeters: X.X= ±0.5 , X.XX=±0.25



CASE AS

Figure1. Typical Derating curve for Natural Convection



PIN CONNECTION								
500 VDC					1.5K & 3K VDC			
Pin	Single Output		Dual Output		Pin	Single Output		Dual Output
	DIP	SMD	DIP	SMD		DIP	SMD	
1,24	+V Input		+V Input		1,24	NP	NC	NP
2,23	NC		-V Output		2,3	-V Input		-V Input
3,22	NC		Common		4,5	NP	NC	NP
4	NP	NC	NP	NC	9	NC		Common
5	NP	NC	NP	NC	10,15	NC		NC
9	NP	NC	NP	NC	11	NC		-V Output
10,15	-V Output		Common		12,13	NP	NC	NP
11,14	+V Output		+V Output		14	+V Output		+V Output
12,13	-V Input		-V Input		16	-V Output		Common
16	NP	NC	NP	NC	20,21	NP	NC	NP
20,21	NP	NC	NP	NC	22,23	+V Input		+V Input

* NP-NO PIN
 * NC-NO CONNECTION WITH PIN

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Cincon:

[EC4A02H](#) [EC4A26H](#) [EC4A05H](#) [EC4A01](#) [EC4A02](#) [EC4A03](#) [EC4A04](#) [EC4A05](#) [EC4A06](#) [EC4A07](#) [EC4A11](#)
[EC4A12](#) [EC4A13](#) [EC4A14](#) [EC4A15](#) [EC4A16](#) [EC4A17](#) [EC4A21](#) [EC4A22](#) [EC4A23](#) [EC4A24](#) [EC4A25](#) [EC4A26](#)
[EC4A27](#) [EC4A03HM](#) [EC4A05HM](#) [EC4A02M](#) [EC4A25M](#) [EC4A22HM](#) [EC4A17M](#) [EC4A24HM](#) [EC4A15M](#)
[EC4A02HM](#) [EC4A17HM](#) [EC4A03M](#) [EC4A16HM](#) [EC4A27HM](#) [EC4A27M](#) [EC4A13HM](#) [EC4A06HM](#) [EC4A04M](#)
[EC4A14M](#) [EC4A22M](#) [EC4A16M](#) [EC4A14HMS](#) [EC4A03MS](#) [EC4A02MS](#) [EC4A25MS](#) [EC4A14MS](#) [EC4A22MS](#)
[EC4A17MS](#) [EC4A16MS](#) [EC4A11MS](#) [EC4A05MS](#) [EC4A15MS](#) [EC4A07MS](#) [EC4A27MS](#) [EC4A24MS](#) [EC4A12MS](#)
[EC4A26MS](#) [EC4A21MS](#) [EC4A01MS](#) [EC4A04MS](#) [EC4A13MS](#) [EC4A23MS](#) [EC4A06MS](#) [EC4A01H-E](#) [EC4A02H-E](#)
[EC4A04H-E](#) [EC4A06H-E](#) [EC4A07H-E](#) [EC4A11H-E](#) [EC4A12H-E](#) [EC4A14H-E](#) [EC4A16H-E](#) [EC4A17H-E](#) [EC4A21H-](#)
[E](#) [EC4A22H-E](#) [EC4A24H-E](#) [EC4A26H-E](#) [EC4A27H-E](#) [EC4A01H](#) [EC4A03H](#) [EC4A07H](#) [EC4A11H](#) [EC4A12H](#)
[EC4A13H](#) [EC4A17H](#) [EC4A21H](#) [EC4A22H](#) [EC4A23H](#) [EC4A27H](#) [EC4A04H](#) [EC4A06H](#) [EC4A14H](#) [EC4A15H](#)
[EC4A16H](#) [EC4A24H](#) [EC4A25H](#) [EC4A21HM](#)