



CFM150M SERIES

150W MEDICAL AND ITE OPEN FRAME AC-DC MODULES WITH PFC



Features

- * Universal Input Range 90 ~ 264VAC
- * Medical and ITE Safeties
- * 3"x 5" Compact Size
- * Less than 1 U high : 1.05"
- * Industry Standard Pin Out
- * Active PFC Meets EN61000-3-2
- * High Efficiency up to 93%
- * Meets CISPR/FCC Class B
- * Remote Voltage Sense
- * Over Voltage Protection
- * Continuous Short Circuit Protection
- * No load Power Consumption<0.5W
- * Meets 2MOPP

MODEL	OUTPUT VOLTAGE	MAX. LOAD	MIN. LOAD	RIPPLE & NOISE NOTE 1	VOLTAGE ACCURACY NOTE 2	LINE REGULATION NOTE 3	LOAD REGULATION NOTE 4	% EFF. (Typ.) NOTE 5
CFM150M120	12 V	12.5 A	0A	1%	±1%	±0.5%	±1%	90%
CFM150M240	24 V	6.25 A	0A	1%	±1%	±0.5%	±1%	92%
CFM150M360	36 V	4.17 A	0A	1%	±1%	±0.5%	±1%	92%
CFM150M480	48 V	3.13 A	0A	1%	±1%	±0.5%	±1%	93%

Specifications

INPUT SPECIFICATIONS:

Voltage	90~264Vac
Frequency	47 to 63Hz
Inrush Current	110A max. @240Vac
Leakage Current	300uA max.

OUTPUT SPECIFICATIONS:

Hold-up Time	16ms typ.
Short Circuit Protection	Hiccup mode(Auto Recovery)
Adjustment Range on Vout	±5%
Over Voltage Protection	Recycle AC input to restart
Temperature Coefficient	±0.05%/°C

GENERAL SPECIFICATIONS:




Isolation	Input to output = 5,656VDC
Operating Temperature	-20°C ~ 70°C (see Derating Curve)
Storage Temperature	-20 ~ 85°C
Humidity	93% RH max. Non condensing
Cooling	Natural Convection
Switching Frequency	90KHz Typical.
MTBF	MIL-HDBK-217F, GB, 25°C/115VAC 100Khrs min.
Altitude	3000m
Dimensions	5.000x3.000x1.050inches (127.00x76.20x26.67mm)
Weight	270g (0.6Pounds)

SAFETY AND EMC:


Emission and Immunity (Ed. 4.0)	EN55011, EN55032 Class B
FCC CFR 47 Part 15, EN61000-3-2, 3, IEC61000-4-2, 3, 4, 5, 6, 8, 11	
Safety (Ed. 3.1)	IEC60601-1:2005+A1:2012
IEC60950-1:2005+A1:2009+A2:2013, EN60601-1:2006+A11:2011+A1+A12	
EN60950-1:2006+A11+A1+A12:2011+A2:2013, UL ANSI/AAMI ES60601-1:2005, UL60950-1, 2 nd Edition	

CFM150M Series

All Dimensions are in inches[mm]
 Tolerances : Inches : x.xxx=±0.02
 Millimeters : x.xx=±0.5



CFM150M Series Derating Curve



NOTE:

1. Add a 0.1uF ceramic capacitor and 10uF E.L. capacitor to output for Ripple & Noise measuring @20MHz BW.
2. Voltage accuracy is set at 100% rated load and 25°C Ta.
3. Line regulation is measured from high line to low line with full load.
4. Load regulation is measured from full to 10% load.
5. Typical efficiency at 230VAC and full load at 25°C.
6. Standard input and output connectors wafer with LONG CHU P3060 series and mate with MOLEX housing 09-50-1031 and 09-50-1081 or equivalent.
7. DC output pin 1, 2, 3, 4: Vout (-), DC output pin 5, 6, 7, 8: Vout (+).

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Cincon:

[CFM150M120](#) [CFM150M240](#) [CFM150M360](#) [CFM150M480](#)