

## Voltage Detector with Delay Circuit Built-In

### GENERAL DESCRIPTION

The XC61H series is a highly accurate, low power consumption CMOS voltage detector with a delay circuit. Detect voltage is accurate with minimal temperature drift. Output configurations are available in both CMOS and N-channel open drain. Since the full delay circuit is built-in, an external delay-time capacitor is not necessary so that high density mounting is possible.


### APPLICATIONS

- Microprocessor reset circuitry
- System battery life and charge voltage monitors
- Memory battery back-up circuits
- Power-on reset circuits
- Power failure detection
- Delay circuitry

### FEATURES


- Detect Voltage Accuracy** :  $\pm 2\%$
- Low Power Consumption** :  $1.0 \mu\text{A (TYP.)}$  [  $V_{\text{IN}}=2.0\text{V}$  ]
- Detect Voltage Range** :  $1.6\text{V} \sim 6.0\text{V}$  (0.1V increments)
- Operating Voltage Range** :  $0.7\text{V} \sim 10.0\text{V}$
- Detect Voltage Temperature Characteristics** :  $\pm 100\text{ppm/}^\circ\text{C}$  (TYP.)
- Built-In Release Delay time**: 1ms (MIN.)  
50ms (MIN.)  
80ms (MIN.)
- Output Configuration** : N-ch open drain output or CMOS
- Operating Ambient Temperature** :  $30 \sim +80$
- Package** : SOT-23
- Environmentally Friendly** : EU RoHS Compliant, Pb Free

### TYPICAL APPLICATION CIRCUITS




### TYPICAL PERFORMANCE CHARACTERISTICS

Release Delay Time ( $t_{\text{DR}}$ ) vs. Ambient Temperature



## PIN CONFIGURATION



## PIN ASSIGNMENT

PIN NUMBER	PIN NAME	FUNCTION
SOT-23		
1	V <sub>SS</sub>	Ground
2	RESETB	Output
3	V <sub>IN</sub>	Supply Voltage Input

## PRODUCT CLASSIFICATION

### Ordering Information

XC61H \_\_\_\_\_ (\*1)


DESIGNATOR	ITEM	SYMBOL	DESCRIPTION
	Output Configuration	C	CMOS output
		N	N-ch open drain output
	Detect Voltage (V <sub>DF</sub> )	16 ~ 60	e.g. 2.5V    2 ,    5
	Release Delay Time	1	50ms ~ 200ms
		4	80ms ~ 400ms
		5	1ms ~ 50ms
	Detect Accuracy	2	± 2.0% (*2)
- (*1)	Package (Order Unit)	MR-G	SOT-23 (3000/Reel)

(\*1) The "-G" suffix indicates that the products are Halogen and Antimony free as well as being fully RoHS compliant.


(\*2) No parts are available with an accuracy of ± 1%

## BLOCK DIAGRAMS

(1)CMOS output



(2)N-ch open drain output



## ABSOLUTE MAXIMUM RATINGS

Ta=25

PARAMETER	SYMBOL	RATINGS	UNITS
Input Voltage	$V_{IN}$	$V_{SS} - 0.3 \sim 12.0$	V
Output Current	$I_{OUT}$	50	mA
Output Voltage	CMOS	$V_{RESETB}$	V
	N-ch open drain output		
Power Dissipation	SOT-23	$V_{SS} - 0.3 \sim V_{IN} + 0.3$ $V_{SS} - 0.3 \sim 12$	mW
Operating Ambient Temperature	$T_{opr}$	-30 ~ +80	
Storage Temperature	$T_{stg}$	-40 ~ +125	

## ELECTRICAL CHARACTERISTICS

Ta = 25

PARAMETER		SYMBOL	CONDITIONS	MIN.	TYP.	MAX.	UNITS	CIRCUIT	
Detect Voltage		V <sub>DF</sub>		V <sub>DF(T)</sub> x 0.98	V <sub>DF(T)</sub>	V <sub>DF(T)</sub> x 1.02	V		
Hysteresis Width		V <sub>HYS</sub>		V <sub>DF</sub> x 0.02	V <sub>DF</sub> x 0.05	V <sub>DF</sub> x 0.08	V		
Supply Current <sup>(*1)</sup>		I <sub>SS</sub>	V <sub>IN</sub> = 1.5V	-	0.9	2.6	μ A		
			V <sub>IN</sub> = 2.0V	-	1.0	3.0			
			V <sub>IN</sub> = 3.0V	-	1.3	3.4			
			V <sub>IN</sub> = 4.0V	-	1.6	3.8			
			V <sub>IN</sub> = 5.0V	-	2.0	4.2			
Operating Voltage		V <sub>IN</sub>	V <sub>DF</sub> =1.6V ~ 6.0V	0.7	-	10.0	V		
Output Current		I <sub>OUT</sub>	N-ch, V <sub>DS</sub> = 0.5V	V <sub>IN</sub> = 1.0V	1.0	2.2	-	mA	
				V <sub>IN</sub> = 2.0V	3.0	7.7	-		
				V <sub>IN</sub> = 3.0V	5.0	10.1	-		
				V <sub>IN</sub> = 4.0V	6.0	11.5	-		
				V <sub>IN</sub> = 5.0V	7.0	13.0	-		
			P-ch, V <sub>DS</sub> =2.1V (CMOS Output)	V <sub>IN</sub> = 8.0V		-10.0	-2.0		
Leakage Current	CMOS Output (Pch)	I <sub>LEAK</sub>	V <sub>IN</sub> =V <sub>DF</sub> x 0.9V, V <sub>RESETB</sub> =0V		-	-0.01	-	μ A	
	Nch Open Drain Output		V <sub>IN</sub> =10.0V, V <sub>RESETB</sub> =10.0V		-	0.01	0.1		
Detect Voltage Temperature Characteristics		V <sub>DF</sub> / ( T <sub>opr</sub> • V <sub>DF</sub> )	-30 T <sub>opr</sub> 80		-	±100	-	ppm/	
Release Delay Time (V <sub>DR</sub> RESETB inversion)		t <sub>DR</sub>	V <sub>IN</sub> changes from 0.6V to 10V		50	-	200	ms	
					80	-	400		
					1	-	50		

 $V_{DF(T)}$  is nominal detect voltage valueRelease Voltage:  $V_{DR} = V_{DF} + V_{HYS}$ 

(\*1) The supply current during power-start until output being stable (during release operation) is 2  $\mu A$  greater with comparison to the period after the completion of release operation because of the shoot-through current in delay current.

## OPERATIONAL EXPLANATION

### CMOS output

An input voltage  $V_{IN}$  starts higher than the release voltage  $V_{DR}$ . Then,  $V_{IN}$  voltage will gradually fall. When  $V_{IN}$  voltage is higher than detect voltage  $V_{DF}$ , output voltage RESETB is equal to the  $V_{IN}$  voltage.

\*Note that high impedance exists at RESETB with the N-channel open drain output configuration. If the RESETB pin is pulled up, RESETB will be equal to the pull up voltage.

When  $V_{IN}$  falls below  $V_{DF}$ , RESETB will be equal to ground voltage  $V_{SS}$  level (detect state).

\* Note that this also applies to N-channel open drain output configurations.

When  $V_{IN}$  falls to a level below that of the minimum operating voltage  $V_{MIN}$ , output will become unstable.

\*When the output pin is generally pulled up with N-channel open drain output configurations, output will be equal to pull up voltage.

When  $V_{IN}$  rises above the  $V_{SS}$  level (excepting levels lower than minimum operating voltage), RESETB will be equal to  $V_{SS}$  until  $V_{IN}$  reaches the  $V_{DR}$  level.

Although  $V_{IN}$  will rise to a level higher than  $V_{DR}$ , RESETB maintains ground voltage level via the delay circuit.


After taking a release delay time,  $V_{IN}$  voltage will be output at the RESETB pin.

\*High impedance exists with the N-channel open drain output configuration and that voltage will be dependent on pull up.

#### Notes:

1. The difference between  $V_{DR}$  and  $V_{DF}$  represents the hysteresis width.
2. Release delay time ( $t_{DR}$ ) represents the time it takes until when  $V_{IN}$  voltage appears at RESETB pin once the input voltage has exceeded the  $V_{DR}$  level.

### Timing Chart



## NOTES ON USE

1. Please use this IC within the stated maximum ratings. For temporary, transitional voltage drop or voltage rising phenomenon, the IC is liable to malfunction should the ratings be exceeded.
2. When a resistor is connected between the  $V_{IN}$  pin and the power supply with CMOS output configurations, irregular oscillation may occur as a result of voltage drops at  $R_{IN}$  if load current ( $I_{OUT}$ ) exists. It is therefore recommend that no resistor be added. (refer to Figure 1 below)
3. When a resistor ( $R_{IN}$ ) is connected between the  $V_{IN}$  pin and the power supply with CMOS output configurations, irrespective of N-ch open drain output configurations, oscillation may occur as a result of shoot-through current at the time of voltage release even if load current ( $I_{OUT}$ ) does not exist. (refer to Figure 2 below)
4. If a resistor ( $R_{IN}$ ) must be used, then please use with as small a level of input impedance as possible in order to control the occurrences of oscillation as described above. Further, please ensure that  $R_{IN}$  is less than 10k $\Omega$  and that  $C_{IN}$  is more than 0.1  $\mu$ F, please test with the actual device. However, N-ch open drain output only. (Figure 1).
5. With a resistor  $R_{IN}$  connected between the  $V_{IN}$  pin and the power supply, the  $V_{IN}$  pin voltage will be getting lower than the power supply voltage as a result of the IC's supply current flowing through the  $V_{IN}$  pin.
6. Depending on circuit's operation, release delay time of this IC can be widely changed due to upper limits or lower limits of operational ambient temperature.
7. Torex places an importance on improving our products and its reliability.  
However, by any possibility, we would request user fail-safe design and post-aging treatment on system or equipment.

### Irregular Oscillations

- (1) Irregular oscillation as a result of load current with the CMOS output configuration:

When the voltage applied at power supply, release operations commence and the detector's output voltage increases. Load current ( $I_{OUT}$ ) will flow through  $R_L$ . Because a voltage drop ( $R_{IN} \times I_{OUT}$ ) is produced at the  $R_{IN}$  resistor, located between the power supply and the  $V_{IN}$  pin, the load current will flow via the IC's  $V_{IN}$  pin. The voltage drop will also lead to a fall in the voltage level at the  $V_{IN}$  pin. When the  $V_{IN}$  pin voltage level falls below the detect voltage level, detect operations will commence. Following detect operations, load current flow will cease and since voltage drop at  $R_{IN}$  will disappear, the voltage level at the  $V_{IN}$  pin will rise and release operations will begin over again.

Irregular oscillation may occur with this "release - detect - release" repetition.

Further, this condition will also appear via means of a similar mechanism during detect operations.

- (2) Irregular oscillation as a result of shoot-through current:

Since the XC61H series are CMOS ICs, shoot-through current will flow when the IC's internal circuit switching operates (during release and detect operations). Consequently, irregular oscillation is liable to occur during release voltage operations as a result of output current which is influenced by this shoot-through current (Figure 3).

Since hysteresis exists during detect operations, irregular oscillation is unlikely to occur.




Figure 1 Use of input resistor  $R_{IN}$

## NOTES ON USE (Continued)

### Irregular Oscillations (Continued)




Figure 2 Irregular Oscillation by output current






Figure 3 Irregular Oscillation by shoot-through current

## TEST CIRCUITS


Circuit




Circuit




Circuit



Circuit






Circuit






\*R is not necessary with CMOS output products.

## TYPICAL PERFORMANCE CHARACTERISTICS




(1) Supply Current vs. Input Voltage






(2) Detect Voltage, Release Voltage vs. Ambient Temperature



(3) Detect Voltage, Release Voltage vs. Input Voltage




(4) N-Channel Driver Output Current vs. V\_DS






## TYPICAL PERFORMANCE CHARACTERISTICS (Continued)


(4) N-Channel Driver Output Current vs.  $V_{DS}$  (Continued)




(5) N-Channel Driver Output Current vs. Input Voltage



(6) P-Channel Driver Output Current vs. Input Voltage




(7) Ambient Temperature vs. Release Delay Time ( $t_{DR}$ )



## TYPICAL PERFORMANCE CHARACTERISTICS (Continued)

( 8 ) Input Voltage vs. Release Delay Time ( $t_{DR}$ )


**XC61HC2712**



## PACKAGING INFORMATION


### SOT-23

(unit : mm)



## MARKING RULE

SOT-23



SOT-23  
(TOP VIEW)

represents product series

MARK	PRODUCTS SERIES
8	XC61H*****-G

standard : represents output configuration and integer number of detect voltage

CMOS output (XC61HC series)

MARK	VOLTAGE (V)
A	1. X
B	2. X
C	3. X
D	4. X
E	5. X
F	6. X

N-channel open drain (XC61HN series)

MARK	VOLTAGE (V)
P	1. X
R	2. X
S	3. X
T	4. X
U	5. X
V	6. X

represents decimal number of detect voltage and delay time.

DETECT VOLTAGE (V)	MARK		
	DELAY TIME 50ms~200ms (XC61H***1***-G)	DELAY TIME 80ms~400ms (XC61H***4***-G)	DELAY TIME 1ms~50ms (XC61H***5***-G)
X.0	0	A	N
X.1	1	B	P
X.2	2	C	R
X.3	3	D	S
X.4	4	E	T
X.5	5	F	U
X.6	6	H	V
X.7	7	K	X
X.8	8	L	Y
X.9	9	M	Z

represents production lot number

0 to 9, A to Z or inverted characters of 0 to 9, A to Z repeated.

(G, I, J, O, Q, W excluded)

\*No character inversion used.

1. The products and product specifications contained herein are subject to change without notice to improve performance characteristics. Consult us, or our representatives before use, to confirm that the information in this datasheet is up to date.
2. We assume no responsibility for any infringement of patents, patent rights, or other rights arising from the use of any information and circuitry in this datasheet.
3. Please ensure suitable shipping controls (including fail-safe designs and aging protection) are in force for equipment employing products listed in this datasheet.
4. The products in this datasheet are not developed, designed, or approved for use with such equipment whose failure or malfunction can be reasonably expected to directly endanger the life of, or cause significant injury to, the user.  
(e.g. Atomic energy; aerospace; transport; combustion and associated safety equipment thereof.)
5. Please use the products listed in this datasheet within the specified ranges.  
Should you wish to use the products under conditions exceeding the specifications, please consult us or our representatives.
6. We assume no responsibility for damage or loss due to abnormal use.
7. All rights reserved. No part of this datasheet may be copied or reproduced without the prior permission of TOREX SEMICONDUCTOR LTD.

**TOREX SEMICONDUCTOR LTD.**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Torex Semiconductor:

[XC61HC2752MR-G](#) [XC61HC3242MR-G](#) [XC61HC2342MR-G](#) [XC61HC4442MR-G](#) [XC61HC2942MR-G](#)  
[XC61HC4642MR-G](#) [XC61HC2642MR-G](#) [XC61HC4252MR-G](#) [XC61HC1942MR-G](#) [XC61HC3142MR-G](#)  
[XC61HC2442MR-G](#) [XC61HC2742MR-G](#) [XC61HC3042MR-G](#) [XC61HC4552MR-G](#) [XC61HC3542MR-G](#)