ETR0412-005

Low Power Consumption Hall IC (Magnetic Sensor)

■GENERAL DESCRIPTION

The XC3202 series is a Hall effect magnetic sensor IC with a built-in CMOS output driver. The device features low power consumption and small packaging which is ideally suited for battery powered portable applications such as mobile phones, electronic dictionaries and handheld game consoles. When the magnetic flux density (Omnipolar) is larger than the operating magnetic flux density (Bop), the CMOS output driver will be turned on (Detect Low). The output driver will be turned off (Release High) when the output is lower than the release magnetic flux density (Brp).

APPLICATIONS

- •Cover detector, Home security systems
- Mobile phones
- Electronic dictionaries
- Portable game consoles
- Home electronics (refrigerators, washing machines etc)

FEATURES

Supply Voltage Range	: 2.4~5.5V			
Average Supply Current	:8 µ A			
Operating Magnetic Flux Density	: South Pole	3mT(TYP.)		
	North Pole	-3mT(TYP.)		
Release Magnetic Flux Density	: South Pole	2mT(TYP.)		
	North Pole	-2mT(TYP.)		
Hysteresis Width	: South Pole	1mT(TYP.)		
	North Pole	1mT(TYP.)		
Packages	: SOT-23D			
	QFN-0601 (un	der development		
Environmentally Friendly	: EU RoHS Compliant, Pb Free			

TYPICAL APPLICATION CIRCUIT

TYPICAL PERFORMANCE CHARACTERISTICS

Supply Current (avg) vs. Ambient Temperature



XC3202A183



*C is a capacitor for noise reduction and input voltage stability. The recommended value is 10nF~100nF

■ PIN CONFIGURATION





QFN-0601 (BOTTOM VIEW)

* QFN-0601 is under development.

PIN ASSIGNMENT

PIN N	UMBER		FUNCTION
SOT-23D	QFN-0601	PIN NAME	FUNCTION
1	1	V _{DD}	Power Input
2	3	V _{OUT}	Output Pin
3	5	V _{SS}	Ground
-	2,4,6	NC	No Connection

* QFN-0601 is under development.

■PRODUCT CLASSIFICATION

•Ordering Information

XC3202123456-7

DESIGNATOR	DESCRIPTION	SYMBOL	DESCRIPTION
1	Product Type	А	CMOS Output
234	Product No.	183	Based on the internal standard
Packages		MR-G	SOT-23D (Halogen & Antimony free)
(5)(6)-(7)	Taping Type ^(*2)	ZR-G	QFN-0601 (Halogen & Antimony free) (under development)

* QFN-0601 is under development.

^(*1) The "-G" suffix indicates that the products are Halogen and Antimony free as well as being fully RoHS compliant.

^('2) The device orientation is fixed in its embossed tape pocket. For reverse orientation, please contact your local Torex sales office or representative. (Standard orientation: (SR-⑦, Reverse orientation: (SL-⑦))

■BLOCK DIAGRAMS



■ABSOLUTE MAXIMUM RATINGS

PARAN	/IETER	SYMBOL	RATINGS	UNITS	
Supply Voltage		V _{DD}	7	V	
Magnetic F	lux Density	В	Unlimited	-	
Operating Temperature Range		Topr	-40~+85	°C	
Storage Temperature Range		Tstg	-55~+150	°C	
Power Dissipation SOT-23D QFN-0601		Dd	150	mW	
		Fu	under development		
Maximum Junction Temperature		Tjc	125	°C	
Maximum Output Current		IOUT	40	mA	

* This IC should be used within the stated absolute maximum ratings in order to prevent damage.

■OPERATING CONDITION

PARAMETER	SYMBOL	CONDITONS	RATINGS	UNITS	CIRCUIT
Supply Voltage	V _{DD}	Operating	2.4~5.5	V	-

■ELECTRICAL CHARACTERISTICS

						Ta=.	$25 C, V_{DD}=3V$
PARAMETER	SYMBOL	CONDITONS	TYP.	MAX.	UNITS	CIRCUIT	
On-state Output Voltage	V _{OUT}	I _{OUT} =1mA	-	0.1	0.3	V	3
	I _{DD} (en)		-	3	6	mA	2
Supply Current	I _{DD} (dis)		-	5	10	μA	1
	I _{DD} (avg)		-	8	16	μA	2
Detection Time	tawake		-	75	150	μs	٢
Detection Period	tperiod		-	75	150	ms	۷ ۷
Duty Cycle	DTY		-	0.1	-	%	2

Ta-25℃ \/ -31/

■MAGNETIC CHARACTERISTCS

Ta=25°C, V_{DD}=3V, 1mT=10Gauss

PARAMETER	SYMBOL	MIN.	TYP.	MAX.	UNITS	CIRCUIT
Operating Magnetic Flux Density: South Pole	Bops	2	3	4	mT	3
Operating Magnetic Flux Density: North Pole	Bopn	-4	-3	-2	mT	3
Release Magnetic Flux Density: South Pole	Brps	1	2	-	mT	3
Release Magnetic Flux Density: North Pole	Brpn	-	-2	-1	mT	3
Hysteresis Width	Bhy(Bop-Brp)	0.5	1	-	mT	3

OPERATIONAL

Operating by flux density



Timing chart



*1: When the magnetic flux density to the IC becomes larger than Bop, the IC goes into an on-state and outputs a low signal (V_{OUT}=Low) at the leading edge of the next "tawake" pulse.

*2: When the magnetic flux density to the IC becomes lower than Brp, the IC goes into an off-state and outputs a high signal (V_{OUT}=High) at the leading edge of the next "tawake" pulse.

During the other periods, the previous state is maintained.

■TEST CIRCUITS

 $\text{Circuit} \ \textcircled{1}$



Circuit (2)



OSC:Oscilloscope



■ PACKAGING INFORMATION

●SOT-23D





Position of sensor







●QFN-0601 (under development)





Position of sensor



MARKING RULE

SOT-23D / QFN-0601

① represents production number: standard / custom production

MARK	PRODUCT SERIES
2	XC3202*****

2 denotes production registered number: standard / custom production

1, ..., 9, A, ..., Z in order (G, I, J, O, Q, W are excluded)



QFN0601

*QFN-0601 is under development



③ represents the last 1 digit of the manufacturing year: standard / custom production

(e.g)	
MARK	YEAR
9	2009
0	2010

④ represents manufacturing month: standard / custom production

MARK	MANUFACTURING MONTH	MARK	MANUFACTURING MONTH	MARK	MANUFACTURING MONTH
А	January	E	Мау	J	September
В	February	F	June	К	October
С	March	G	July	L	November
D	April	Н	August	М	December

⑤ denotes production lot number

A, ..., Z, in order

(G, I, J, O, Q, W are excluded)

XC3202 Series

- 1. The products and product specifications contained herein are subject to change without notice to improve performance characteristics. Consult us, or our representatives before use, to confirm that the information in this datasheet is up to date.
- 2. We assume no responsibility for any infringement of patents, patent rights, or other rights arising from the use of any information and circuitry in this datasheet.
- 3. Please ensure suitable shipping controls (including fail-safe designs and aging protection) are in force for equipment employing products listed in this datasheet.
- 4. The products in this datasheet are not developed, designed, or approved for use with such equipment whose failure of malfunction can be reasonably expected to directly endanger the life of, or cause significant injury to, the user.

(e.g. Atomic energy; aerospace; transport; combustion and associated safety equipment thereof.)

- Please use the products listed in this datasheet within the specified ranges.
 Should you wish to use the products under conditions exceeding the specifications, please consult us or our representatives.
- 6. We assume no responsibility for damage or loss due to abnormal use.
- 7. All rights reserved. No part of this datasheet may be copied or reproduced without the prior permission of TOREX SEMICONDUCTOR LTD.

TOREX SEMICONDUCTOR LTD.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Torex Semiconductor: XC3202A183MR-G