



TPS-3162GT-M12X-BP1-MV

EN50155 18-port managed PoE Ethernet switch with 16x10/100Base-T(X) P.S.E. and 2x10/100/1000Base-T(X), M12 connector and 1xbypass included, 110VDC power input

Features

- Leading EN50155-compliant Ethernet switch for rolling stock application
- 16 ports P.S.E. fully compliant with IEEE802.3af standard, provide up to 15.4 Watts per port
- World's fastest Redundant Ethernet Ring: **O-Ring** (recovery time < 10ms over 250 units of connection)
- **O-Chain** support applications with multiple redundant rings topology
- Support standard IEC 62439-2 **MRP*NOTE** (Media Redundancy Protocol) function
- STP/RSTP/MSTP supported
- Support **PTP Client** (Precision Time Protocol) clock synchronization
- Support Modbus TCP protocol
- IGMP v2/v3 (IGMP snooping support) for filtering multicast traffic
- SNMP v1/v2c/v3 support for secured network management
- RMON for traffic monitoring
- Support VLAN and LLDP protocol
- DHCP assign each Equipment IP by each Port
- Provided Relay bypass function with two gigabit ports
- Event notification through Syslog, Email, SNMP trap, and Relay Output
- Windows utility (**Open-Vision**) support centralized management and configurable by Web-based, Telnet, and Console (CLI)
- M12 connectors to guarantee reliable operation against environmental disturbances
- Wall mounting enabled



Introduction

ORing's Transporter™ series managed Ethernet switches are designed for industrial applications, such as rolling stock, vehicle, and railway applications. The TPS-3162GT-M12X-BP1-MV is a managed PoE Redundant Ring Ethernet switch with 16x10/100Base-T(X) P.S.E. and 2x10/100/1000Base-T(X) ports which is specifically designed for the toughest and fully compliant with EN50155 requirement. With completely support of Ethernet Redundancy protocol, O-Ring (recovery time < 10ms over 250 units of connection), O-Chain and MSTP/RSTP/STP (IEEE 802.1s/w/D) can protect your mission-critical applications from network interruptions or temporary malfunctions with its fast recovery technology.

TPS-3162GT-M12X-BP1-MV also supports Power over Ethernet, a system to transmit electrical power, along with data, to remote devices over standard twisted-pair cable in an Ethernet network. Each TPS-3162GT-M12X-BP1-MV switch has 16X10/100Base-T(X) P.S.E. (Power Sourcing Equipment) ports. P.S.E. is a device (switch or hub for instance) that will provide power in a PoE setup. TPS-3162GT-M12X-BP1-MV EN50155 Ethernet switch use M12 connectors to ensure tight,

***NOTE: This function is available by request only.**

Open-Vision

[illegible]

The screenshot displays the Cisco Packet Tracer 'Topology View' for a 30-device network. The top menu bar includes 'General', 'Topology Management', and 'Map Management'. Below the menu is a toolbar with icons for 'Handbook', 'Pick', 'Edit', 'Zoom In', 'Zoom Out', 'Layout', 'Generation', 'Print', '192.168.1.1/24', 'Go', and 'Display'. The left sidebar, titled 'Device Tree', shows a tree structure with 'Global' at the top, followed by '192.168.2.4', '192.168.2.6', and the selected device '192.168.200.6'. The main workspace shows the 'Topology Map' with a circular network diagram. The bottom status bar displays the device's IP address '192.168.200.6' and the command 'show ipconfig'.

Dimension

The drawing shows the front and rear views of the ORing Transporter control panel. The front view includes a 4x4 grid of 16 push buttons labeled P1 through P16, a 'Relay Output' section with two indicator lights, a 'Console' section with a single indicator light, and a 'Power' section with a single indicator light. The rear view shows the panel's mounting holes and dimensions. Dimensions are given in millimeters (mm).



Dimensions:

- Overall width: 260.00 mm
- Overall height: 206.00 mm
- Panel width: 237.90 mm
- Panel height: 207.90 mm
- Mounting hole diameter: Ø5.0 mm
- Panel hole diameter: Ø11.05 mm
- Panel hole diameter: Ø5.0 mm

Components and Labels:

- ORing Transporter** (Main unit)
- Relay Output** (Two indicator lights)
- Console** (One indicator light)
- Power** (One indicator light)
- Buttons:** P1, P2, P3, P4, P5, P6, P7, P8, P9, P10, P11, P12, P13, P14, P15, P16
- Labels:** T1, T2, T3, T4, T5, T6, T7, T8, T9, T10, T11, T12, T13, T14, T15, T16
- Dimensions:** 260.00, 237.90, 207.90, 206.00, Ø5.0, Ø11.05, Ø5.0

Pin Definition

 D-Coding M12	10/100Base-T(X) P.S.E. M12 port		 X-Coding M12	10/100/1000Base-T(X) M12 port	
	Pin No.	Description		Pin No.	Description
	#1	Tx+ with PoE Vout+		#1	BI_DA+
	#2	Rx+ with PoE Vout-		#2	BI_DA-
	#3	Tx- with PoE Vout+		#3	BI_DB+
	#4	Rx- with PoE Vout-		#4	BI_DB-
	#5	N.C.		#5	BI_DD+
	#6	N.C.		#6	BI_DD-
	#7	N.C.		#7	BI_DC-
	#8	N.C.		#8	BI_DC+

Specifications

ORing Switch Model	TPS-3162GT-M12X-BP1-MV
Physical Ports	
10/100Base-T(X) Ports in M12 Auto MDI/MDIX with P.S.E.	16 x M12 connector (4-pin D-coding, female)
10/100/1000Base-T(X) ports in M12	2 x M12 connectors (8-pin X-coding, female)
RS-232 Serial Console Port	RS-232 in M12 connector (5-pin A-coding, female). Baud rate setting: 9600bps, 8, N, 1
Technology	
Ethernet Standards	IEEE 802.3 for 10Base-T IEEE 802.3u for 100Base-TX IEEE 802.3ab for 1000Base-T IEEE 802.3x for Flow control IEEE 802.3ad for LACP (Link Aggregation Control Protocol) IEEE 802.1D for STP (Spanning Tree Protocol) IEEE 802.1p for COS (Class of Service) IEEE 802.1Q for VLAN Tagging IEEE 802.1w for RSTP (Rapid Spanning Tree Protocol) IEEE 802.1s for MSTP (Multiple Spanning Tree Protocol) IEEE 802.1x for Authentication IEEE 802.1AB for LLDP (Link Layer Discovery Protocol) IEEE 802.3af PoE specification (up to 15.4 Watts per port for P.S.E.)
MAC Table	8192 MAC addresses
Priority Queues	4
Processing	Store-and-Forward
Switch Properties	Switching latency: 7 us Switching bandwidth: 7.2Gbps Max. Number of Available VLANs: 4096 IGMP multicast groups: 1024 Port rate limiting: User Define
Security Features	Enable/disable ports, MAC based port security Port based network access control (802.1x) VLAN (802.1Q) to segregate and secure network traffic Supports Q-in-Q VLAN for performance & security to expand the VLAN space Radius centralized password management SNMP v1/v2c/v3 encrypted authentication and access security


Software Features	STP/RSTP/MSTP (IEEE 802.1D/w/s) Redundant Ring (O-Ring) with recovery time less than 10ms over 250 units TOS/Diffserv supported Quality of Service (802.1p) for real-time traffic VLAN (802.1Q) with VLAN tagging and GVRP supported IGMP Snooping for multicast filtering Port configuration, status, statistics, monitoring, security NTP for synchronizing of clocks over network Support PTP Client (Precision Time Protocol) clock synchronization DHCP Server / Client support Port Trunk support MVR (Multicast VLAN Registration) support Modbus TCP
Network Redundancy	O-Ring O-Chain MRP* NOTE STP RSTP MSTP
Warning / Monitoring System	Relay output for fault event alarming Syslog server / client to record and view events Include SMTP for event warning notification via email Event selection support
LED Indicators	
Power Indicator	Green: Power LED x 1
R.M. Indicator	Green: Indicate system operated in O-Ring Master mode
O-Ring Indicator	Green: Indicate system operated in O-Ring mode
Fault Indicator	Amber: Indicate unexpected event occurred
10/100Base-T(X) M12 P.S.E. Port Indicator	Top Green LED for Link/Act indicator Middle Green LED for PoE enabled indicator Bottom Amber LED for Collision/Duplex indicator
10/100/1000Base-T(X) M12 Port Indicator	Top Green LED for Link/Act indicator Bottom Green LED for 100Mbps indicator
Fault contact	
Relay	Relay output to carry capacity of 3A at 24VDC on M12 connector (5-pin A-coding, female)
Power	
Redundant Input Power	72/110 (50.4-137.5) VDC. 7/8 inch 5-pin male connector
Power Consumption (Typ.)	28 watts (PoE output not included)
Total PoE budget	95 watts
Overload Current Protection	Present
Reverse Polarity Protection	Present
Physical Characteristic	
Enclosure	IP-30
Dimension (W x D x H)	260 (W) x 79.3 (D) x 222 (H) mm
Weight (g)	2850 g
Environmental	
Storage Temperature	-40 to 85°C (-40 to 185°F)
Operating Temperature	-40 to 75°C (-40 to 167°F)
Operating Humidity	5% to 95% Non-condensing
Regulatory approvals	
EMC	CE EMC (EN 55024, EN 55032), FCC Part 15 B, EN 50121-3-2(EN 50155)
EMI	EN 55032, CISPR32, EN 61000-3-2, EN 61000-3-3, FCC Part 15 B class A
EMS	EN 55024 (IEC/EN 61000-4-2 (ESD), IEC/EN 61000-4-3 (RS), IEC/EN 61000-4-4 (EFT), IEC/EN 61000-4-5 (Surge), IEC/EN 61000-4-6 (CS), IEC/EN 61000-4-8(PFMF), IEC/EN 61000-4-11 (DIP))
Shock	IEC60068-2-27
Free Fall	IEC60068-2-31
Vibration	IEC60068-2-6

*NOTE: This function is available by request only.

Safety	EN60950-1
Other	EN 50155
MTBF	261,222 hours
Warranty	5 years

Ordering Information

TPS-3AABCC-M12-DDD



Code	10/100Base-T(X) P.S.E. Port Definition Number	Additional Port Number	Additional Port Type	Bypass Function
Option	- 16: 16 ports	- 2: 2 ports	- GT: 10/100/1000Base-T(X) port	- BP1: 1xbypass function included

Available Model	Model Name	Description
	TPS-3162GT-M12X-BP1-MV	EN50155 18-port managed PoE Ethernet switch with 16x10/100Base-T(X) P.S.E. and 2x10/100/1000Base-T(X), M12 connector and 1xbypass included, 110VDC power input

Packing List

- **TPS-3162GT-M12X-BP1-MV x 1**
- **ORing Tool CD x 1**
- **Quick Installation Guide x 1**

Optional Accessories

- **Open-Vision M500: Powerful Network Management Windows utility Suit, 500 IP devices**
- **M12C: M12 cable accessories**

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

ORing:

[TPS-3162GT-M12X-BP1-MV](#)