

EBC-3000

Mini-ITX Chassis for High Power Consumption Applications




Features

- Designed for high performance applications, bundled with 270W high efficiency ATX power supply
- Front accessible I/O design
- One 3.5" hard drive capacity

Specifications

Model Name		EBC-3000
Platform		Case only
Chassis	Color	Black
	Dimensions (WxDxH) (mm)	280 x 230 x 88
	System Fan (WxDxH) (mm)	60 x 60 x 25
	Chassis Construction	Heavy duty metal with plastic front panel
Motherboard	Motherboard Model	Refer to KINO Series
	SBC Size (mm)	Mini-ITX (170 x 170)
Storage	Hard Drive	1 x 3.5" SATA HDD space
Power	Power Input	90 V~264 V AC
	Power Model	ACE-A618C 180W, ACE-A627A 270W
Reliability	Mounting	Desktop, wall mount
	Operating Temperature	0°C ~ 50°C
	Weight (Net/Gross)	2.5 kg/3.9 kg

Dimensions (Unit: mm)



Compatible SBC

Part No.	Recommended CPU Cooler
KINO-AQ170	CF-115XA-R10, CF-115XC-R10, CF-115XD-R10
KINO-ABT	Fanless
KINO-AA750-i2	CF-989B-RS
KINO-AQ870	CF-1150SC-RS
KINO-AQ670	CF-115XA-R10, CF-115XC-R10, CF-115XD-R10
KINO-AH611	CF-115XA-R10, CF-115XC-R10, CF-115XD-R10
KINO-AH612	CF-115XA-R10, CF-115XC-R10, CF-115XD-R10

1U AC Input									
Products	Model No.	Watt AT/ATX PFC	Input Voltage	Output Current Range					Efficiency
				+3.3 V	+5 V	+12 V	-12 V	+5 Vsb	
	ACE-A630C	300W ATX	90~265 VAC	16A (0.5A min.)	15A (0.5A min.)	0.5A	0.8A	3A	82%
	ACE-A618C	180W ATX	90~264 VAC	10A (0.1A min.)	14A (0.2A min.)	10A (0.6A min.)	0.3A	2.5A	85%

Ordering Information

Part No.	Description
EBC-3000-R12/ACE-A618C	Mini-ITX embedded chassis, one 3.5" hard drive bay, with ACE-A618C-RS 180W ATX power supply, black
EBC-3000-R12/ACE-A630C	Mini-ITX embedded chassis, one 3.5" hard drive bay, with ACE-A630C-RS 300W ATX power supply, black

Packing List

1 x System fan	1 x Screw set	1 x QIG
1 x Power cord	1 x Wall mount kit	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

IEI:

[EBC-3000-R12/ACE-A618C](#) [EBC-3000-R12/ACE-A630C](#)