




# gKINO-V1000-R1000

Mini-ITX SBC supports AMD® Ryzen™ Embedded V1000/R1000 Series on board SoC, DDR4, quadruple independent displays, dual GbE, SATA 6Gb/s, USB 3.2, M.2, COM, TPM 2.0, HD audio and RoHS



## Specifications


- ◆ CPU
  - AMD® Ryzen™ Embedded V1605B, Quad Core, 2MB Cache, 8 CU, 2.0GHz (3.6GHz), 12-25W
  - AMD® Ryzen™ Embedded V1202B, Dual Core, 1MB Cache, 3 CU, 2.3GHz (3.2GHz), 12-25W
  - AMD® Ryzen™ Embedded R1606G, Dual Core, 1MB Cache, 3 CU, 2.6GHz (3.5GHz), 12-25W
  - AMD® Ryzen™ Embedded R1505G, Dual Core, 1MB Cache, 3 CU, 2.4GHz (3.3GHz), 12-25W
- ◆ BIOS: AMI BIOS
- ◆ Memory: 2 x SO-DIMM DDR4 2400MHz up to 64GB (ECC support)
- ◆ Graphic
  - AMD Radeon™ VEGA GPU with up to 8 Compute Units
  - H.2651 (10-bit) Decode and (8-bit) Encode support, VP9 (10-bit) Decode integrated
- ◆ Display Output
  - 4 x DP (gKINO-V1000): 4 x 4K UHD 3840x2160
  - 3 x DP (gKINO-R1000): 3 x 4K UHD 3840x2160
- ◆ Ethernet: 2 x GbE LAN (RTL 81191)
- ◆ External I/O Interfaces
  - 2 x RS-232
  - 2 x USB 2.0
  - 2 x USB 3.2 Gen1 (5Gb/s)
- ◆ Internal I/O Interfaces
  - 1 x SATA 3.0 (6Gb/s) with 5/12V SATA power connector
  - 2 x RS-232 (support Cctalk, TTL)(1x4 pin, P=2.54)
  - 2 x USB 2.0 (2x4 pin, P=2.0)
  - 4 x RS-232 (2x5 pin, P=2.00)
- ◆ Audio
  - Realtek ALC662 HD audio codec
  - 2 x 6W audio amplifier L+R
  - 2 x Audio jacks (line-out, mic-in) on rear IO
  - 1 x Front audio (2x5-pin)
  - 1 x Onboard SPDIF output
- ◆ Front Panel
  - 1 x Front panel connector (2x7 pin, power LED, HDD LED, speaker, power button, reset button)
- ◆ LAN LED: 2 x LAN LED (1x2 pin)
- ◆ TPM: 1 x TPM 2.0 connector (2x10 pin) (LPC interface)
- ◆ SMBUS: 1 x SMBus (1x4 pin)
- ◆ I<sup>2</sup>C: 1 x I<sup>2</sup>C (1x4 pin)
- ◆ Digital I/O: 8-bit digital I/O (2x5 pin)
- ◆ Expansion
  - 1 x PCIe x16 slot (with x8 Gen 3.0 signal)
  - 1 x M.2 2242/2280 M key (PCIe x2/SATA)
- ◆ Watchdog Timer: Software programmable support 1~255 sec. system reset by super I/O
- ◆ Chassis Open: 1 x Intrusion pin (1x2 pin)
- ◆ Power Supply
  - 12V DC input
  - 1 x External DC jack (4-pin DIN)
  - 1 x Internal power connector (2x2 pin)
  - Support AT/ATX mode
- ◆ Fan Connector
  - 1 x CPU smart (1x4 pin)
  - 1 x System fan (1x4 pin)
- ◆ Power Consumption
  - 12V@5.144A (AMD Ryzen V1605B 2.0GHz CPU with 2666 MHz 32GB DDR4 memory)
  - 12V@5.146A (AMD Ryzen R1606G 2.6GHz CPU with 2666 MHz 32GB DDR4 memory)
- ◆ Storage Temperature: -10°C ~ 70°C
- ◆ Operating temperature: 0°C ~ 60°C
- ◆ Operating Humidity: 5% ~ 95%, non-condensing
- ◆ Weight: GW:900g / NW:400g
- ◆ Dimensions: 170mm x 170mm
- ◆ CE/FCC compliant



## Features

- ◆ Mini ITX form factor with AMD® Ryzen™ Embedded processor supports dual-channel ECC DDR4 SO-DIMMs
- ◆ Maximum up to quadruple DisplayPort output for multi-display support
- ◆ M.2 slot support SATA or PCIe (2242/2280) & PCIe x16 slot support
- ◆ Chassis intrusion detect pin and ECC support in gaming applications
- ◆ COM RS-232 support Cctalk, TTL
- ◆ TPM 2.0 hardware security function supported by TPM module

## Dimensions (Unit: mm)



## Packing List

|                                                  |                |
|--------------------------------------------------|----------------|
| 1 x gKINO-V1000/R1000 series SBC with CPU cooler | 1 x SATA cable |
| 1 x I/O shielding                                | 1 x QIG        |

## Ordering Information

| Part No.            | Description                                                                                                                                                                                                      |
|---------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| gKINO-V1605B-R10    | Mini-ITX SBC supports AMD® Ryzen™ Embedded V1605B on board SoC (quad-core 2.0GHz, 15W) , DDR4, quadruple independent displays, quadruple DP, dual GbE, SATA 6Gb/s, USB 3.2, M.2, COM, TPM 2.0, HD audio and RoHS |
| gKINO-V1202B-R10    | Mini-ITX SBC supports AMD® Ryzen™ Embedded V1202B on board SoC (dual-core 2.3GHz, 15W) , DDR4, quadruple independent displays, quadruple DP, dual GbE, SATA 6Gb/s, USB 3.2, M.2, COM, TPM 2.0, HD audio and RoHS |
| gKINO-R1606G-R10    | Mini-ITX SBC supports AMD® Ryzen™ Embedded R1606G on board SoC (dual-core 2.6GHz, 15W) , DDR4, triple independent displays, triple DP, dual GbE, SATA 6Gb/s, USB 3.2, M.2, COM, TPM 2.0, HD audio and RoHS       |
| gKINO-R1505G-R10    | Mini-ITX SBC supports AMD® Ryzen™ Embedded R1505G on board SoC (dual-core 2.4GHz, 15W) , DDR4, triple independent displays, triple DP, dual GbE, SATA 6Gb/s, USB 3.2, M.2, COM, TPM 2.0, HD audio and RoHS       |
| 19800-000300-100-RS | RS-232 cable with bracket, 300mm, P=2.0                                                                                                                                                                          |
| CB-USB02A-RS        | Dual-port USB cable with bracket, 300mm, P=2.0                                                                                                                                                                   |
| TPM-IN02-R20        | 20-pin Infineon TPM 2.0 module, software management tool, firmware v5.5                                                                                                                                          |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

IEI:

[gKINO-R1505G-R10](#) [gKINO-R1606G-R10](#) [gKINO-V1202B-R10](#) [gKINO-V1605B-R10](#)