

LOCTITE ABLESTIK ABP 8420

January 2020

PRODUCT DESCRIPTION

LOCTITE ABLESTIK ABP 8420 provides the following product characteristics:

Technology	Epoxy
Appearance	Black
Cure	Heat cure
Product Benefits	• Non-conductive • Excellent resin bleed out (RBO) performance • Fast cure • Black pigmentation for blocking stray light • Good adhesion to PA substrates • Good reliability performance
Application	Die attach
Key Substrates	Most plastics and Glass
Typical Applications	Cap, diffuser attach in wirebond packages

LOCTITE ABLESTIK ABP 8420 non-conductive adhesive is designed for cap and lid attach applications in wirebond packages. This adhesive can be fast cured using directed heat energy or hot plate curing techniques. LOCTITE ABLESTIK ABP 8420 will cure at temperatures as low as 80°C in conventional box or convection conveyor oven curing.

If used over an active die face, an adhesive bondline thickness of >1 mil must be maintained to prevent die scarring.

TYPICAL PROPERTIES OF UNCURED MATERIAL

Thixotropic Index (0.5/5 rpm)	5.8
Viscosity, Brookfield CP51, 25 °C, mPa·s (cP):	
Speed 5 rpm	13,500
Work Life @ 25°C, hours	24
Shelf Life @ -20°C (from date of manufacture), days	180

TYPICAL CURING PERFORMANCE

Weight Loss on Cure

Weight Loss on Cure, %	0.5
------------------------	-----

Cure Schedule

30 minutes ramp to 150°C, hold 15 minutes @ 150 °C

Alternate Cure Schedule 1

30 minutes @ 100°C or
120 minutes @ 80°C

Alternate Cure Schedule 2

60 minutes @ 120°C

The above cure profiles are guideline recommendations. Cure conditions (time and temperature) may vary based on customers' experience and their application requirements, as well as customer curing equipment, oven loading and actual oven temperatures.

TYPICAL PROPERTIES OF CURED MATERIAL

Physical Properties

Glass Transition Temperature (Tg) by TMA, °C	75
Coefficient of Thermal Expansion, :	
Below Tg, ppm/°C	54
Above Tg, ppm/°C	154
Thermal Conductivity, W/(m·K)	0.3
Extractable Ionic Content, @ 100°C:	
Chloride (Cl-)	<120
Sodium (Na+)	<5
Potassium (K+)	<5
Water Extract Conductivity, µmhos/cm	147
Weight Loss, %	0.5
DMA Modulus :	
@ 25°C	N/mm ² 2,850 (psi) (413,357)
@ 100°C	N/mm ² 1,919 (psi) (278,327)
@ 150°C	N/mm ² 90 (psi) (13,053)
@ 250°C	N/mm ² 84 (psi) (12,183)

TYPICAL PERFORMANCE OF CURED MATERIAL

Sample cured 15 minutes @ 150°C

Miscellaneous

Die Shear Strength, kg-f	
1 x 1 mm Si die on glass	6
2 x 2 mm Si die:	
on GBA	15.5
on PA	12
on Cu LF	13
3 x 3 mm Glass die on PC	12

GENERAL INFORMATION

For safe handling information on this product, consult the Safety Data Sheet, (SDS).

STORAGE:

Store product in the unopened container in a dry location. Storage information may be indicated on the product container labeling.

Optimal Storage : -20 °C

Material removed from containers may be contaminated during use. Do not return product to the original container. Henkel Corporation cannot assume responsibility for product which has been contaminated or stored under conditions other than those previously indicated. If additional information is required, please contact your local Technical Service Center or Customer Service Representative.

Conversions

$(^{\circ}\text{C} \times 1.8) + 32 = ^{\circ}\text{F}$

$\text{kV/mm} \times 25.4 = \text{V/mil}$

$\text{mm} / 25.4 = \text{inches}$

$\text{N} \times 0.225 = \text{lb/F}$

$\text{N/mm} \times 5.71 = \text{lb/in}$

$\text{psi} \times 145 = \text{N/mm}^2$

$\text{MPa} = \text{N/mm}^2$

$\text{N} \cdot \text{m} \times 8.851 = \text{lb} \cdot \text{in}$

$\text{N} \cdot \text{m} \times 0.738 = \text{lb} \cdot \text{ft}$

$\text{N} \cdot \text{mm} \times 0.142 = \text{oz} \cdot \text{in}$

$\text{mPa} \cdot \text{s} = \text{cP}$

Disclaimer**Note:**

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. The product can have a variety of different applications as well as differing application and working conditions in your environment that are beyond our control. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product. Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

In case products are delivered by Henkel Belgium NV, Henkel Electronic Materials NV, Henkel Nederland BV, Henkel Technologies France SAS and Henkel France SA please additionally note the following:

In case Henkel would be nevertheless held liable, on whatever legal ground, Henkel's liability will in no event exceed the amount of the concerned delivery.

In case products are delivered by Henkel Colombiana, S.A.S. the following disclaimer is applicable:

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product.

Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

In case products are delivered by Henkel Corporation, Resin Technology Group, Inc., or Henkel Canada Corporation, the following disclaimer is applicable:

The data contained herein are furnished for information only and are believed to be reliable. We cannot assume responsibility for the results obtained by others over whose methods we have no control. It is the user's responsibility to determine suitability for the user's purpose of any production methods mentioned herein and to adopt such precautions as may be advisable for the protection of property and of persons against any hazards that may be involved in the handling and use thereof. In light of the foregoing, **Henkel Corporation specifically disclaims all warranties expressed or implied, including warranties of merchantability or fitness for a particular purpose, arising from sale or use of Henkel Corporation's products. Henkel Corporation specifically disclaims any liability for consequential or incidental damages of any kind, including lost profits.** The discussion herein of various processes or compositions is not to be interpreted as representation that they are free from domination of patents owned by others or as a license under any Henkel Corporation patents that may cover such processes or compositions. We recommend that each prospective user test his proposed application before repetitive use, using this data as a guide. This product may be covered by one or more United States or foreign patents or patent applications.

Trademark usage

Except as otherwise noted, all trademarks in this document are trademarks of Henkel Corporation in the U.S. and elsewhere. ® denotes a trademark registered in the U.S. Patent and Trademark Office.

Reference 3

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Loctite:](#)

[2237517](#)