

# LOCTITE ABLESTIK QMI3555R

September 2019

### PRODUCT DESCRIPTION

QMI 3555R is a low temperature processing, no dry, silver glass die attach adhesive for the attachment of integrated circuits in both solder seal and glass seal hermetic packages. It is designed for fast firing large die or small dies on either gold plated or bare ceramic substrates. The paste fires into a film that provides high thermal and electrical conductivity as well as excellent initial adhesion. It is extremely resistant to degradation during temperature cycling from -65°C to +150°C.

QMI 3555R incorporates a patented silver/vanadium glass. Sub-350°C firing enhances the reliability of devices fabricated with sub-micron design rules. Also, in cofired package applications, nickel diffusion through gold plated seal rings and leadfinger pads are minimized at lower temperatures. QMI3555R low stress allows for a thin bondline, offering improved thermal performance for high power devices.

## TYPICAL PROPERTIES OF UNCURED MATERIAL

40,000
9.5
365
87
6.5:1

### TYPICAL CURING CONDITIONS

QMI 3555R can be fired at temperatures between 300°C and 450°C on bare ceramic. On gold plated parts, the minimum peak should be 325°C. The minimum dwell time should be at least 14 minutes above 300°C when the peak is <325°C. Higher peak temperatures require less dwell time. There should not be any rapid spikes in the ramp that would volatilize the solvents and create voids.

#### Firing Profile and Minimum Recommended Bondlines Firing must be in CDA (clean/dry/air)

Die Size (mils largest side)	Minimum Wet Bondline (mils)	Minimum Fired Bondline (mils)
200	2.5	2.1
300	3.0	2.3
400	3.5	2.7
500	4.0	3.1
600	4.5	3.5
700	5.0	3.9
800	5.5	4.3

Staging time(time after the die is placed and before the parts are fired)should be less than eight hours

# Maximum Ramp Rates in °C / Minute

Temp	<200	<300	<400	<500	<600	<700	<800
40-120° C	<34	<28	<24	<20	<14	<8	<6
120-200 °C	<44	<38	<32	<28	<26	<22	<18
200-280 °C	<65	<60	<55	<50	<40	<34	<24
>280°C	<65	<65	<60	<50	<40	<40	<40

After firing, the parts should be stored in a low humidity(<30%)atmosphere before sealing to optimize RGA moisture

and adhesion.

# TYPICAL PROPERTIES OF CURED MATERIAL

# Physical Properties

Coefficient of Thermal Expansion, TMA, ppm alpha 1	/°C:	16
Glass Transition Temperature, °C		150
DMA Modulus @ 25°C	N/mm² (psi)	11,500 (1.67×10⁺ <sup>6</sup> )
Thermal Conductivity, W/(m-K)		>80
Extractable Ionic Content, :		
Sodium (Na+)		≤20
Potassium (K+)		≤20
Chloride (Cl-)		≤60
Fluoride (F-)		≤20
Package cavity headspace moisture concent Residual Glass Analysis (RGA), ppm H2 O	ration,	<2,000

## TYPICAL PERFORMANCE OF CURED MATERIAL

Miscellaneous	
Tensile Adhesion @ 25°C:	
0.6 x 0.6 inch Si die on ceramic, lb-f	≥350

## GENERAL INFORMATION

For safe handling information on this product, consult the Safety Data Sheet, (SDS).

#### Data Ranges

The data contained herein may be reported as a typical value and/or range values based on actual test data and are verified on a periodic basis.

# Disclaimer

#### Note:

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. The product can have a variety of different applications as well as differing application and working conditions in your environment that are beyond our control. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product.

Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

#### In case products are delivered by Henkel Belgium NV, Henkel Electronic Materials NV, Henkel Nederland BV, Henkel Technologies France SAS and Henkel France SA please additionally note the following:

In case Henkel would be nevertheless held liable, on whatever legal ground, Henkel's liability will in no event exceed the amount of the concerned delivery.

# In case products are delivered by Henkel Colombiana, S.A.S. the following disclaimer is applicable:

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product.

Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

#### In case products are delivered by Henkel Corporation, Resin Technology Group, Inc., or Henkel Canada Corporation, the following disclaimer is applicable:

The data contained herein are furnished for information only and are believed to be reliable. We cannot assume responsibility for the results obtained by others over whose methods we have no control. It is the user's responsibility to determine suitability for the user's purpose of any production methods mentioned herein and to adopt such precautions as may be advisable for the protection of property and of persons against any hazards that may be involved in the handling and use thereof. In light of the foregoing, Henkel Corporation specifically disclaims all warranties expressed or implied, including warranties of merchantability or fitness for a particular purpose, arising from sale or use of Henkel Corporation's products. Henkel Corporation specifically disclaims any liability for consequential or incidental damages of any kind, including lost profits. The discussion herein of various processes or compositions is not to be interpreted as representation that they are free from domination of patents owned by others or as a license under any Henkel Corporation patents that may cover such processes or compositions. We recommend that each prospective user test his proposed application before repetitive use, using this data as a guide. This product may be covered by one or more United States or foreign patents or patent applications.

**Trademark usage:** [Except as otherwise noted] All trademarks in this document are trademarks and/or registered trademarks of Henkel and its affiliates in the U.S. and elsewhere.

Americas +888-9Henkel Europe +44.1442.233.233 Asia +605.547.6811

# **Mouser Electronics**

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Loctite: 1419015