

LOCTITE ECI 1006 E&C

May 2014

PRODUCT DESCRIPTION

LOCTITE ECI 1006 E&C provides the following product characteristics:

Technology	Thermoplastic
Appearance	Creamy, silver paste
Product Benefits	- Fine-line screen printable - Halogen free - Excellent adhesion - High conductivity
Cure	Heat cure
Application	Conductive Ink
Typical Assembly Applications	ITO film, Membrane switches, Digitizers, Flexible circuits and Electroluminescent lamps
Key Substrates	ITO film, etched ITO and PET substrates

LOCTITE ECI 1006 E&C conductive, screen printable ink is designed for use in touch screen applications.

TYPICAL PROPERTIES OF UNCURED MATERIAL

Solids Content (TGA), %	75
Density, g/cc	2.6
Viscosity, Brookfield - CPE 52, 25 °C, mPa·s (cP):	
Speed 10 rpm	57,000
Shelf Life @ 25 °C, days	365
Flash Point, Estimated, °C	100

TYPICAL CURING PERFORMANCE

Recommended Drying Cycle

10 minutes @ 130°C

The above drying profile is a guideline recommendation. Conditions (time and temperature) may vary based on customers' experience and their application requirements, as well as customer drying equipment, oven loading and actual oven temperatures.

TYPICAL PROPERTIES OF CURED MATERIAL

Physical Properties

Adhesion, Cross Hatch, grade	5B
Pencil hardness, PET substrate	2H

Electrical Properties

Sheet Resistance, 4-point probe, mOhm/sq/mil	30
--	----

GENERAL INFORMATION

For safe handling information on this product, consult the Material Safety Data Sheet, (MSDS).

DIRECTIONS FOR USE

1. Surface Preparation

- No surface treatment is needed for ITO or etched ITO substrates.

2. Mixing/Dilution

- Mix thoroughly before use to ensure it is homogenous.
- Avoid rapid stirring, as this causes air entrapment.
- If needed, the ink can be diluted with up to 1 to 2% by weight maximum with DBE (dibasic ester). The solvent should be mixed in thoroughly, including scraping the sides of the container, for over a minute until it is homogenous and streak free.

3. Application

- LOCTITE ECI 1006 E&C is designed for fine line screen printing application.
- Recommended screen and printing parameters are:

Stainless Steel Screen, mesh	400
Emulsion Thickness, µm	10 to 12
Polyurethane Squeegee, durometer	D90
Print Speed, in/sec	7 to 10
Snap-off Distance, mils	50 to 80

Clean-up

- The equipment can be cleaned with esters (butylacetate, ethylacetate) or ketones (MIBK, MEK).

Storage

Store product in the unopened container in a dry location. Storage information may be indicated on the product container labeling.

Optimal Storage : 18 to 25 °C

Material removed from containers may be contaminated during use. Do not return product to the original container. Henkel Corporation cannot assume responsibility for product which has been contaminated or stored under conditions other than those previously indicated. If additional information is required, please contact your local Technical Service Center or Customer Service Representative.

Not for product specifications

The technical data contained herein are intended as reference only. Please contact your local quality department for assistance and recommendations on specifications for this product.

Conversions

$(^{\circ}\text{C} \times 1.8) + 32 = ^{\circ}\text{F}$
 $\text{kV/mm} \times 25.4 = \text{V/mil}$
 $\text{mm} / 25.4 = \text{inches}$
 $\text{N} \times 0.225 = \text{lb}$
 $\text{N/mm} \times 5.71 = \text{lb/in}$
 $\text{N/mm}^2 \times 145 = \text{psi}$
 $\text{MPa} = \text{N/mm}^2$
 $\text{MPa} \times 145 = \text{psi}$
 $\text{N}\cdot\text{m} \times 8.851 = \text{lb}\cdot\text{in}$
 $\text{N}\cdot\text{m} \times 0.738 = \text{lb}\cdot\text{ft}$
 $\text{N}\cdot\text{mm} \times 0.142 = \text{oz}\cdot\text{in}$
 $\text{mPa}\cdot\text{s} = \text{cP}$

Disclaimer**Note:**

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. The product can have a variety of different applications as well as differing application and working conditions in your environment that are beyond our control. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product.

Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

In case products are delivered by Henkel Belgium NV, Henkel Electronic Materials NV, Henkel Nederland BV, Henkel Technologies France SAS and Henkel France SA please additionally note the following:

In case Henkel would be nevertheless held liable, on whatever legal ground, Henkel's liability will in no event exceed the amount of the concerned delivery.

In case products are delivered by Henkel Colombiana, S.A.S. the following disclaimer is applicable:

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product.

Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

In case products are delivered by Henkel Corporation, Resin Technology Group, Inc., or Henkel Canada Corporation, the following disclaimer is applicable:

The data contained herein are furnished for information only and are believed to be reliable. We cannot assume responsibility for the results obtained by others over whose methods we have no control. It is the user's responsibility to determine suitability for the user's purpose of any production methods mentioned herein and to adopt such precautions as may be advisable for the protection of property and of persons against any hazards that may be involved in the handling and use thereof. In light of the foregoing, **Henkel Corporation specifically disclaims all warranties expressed or implied, including warranties of merchantability or fitness for a particular purpose, arising from sale or use of Henkel Corporation's products. Henkel Corporation specifically disclaims any liability for consequential or incidental damages of any kind, including lost profits.** The discussion herein of various processes or compositions is not to be interpreted as representation that they are free from domination of patents owned by others or as a license under any Henkel Corporation patents that may cover such processes or compositions. We recommend that each prospective user test his proposed application before repetitive use, using this data as a guide. This product may be covered by one or more United States or foreign patents or patent applications.

Trademark usage

Except as otherwise noted, all trademarks in this document are trademarks of Henkel Corporation in the U.S. and elsewhere. ® denotes a trademark registered in the U.S. Patent and Trademark Office.

Reference 0.0

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Loctite:](#)

[1888126](#)