

LOCTITE ABLESTIK 84-1LMIT1

September 2022

PRODUCT DESCRIPTION

LOCTITE ABLESTIK 84-1LMIT1 provides the following product characteristics:

Technology	Epoxy
Appearance	Silver
Cure	Heat cure
pH	4.5
Product Benefits	<ul style="list-style-type: none"> Electrically conductive High thermal conductivity Solvent-free formulation Low viscosity
Application	Die attach
Filler Type	Silver

LOCTITE ABLESTIK 84-1LMIT1 adhesive is designed for medium die attach applications. It is designed for screen printing using 325 mesh.

MIL-STD-883C

LOCTITE ABLESTIK 84-1LMIT1 meets the requirements of MIL-STD-883C, Method 5011.

TYPICAL PROPERTIES OF UNCURED MATERIAL

Viscosity, Brookfield CP51, 25 °C, mPa·s (cP):	
Speed 5 rpm	22,000
Work Life @ 25°C, days	14
Shelf Life @ -40°C (from date of manufacture), days	365

TYPICAL CURING PERFORMANCE

Cure Schedule

1 hour @ 150°C

Alternate Cure Schedule

2 hours @ 125°C

The above cure profiles are guideline recommendations. Cure conditions (time and temperature) may vary based on customers' experience and specific application requirements, as well as customer curing equipment, oven loading and actual oven temperatures.

TYPICAL PROPERTIES OF CURED MATERIAL

Physical Properties

Coefficient of Thermal Expansion, :	
Below Tg, ppm/°C	50
Above Tg, ppm/°C	200

Glass Transition Temperature, TMA, °C	103
Thermal Conductivity, W/(m·K)	3.6
Tensile Modulus, DMTA :	
@ -65 °C	N/mm ² 8,400 (psi) (1,218,317)
@ 25 °C	N/mm ² 7,300 (psi) (1,058,775)
@ 100 °C	N/mm ² 5,400 (psi) (783,203)
@ 150 °C	N/mm ² 540 (psi) (78,320)
@ 200 °C	N/mm ² 390 (psi) (56,564)
@ 250 °C	N/mm ² 460 (psi) (66,717)

Extractable Ionic Content, @ 100°C:

Chloride (Cl-)	≤200
Sodium (Na+)	≤50
Potassium (K+)	≤50
Weight Loss @ 300°C, %	0.16
Water Extract Conductivity, μmhos/cm	13

Electrical Properties

Volume Resistivity, ohms-cm	0.0005
-----------------------------	--------

TYPICAL PERFORMANCE OF CURED MATERIAL

Miscellaneous

Die Shear Strength:	
2 x 2 mm Au die @ 25°C, kg-f	19

Lap Shear Strength :

Aluminum to Aluminum @ 25°C	N/mm ² 13 (psi) (1,885)
-----------------------------	---------------------------------------

TYPICAL ENVIRONMENTAL RESISTANCE

Outgassing Properties

Outgassing , NASA Outgassing:	
TML, %	0.09
CVCM, %	<0.01
WVR, %	0.05


GENERAL INFORMATION

For safe handling information on this product, consult the Safety Data Sheet, (SDS).

Thawing

1. Allow container to reach room temperature before use.
2. After removing from the freezer, set the syringes to stand vertically while thawing.

3. Refer to the Syringe Thaw time chart for the thaw time recommendation.
4. DO NOT open the container before contents reach 25°C temperature. Any moisture that collects on the thawed container should be removed prior to opening the container.
5. DO NOT re-freeze. Once thawed to 25°C, the adhesive should not be re-frozen.



Surface Preparation

1. Proper preparation of substrates is critical to optimize epoxy adhesive flow and adhesion. The substrate water contact angle (WCA) is a good indicator of the capillary forces that drive resin flow and adhesion. Henkel recommends industry standards of <50° for substrate WCA. This allows the epoxy resin to better wet the substrate. Users may want to establish the precise relationship between WCA and product performance for their specific application.
2. Substrate surface chemistry is impacted by the entire substrate supply chain including supplier manufacturing methods, packaging, handling, plasma treatment, storage conditions, exposure to environment, and subsequent cleaning steps.

Directions for Use

1. Thawed material should immediately be placed on dispense equipment for use.
2. If the adhesive is transferred to a final dispensing reservoir, care must be exercised to avoid entrapment of contaminants and/or air into the adhesive.
3. Adhesive must be completely used within the product's recommended work life.
4. Silver-resin separation may occur if the adhesive is left out at room temperature, beyond the recommended work life.

Not for product specifications

The technical data contained herein are intended as reference only. Please contact your local Henkel representative for assistance and recommendations on the specifications of this product.

STORAGE

Store product in the unopened container in a dry location. Storage information may be indicated on the product container labeling.

Optimal Storage: -40 °C. Storage below minus (-)40 °C or greater than minus (-)40 °C can adversely affect product properties.

Material removed from containers may be contaminated during use. Do not return product to the original container. Henkel Corporation cannot assume responsibility for product which has been contaminated or stored under conditions other than those previously indicated. If additional information is required, please contact your local Henkel Representative.

Conversions

$(^{\circ}\text{C} \times 1.8) + 32 = ^{\circ}\text{F}$
 $\text{kV/mm} \times 25.4 = \text{V/mil}$
 $\text{mm} / 25.4 = \text{inches}$
 $\text{N} \times 0.225 = \text{lb/F}$
 $\text{N/mm} \times 5.71 = \text{lb/in}$
 $\text{N/mm}^2 \times 145 = \text{psi}$
 $\text{N/mm}^2 = \text{MPa}$
 $\text{N}\cdot\text{m} \times 8.851 = \text{lb}\cdot\text{in}$
 $\text{N}\cdot\text{m} \times 0.738 = \text{lb}\cdot\text{ft}$
 $\text{N}\cdot\text{mm} \times 0.142 = \text{oz}\cdot\text{in}$
 $\text{mPa}\cdot\text{s} = \text{cP}$

Disclaimer

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. The product can have a variety of different applications as well as differing application and working conditions in your environment that are beyond our control. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product. Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

In case products are delivered by Henkel Belgium NV, Henkel Electronic Materials NV, Henkel Nederland BV, Henkel Technologies France SAS and Henkel France SA please additionally note the following:

In case Henkel would be nevertheless held liable, on whatever legal ground, Henkel's liability will in no event exceed the amount of the concerned delivery.

In case products are delivered by Henkel Colombiana, S.A.S. the following disclaimer is applicable:

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product.

Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

In case products are delivered by Henkel Corporation, or Henkel Canada Corporation, the following disclaimer is applicable:

The data contained herein are furnished for information only and are believed to be reliable. We cannot assume responsibility for the results obtained by others over whose methods we have no control. It is the user's responsibility to determine suitability for the user's purpose of any production methods mentioned herein and to adopt such precautions as may be advisable for the protection of property and of persons against any hazards that may be involved in the handling and use thereof. In light of the foregoing, **Henkel Corporation specifically disclaims all warranties expressed or implied, including warranties of merchantability or fitness for a particular purpose, arising from sale or use of Henkel Corporation's products. Henkel Corporation specifically disclaims any liability for consequential or incidental damages of any kind, including lost profits.** The discussion herein of various processes or compositions is not to be interpreted as representation that they are free from domination of patents owned by others or as a license under any Henkel Corporation patents that may cover such processes or compositions. We recommend that each prospective user test his proposed application before repetitive use, using this data as a guide. This product may be covered by one or more United States or foreign patents or patent applications.

Trademark usage

Except as otherwise noted, all trademarks in this document are trademarks of Henkel Corporation in the U.S. and elsewhere. ® denotes a trademark registered in the U.S. Patent and Trademark Office.

Reference 0.6

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Loctite:](#)

[1199191](#) [1199298](#) [1199430](#) [1199662](#) [1199932](#) [1199980](#) [1199981](#) [1199983](#) [1200528](#) [1201390](#) [1204637](#)
[1199201](#) [1199295](#) [1199897](#) [1200359](#) [1200503](#) [2037767](#)