

LOCTITE ABLESTIK QMI506

October 2014

PRODUCT DESCRIPTION

LOCTITE ABLESTIK QMI506 provides the following product characteristics:

Technology	Silver Filled
Appearance	Silver
Components	One component - requires no mixing
Cure	Heat cure
Application	Die attach

LOCTITE ABLESTIK QMI506 is a silver filled conductive adhesive for attachment of integrated circuits and components to advanced substrates, including: SBGA's, PBGA's, array packages, tape packs and CSP's. The material is hydrophobic and stable at high temperatures. These features produce void-free bonds lines with excellent interfacial adhesion strength to a wide variety of organic and metal surfaces, including solder mask, BT, FR, polyimide, Au, Kapton™ and Mylar™. This adhesive also exhibits a very low modulus, which can reduce inter-package stress. A package or device manufactured with LOCTITE ABLESTIK QMI506 will have good resistance to delamination and "popcorning" after exposure to reflow temperatures. LOCTITE ABLESTIK QMI506 can be cured in a conventional oven, on a snap cure oven, or utilize SkipCure™ processing on a die bonder or wire bonder. The material is formulated to produce cure onset below 100°C. This can reduce or eliminate the need to pre-dry organic substrates prior to the die attach process.

TYPICAL PROPERTIES OF UNCURED MATERIAL

Specific Gravity, gm/cc	2.97
Viscosity @ 25 °C, cP:	
Speed 5 rpm	8,000
Thixotropic Index (Speed 0.5/speed 5)	4.9
Flash Point - See SDS	

TYPICAL PROPERTIES OF CURED MATERIAL

Physical Properties

Glass Transition Temperature (Tg), °C	-32
Coefficient of Thermal Expansion, TMA:	
Alpha 1, ppm/°C	74
Alpha 2, ppm/°C	177
Thermal Conductivity, W/(m-K)	1.1
DMA Modulus @ 25°C	N/mm ² 0.63 (psi) (91,000)

Extractable Ionic Content, , ppm:

Sodium (Na+)	≤20
Potassium (K+)	≤20
Chloride (Cl-)	≤20
Fluoride (F-)	≤20
Moisture Absorption, 168 hours @ 85°C/85% RH, wt. %	≤0.2

Electrical Properties

Volume Resistivity, ohms-cm	
-----------------------------	--

TYPICAL PERFORMANCE OF CURED MATERIAL

Miscellaneous

Die Shear Strength :	
(300 mil ² , 1 mil BLT) Average kg-f @ 25°C	≥14

GENERAL INFORMATION

For safe handling information on this product, consult the Material Safety Data Sheet, (MSDS).

Cure Schedule

Conventional Oven	15 minutes @ 150 °C
Snap Cure Oven	≥10 seconds @ 150 °C
Tunnel Oven:	≥10 seconds @ 150 °C
configured with hot gas or IR	
SkipCure	≥8 seconds @ 150 °C

LOCTITE ABLESTIK QMI506 can be cured using a variety of times and temperatures, depending upon the specific cure equipment. Typical cure profiles are listed below. In these profiles, the temperatures stated are bondline temperatures and the stated times are at temperature.

Not for product specifications

The technical data contained herein are intended as reference only. Please contact your local quality department for assistance and recommendations on specifications for this product.

Storage

Store product in the unopened container in a dry location. Storage information may be indicated on the product container labeling.

LOCTITE ABLESTIK QMI506 is supplied in syringes and should be stored at -40°C. Please review Loctite's Die Attach Handling Procedure for additional details on thawing and usage.

Material removed from containers may be contaminated during use. Do not return product to the original container. Henkel Corporation cannot assume responsibility for product which has been contaminated or stored under conditions other than those previously indicated. If additional information is required, please contact your local Technical Service Center or Customer Service Representative.

Conversions

(°C x 1.8) + 32 = °F
kV/mm x 25.4 = V/mil
mm / 25.4 = inches
N x 0.225 = lb
N/mm x 5.71 = lb/in
N/mm² x 145 = psi
MPa = N/mm²
MPa x 145 = psi
N·m x 8.851 = lb·in
N·m x 0.738 = lb·ft
N·mm x 0.142 = oz·in
mPa·s = cP

Disclaimer**Note**

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. The product can have a variety of different applications as well as differing application and working conditions in your environment that are beyond our control. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product.

Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

In case products are delivered by Henkel Belgium NV, Henkel Electronic Materials NV, Henkel Nederland BV, Henkel Technologies France SAS and Henkel France SA please additionally note the following:

In case Henkel would be nevertheless held liable, on whatever legal ground, Henkel's liability will in no event exceed the amount of the concerned delivery.

In case products are delivered by Henkel Colombiana S.A.S. the following disclaimer is applicable:

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. Henkel, is therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product.

Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

In case products are delivered by Henkel Corporation Resin Technology Group, Inc., or Henkel Canada, Inc. the following disclaimer is applicable:

The data contained herein are furnished for information only and are believed to be reliable. We cannot assume responsibility for the results obtained by others over whose methods we have no control. It is the user's responsibility to determine suitability for the user's purpose of any production methods mentioned herein and to adopt such precautions as may be advisable for the protection of property and of persons against any hazards that may be involved in the handling and use thereof. In light of the foregoing, **Henkel Corporation specifically disclaims all warranties expressed or implied, including warranties of merchantability or fitness for a particular purpose, arising from sale or use of Henkel Corporation's products. Henkel Corporation specifically disclaims any liability for consequential or incidental damages of any kind, including lost profits.** The discussion herein of various processes or compositions is not to be

prospective user test his proposed application before repetitive use, using this data as a guide. This product may be covered by one or more United States or foreign patents or patent applications.

Trademark usage

Except as otherwise noted, all trademarks in this document are trademarks of Henkel Corporation in the U.S. and elsewhere. ® denotes a trademark registered in the U.S. Patent and Trademark Office.

Reference 0.1

Americas
+1.888.943.6535

Europe
+32.1457.5611

Asia
+86.21.3898.4800

For the most direct access to local sales and technical support visit: www.henkel.com/electronics

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Loctite:](#)

[452132](#)