

LOCTITE ECCOBOND UV 9061F

September 2015

PRODUCT DESCRIPTION

LOCTITE ECCOBOND UV 9061F provides the following product characteristics:

Technology	Acrylate
Appearance	Translucent light blue
Product Benefits	<ul style="list-style-type: none"> • Fast cure • One component • Cures in shadowed areas • Easy dispensability without stringing • Fluorescent
Cure	Ultraviolet (UV)/ moisture
Application	Assembly
Typical Package Application	Local protection of WLCSP and BGA on circuit board

LOCTITE ECCOBOND UV 9061F no flow, UV/moisture cure encapsulant is designed for local circuit board protection. This product is fluorescent when viewed with ultraviolet (black) light.

TYPICAL PROPERTIES OF UNCURED MATERIAL

Viscosity, Rheometer, Cone and Plate, mPa·s (cP):

@ 2 s ⁻¹	23,000
@ 20 s ⁻¹	4,300
Shelf Life @ 5°C, days	180
Flash Point - See SDS	

TYPICAL CURING PERFORMANCE

Recommended UV Cure

Light Source and Condition:

Metal halide doped spectrum UV lamp

Light Intensity, mW/cm² 100

UV Wavelength, nm 365

Recommended Dose, seconds 20

Depth of Cure

Cures at least 0.20 inch under optimum conditions.

LOCTITE ECCOBOND UV 9061F can be cured by exposure to UV and/or visible light of sufficient intensity. Cure rate and ultimate depth of cure depend on light intensity, spectral distribution of light source, exposure time and light transmittance of the substrate through which the light must pass.

Moisture cures occurs at ambient temperature and humidity.

The above cure profiles are guideline recommendations. Cure conditions (time and temperature) may vary based on customers' experience and their application requirements, as well as customer curing equipment, oven loading and actual oven temperatures.

TYPICAL PROPERTIES OF CURED MATERIAL

DMA and TMA tests conducted on samples UV + 7 days moisture (RT, 50% RH) cured.

Hardness, Tg and modulus increases with additional moisture cure.

CTE decreases with additional moisture cure.

Physical Properties

Hardness, Shore D, After initial UV dose of 6.4 J/cm², moisture cure condition of 100%RH @ room temperature:

Initial, after UV Cure	55
+ 1 day moisture cure	62
+ 3 days moisture cure	70
+ 7 days moisture cure	75

Coefficient of Thermal Expansion, TMA, ppm/°C:

Below Tg	78
Above Tg	189
Glass Transition Temperature (Tg) by TMA, °C	56

GENERAL INFORMATION

For safe handling information on this product, consult the Material Safety Data Sheet, (MSDS).

DIRECTIONS FOR USE

1. Use cotton gloves to handle syringe. Touching the syringe with bare hands may induce thaw voids between the adhesive and inside walls of the syringe.
2. Handle the syringes by the end or, if packaged in bags, by the corner. A warm hand holding a cold syringe can sometimes cause formation of freeze/thaw voids.
3. Complete cleaning of the substrates should be performed to remove contamination such as oxide layers, dust, moisture, salt and oils which can cause poor adhesion or corrosion in a bonded part.
4. Usable shelf life may vary depending on method of application and storage conditions.

THAWING:

1. DO NOT open the container before contents reach 25°C temperature. Any moisture that collects on the thawed container should be removed prior to opening the container.
2. Once material has reached room temperature, the adhesive should not be re-refrigerated.
3. Voids can form in the syringes if syringes are repeatedly re-refrigerated.
4. Typical thaw/warm-up times for different package sizes are shown below:

@ 25°C, 30 cc syringes, minutes	45 to 60
@ 25°C, 55 cc syringes, hours	2
5. For optimal performance, a consistent dispense temperature is recommended. This will reduce the effects of a potential temperature change between storage place and cleaning room.

Storage

Store in original, tightly covered containers in clean, dry areas. Storage information may be indicated on the product container labeling.

Optimal Storage : 5 °C

Material removed from containers may be contaminated during use. Do not return product to the original container. Henkel Corporation cannot assume responsibility for product which has been contaminated or stored under conditions other than those previously indicated. If additional information is required, please contact your local Technical Service Center or Customer Service Representative.

Conversions

$(^{\circ}\text{C} \times 1.8) + 32 = ^{\circ}\text{F}$

$\text{kV/mm} \times 25.4 = \text{V/mil}$

$\text{mm} / 25.4 = \text{inches}$

$\text{N} \times 0.225 = \text{lb}$

$\text{N/mm} \times 5.71 = \text{lb/in}$

$\text{N/mm}^2 \times 145 = \text{psi}$

$\text{MPa} = \text{N/mm}^2$

$\text{MPa} \times 145 = \text{psi}$

$\text{N}\cdot\text{m} \times 8.851 = \text{lb}\cdot\text{in}$

$\text{N}\cdot\text{m} \times 0.738 = \text{lb}\cdot\text{ft}$

$\text{N}\cdot\text{mm} \times 0.142 = \text{oz}\cdot\text{in}$

$\text{mPa}\cdot\text{s} = \text{cP}$

Disclaimer**Note:**

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. The product can have a variety of different applications as well as differing application and working conditions in your environment that are beyond our control. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product.

Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

In case products are delivered by Henkel Belgium NV, Henkel Electronic Materials NV, Henkel Nederland BV, Henkel Technologies France SAS and Henkel France SA please additionally note the following:

In case Henkel would be nevertheless held liable, on whatever legal ground, Henkel's liability will in no event exceed the amount of the concerned delivery.

In case products are delivered by Henkel Colombiana, S.A.S. the following disclaimer is applicable:

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product.

Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

In case products are delivered by Henkel Corporation, Resin Technology Group, Inc., or Henkel Canada, Inc. the following disclaimer is applicable:

The data contained herein are furnished for information only and are believed to be reliable. We cannot assume responsibility for the results obtained by others over whose methods we have no control. It is the user's responsibility to determine suitability for the user's purpose of any production methods mentioned herein and to adopt such precautions as may be advisable for the protection of property and of persons against any hazards that may be involved in the handling and use thereof. In light of the foregoing, **Henkel Corporation specifically disclaims all warranties expressed or implied, including warranties of merchantability or fitness for a particular purpose, arising from sale or use of Henkel Corporation's products. Henkel Corporation specifically disclaims any liability for consequential or incidental damages of any kind, including lost profits.** The discussion herein of various processes or compositions is not to be interpreted as representation that they are free from domination of patents owned by others or as a license under any Henkel Corporation patents that may cover such processes or compositions. We recommend that each prospective user test his proposed application before repetitive use, using this data as a guide. This product may be covered by one or more United States or foreign patents or patent applications.

Trademark usage

Except as otherwise noted, all trademarks in this document are trademarks of Henkel Corporation in the U.S. and elsewhere. ® denotes a trademark registered in the U.S. Patent and Trademark Office.

Reference 0.0

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Loctite:](#)

[2475914](#)