



LOCTITE® ECI 1010

November 2024

PRODUCT DESCRIPTION

LOCTITE® ECI 1010 provides the following product characteristics:

| | |
|-------------------------------|--|
| Technology | Thermoplastic |
| Appearance | Gray paste |
| Filler type | Silver |
| Product benefits | <ul style="list-style-type: none">• Flexible• Good adhesion• High conductivity |
| Operating temperature | max 100°C |
| Cure | Heat drying |
| Application | Conductive ink |
| Typical assembly applications | Flexible printed circuits, RFID and other conductive circuits |
| Key substrates | PET, PI, PEN, Paper |

LOCTITE® ECI 1010 is a state-of-the-art conductive silver ink with good adhesion and mechanical strength. It offers high conductivity combined with optimal mechanical performance. The resistance level of LOCTITE® ECI 1010 typically lies around 6 mOhm/sq/25µm. Further, it can be blended with the carbon inks LOCTITE® EDAG 440A or B E&C and is compatible with the dielectric ink LOCTITE® EDAG PF 455B E&C. It is also compatible with some LOCTITE® electrically conductive adhesives (ECAs) for component attach. This product is suitable for screen printing.

TYPICAL PROPERTIES OF UNDRIED MATERIAL

| | |
|---|-------|
| Solid content, wt % | 62 |
| Viscosity, Rheometer, at 25 °C; mPa.s (cP) | |
| Shear rate 1.5 s ⁻¹ | 6,400 |
| Thixotropic index (15/1.5 s ⁻¹) | 1.6 |

TYPICAL PROPERTIES OF THE DRIED MATERIAL

Recommended drying cycle
15 minutes @ 120°C

LOCTITE® ECI 1010 can be dried using forced air or infrared systems. Higher temperatures for longer time exposure will improve the performance. Care should be taken with infrared. Too much energy can destroy the coating. Design drying rates for the maximum the substrate and production speeds can tolerate.

The above drying profile is a guideline recommendation. Conditions (time and temperature) may vary based on customers' experience and their application requirements, as well as customer drying equipment, oven loading and actual oven temperatures.

Electrical properties

| | |
|---|--------|
| Sheet resistance, 15 min at 120°C, Ohm/sq/25µm | 0.0057 |
| Resistance increase after double crease test, % | 14 |

GENERAL INFORMATION

For safe handling information on this product, consult the Safety Data Sheet (SDS).

Directions for use

1 Surface preparation

- Clean surface thoroughly prior to application.

2 Mixing/Dilution

- Mix thoroughly before use to ensure the entire ink volume is homogenous. A slow speed propeller may be utilized to mix until product is uniform.
- Should dilution be necessary, use butyl glycol acetate (CAS: 112-07-2). Henkel recommends a maximum of 10 wt%. This should be accomplished by adding solvent at 0.5 wt% intervals until desired viscosity and printability is achieved.

3 Application

- LOCTITE® ECI 1010 may be applied by screen printing method.
- Recommended screen and printing parameters are

| | |
|------------------------|------------------|
| Screen type | Polyester screen |
| Screen mesh, mesh/cm | 68 to 90 |
| Emulsion thickness, µm | 10 to 40 |
| Squeegee hardness | 70 to 80 |

Clean up

1. The screen and equipment can be cleaned with dilution solvent, or esters (butylacetate, propylacetate, or ethylacetate), or ketones (MEK, Acetone), or similar solvents.

Storage

Store product in the unopened container in a dry location. Storage information may be indicated on the product container labeling.

Optimal storage: 2 to 8°C. Storage below 0°C or above 30°C can adversely affect product properties.

Material removed from containers may be contaminated during use. Do not return product to the original container. Henkel cannot assume responsibility for product which has been contaminated or stored under conditions other than those previously indicated. If additional information is required, please contact your local Henkel representative.



Not for product specifications

The technical data contained herein are intended as reference only. Please contact your local quality department for assistance and recommendations on the specifications of this product.

Conversions

$(^{\circ}\text{C} \times 1.8) + 32 = ^{\circ}\text{F}$
 $\text{kV/mm} \times 25.4 = \text{V/mil}$
 $\text{mm} / 25.4 = \text{inches}$
 $\mu\text{m} / 25.4 = \text{mil}$
 $\text{N} \times 0.225 = \text{lb}$
 $\text{N/mm} \times 5.71 = \text{lb/in}$
 $\text{N/mm}^2 \times 145 = \text{psi}$
 $\text{MPa} \times 145 = \text{psi}$
 $\text{N}\cdot\text{m} \times 8.851 = \text{lb}\cdot\text{in}$
 $\text{N}\cdot\text{m} \times 0.738 = \text{lb}\cdot\text{ft}$
 $\text{N}\cdot\text{mm} \times 0.142 = \text{oz}\cdot\text{in}$
 $\text{mPa}\cdot\text{s} = \text{cP}$

Disclaimer

The information provided in this Technical data sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. The product can have a variety of different applications as well as differing application and working conditions in your environment that are beyond our control. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product. Any liability in respect of the information in the Technical data sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

In case products are delivered by Henkel Belgium NV, Henkel Electronic Materials NV, Henkel Nederland BV, Henkel Technologies France SAS and Henkel France SA please additionally note the following:

In case Henkel would be nevertheless held liable, on whatever legal ground, Henkel's liability will in no event exceed the amount of the concerned delivery.

In case products are delivered by Henkel Colombiana, S.A.S. the following disclaimer is applicable:

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product. Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

In case products are delivered by Henkel Corporation, or Henkel Canada Corporation, the following disclaimer is applicable:

The data contained herein are furnished for information only and are believed to be reliable. We cannot assume responsibility for the results obtained by others over whose methods we have no control. It is the user's responsibility to determine suitability for the user's purpose of any production methods mentioned herein and to adopt such precautions as may be advisable for the protection of property and of persons against any hazards that may be involved in the handling and use thereof. In light of the foregoing, **Henkel Corporation specifically disclaims all warranties expressed or implied, including warranties of merchantability or fitness for a particular purpose, arising from sale or use of Henkel Corporation's products. Henkel Corporation specifically disclaims any liability for consequential or incidental damages of any kind, including lost profits.** The discussion herein of various processes or compositions is not to be interpreted as representation that they are free from domination of patents owned by others or as a license under any Henkel Corporation patents that may cover such processes or compositions. We recommend that each prospective user test his proposed application before repetitive use, using this data as a guide. This product may be covered by one or more United States or foreign patents or patent applications.

Trademark usage

Except as otherwise noted, all trademarks in this document are trademarks of Henkel Corporation in the U.S. and elsewhere. ® denotes a trademark registered in the U.S. Patent and Trademark Office.

Reference 2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Loctite:](#)

[2022182](#) [2022184](#)