

LOCTITE® EDAG 456

April 2024

PRODUCT DESCRIPTION

LOCTITE® EDAG 456 provides the following product characteristics:

Technology	Acrylate
Appearance	Off-white
Product benefits	<ul style="list-style-type: none"> • Non-conductive • Fast UV cure • Flexible • Excellent adhesion • Excellent printability • Thermoformable • Low odor • Low yellowing
Cure	Ultraviolet (UV) light
Application	Non-conductive coating
Typical assembly applications	Insulating layer; Thermoforming
Key substrates	Polyester, Polycarbonate, Polyurethane

LOCTITE® EDAG 456 is a flexible, thermoformable, non-conductive coating which can be applied by screen printing techniques.

LOCTITE® EDAG 456 is compatible with thermoformable silver ink LOCTITE® ECI 1501 and stretchable silver ink LOCTITE® ECI 1014.

TYPICAL PROPERTIES OF UNCURED MATERIAL

Viscosity, Rheometer, 25°C, mPa.s (cP)	
Shear rate 15s ⁻¹	12,000
Solid content, %	100
Density, g/cm ³	1.35
Shelf life @ 25°C, days	365

TYPICAL CURING PERFORMANCE

Recommended cure condition	
Mercury lamp, Light dose, mJ/cm ²	1,000

The above cure profiles are guideline recommendations. These conditions (time and temperature) may vary based on customers' experience and specific application requirements, as well as customer curing equipment, oven loading and actual oven temperatures.

TYPICAL SCREEN PRINTING PROCESS

Recommended screen type	
Polyester screen, threads/cm	120
Typical one layer thickness, µm	12

TYPICAL PROPERTIES OF CURED MATERIAL

Electrical properties	
Breakdown voltage @ 25µm, volts AC	>1,000
Adhesion properties	
Adhesion to PET, ASTM 3359B	5B

GENERAL INFORMATION

Please consult the Safety Data Sheet (SDS) for safe handling information of this product.

Directions for use

Surface preparation

- Clean surface before use to remove possible contamination.

Mixing/Dilution

- Stir to ensure homogeneity before use.
- Avoid rapid stirring as this causes air entrapment.

Other

- When applying LOCTITE® EDAG 456, two layers of approximately 12 to 15 µm each should be applied. Cure both layers according to the recommended cure profile to obtain good inter-coat adhesion between the first and second layer.
- Do not freeze.
- Keep product container tightly closed when not in use.
- Keep away from heat, sparks and open flame.
- Protect material against exposure to UV sources such as daylight and fluorescent lighting.

Clean up

The equipment can be cleaned with esters (butylacetate, ethylacetate) or ketones (MEK).

Storage

Store product in the unopened container in a dry location. Storage information may be indicated on the product container labeling.

Optimal Storage: 25°C. Storage below 0°C or greater than 40°C can adversely affect product properties.

Material removed from containers may be contaminated during use. Do not return product to the original container. Henkel cannot assume responsibility for product which has been contaminated or stored under conditions other than those previously indicated. If additional information is required, please contact your local Henkel representative.

Not for product specifications

The technical data contained herein are intended as reference only. Please contact your local quality department for assistance and recommendations on the specifications of this product.

Conversions

$(^{\circ}\text{C} \times 1.8) + 32 = ^{\circ}\text{F}$
 $\text{kV/mm} \times 25.4 = \text{V/mil}$
 $\text{mm} / 25.4 = \text{inches}$
 $\mu\text{m} / 25.4 = \text{mil}$
 $\text{N} \times 0.225 = \text{lb}$
 $\text{N/mm} \times 5.71 = \text{lb/in}$
 $\text{N/mm}^2 \times 145 = \text{psi}$
 $\text{MPa} \times 145 = \text{psi}$
 $\text{N}\cdot\text{m} \times 8.851 = \text{lb}\cdot\text{in}$
 $\text{N}\cdot\text{m} \times 0.738 = \text{lb}\cdot\text{ft}$
 $\text{N}\cdot\text{mm} \times 0.142 = \text{oz}\cdot\text{in}$
 $\text{mPa}\cdot\text{s} = \text{cP}$

Disclaimer

The information provided in this Technical data sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. The product can have a variety of different applications as well as differing application and working conditions in your environment that are beyond our control. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product. Any liability in respect of the information in the Technical data sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

In case products are delivered by Henkel Belgium NV, Henkel Electronic Materials NV, Henkel Nederland BV, Henkel Technologies France SAS and Henkel France SA please additionally note the following:

In case Henkel would be nevertheless held liable, on whatever legal ground, Henkel's liability will in no event exceed the amount of the concerned delivery.

In case products are delivered by Henkel Colombiana, S.A.S. the following disclaimer is applicable:

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product. Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

In case products are delivered by Henkel Corporation, or Henkel Canada Corporation, the following disclaimer is applicable:

The data contained herein are furnished for information only and are believed to be reliable. We cannot assume responsibility for the results obtained by others over whose methods we have no control. It is the user's responsibility to determine suitability for the user's purpose of any production methods mentioned herein and to adopt such precautions as may be advisable for the protection of property and of persons against any hazards that may be involved in the handling and use thereof. In light of the foregoing, **Henkel Corporation specifically disclaims all warranties expressed or implied, including warranties of merchantability or fitness for a particular purpose, arising from sale or use of Henkel Corporation's products. Henkel Corporation specifically disclaims any liability for consequential or incidental damages of any kind, including lost profits.** The discussion herein of various processes or compositions is not to be interpreted as representation that they are free from domination of patents owned by others or as a license under any Henkel Corporation patents that may cover such processes or compositions. We recommend that each prospective user test his proposed application before repetitive use, using this data as a guide. This product may be covered by one or more United States or foreign patents or patent applications.

Trademark usage

Except as otherwise noted, all trademarks in this document are trademarks of Henkel Corporation in the U.S. and elsewhere. ® denotes a trademark registered in the U.S. Patent and Trademark Office.

Reference 2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Loctite:](#)

[2951866](#)