

LOCTITE STYCAST 2741 CAT 15

November 2017

PRODUCT DESCRIPTION

LOCTITE STYCAST 2741 CAT 15 provides the following product characteristics:

Technology	Epoxy
Technology (Catalyst)	Amine
Appearance	Black
Appearance (Catalyst)	Black
Components	Two-component
Product Benefits	<ul style="list-style-type: none"> • Ease of use • Variable flexibility • General purpose • Room temperature cure capability • Shock and impact resistant
Application	Encapsulation
Cure	Room Temperature or Heat Cure
Key Substrates	Glass, Metals, Plastics and Ceramics

LOCTITE STYCAST 2741 CAT 15 is designed for electronic embedment and in sealing or cementing of metals, ceramics and plastics. The hardness can be adjusted by varying the amount of LOCTITE CAT 15 used.

TYPICAL PROPERTIES OF UNCURED MATERIAL

Part A Properties LOCTITE STYCAST 2741

Density, g/cm ³	1.65
Viscosity, Brookfield, mPa·s (cP)	225,000
Flash Point - See SDS	

Part B Properties LOCTITE CAT 15

Density, g/cm ³	0.97
Viscosity, Brookfield, mPa·s (cP)	25,000
Flash Point - See SDS	

Mixed Properties LOCTITE STYCAST 2741 with LOCTITE CAT 15

Viscosity, Brookfield, mPa·s (cP):	
Rigid Material	37,000
Semi-rigid Material	37,000
Flexible Material	36,000

Density, g/cm ³ :	
Rigid Material	1.32
Semi-rigid Material	1.21
Flexible Material	1.15

Mix Ratio, Material:Catalyst, amount of LOCTITE CAT 15 per 100 parts LOCTITE STYCAST 2741:

By Weight:	
Rigid Material	50 : 100
Semi-rigid Material	100 : 100
Flexible Material	150 : 100
By Volume:	
Rigid Material	85 : 100
Semi-rigid Material	170 : 100
Flexible Material	250 : 100

Work Life (100 g) @ 25°C, minutes:

Rigid Material	120
Semi-rigid Material	140
Flexible Material	160

Flash Point - See SDS

TYPICAL CURING PERFORMANCE

Recommended Cure Schedule

16 to 24 hours @ 25°C
4 to 6 hours @ 45°C
2 to 4 hours @ 65°C

The above cure profiles are guideline recommendations. Cure conditions (time and temperature) may vary based on customers' experience and their application requirements, as well as customer curing equipment, oven loading and actual oven temperatures.

TYPICAL PROPERTIES OF CURED MATERIAL

Physical Properties

Hardness:	
Rigid Material, Shore D	80
Semi-rigid Material, Shore D	60
Flexible Material, Shore A	60

Thermal Conductivity, W/(m·K):

Rigid Material	0.35
Semi-rigid Material	0.35
Flexible Material	0.35

Operating temperature, °C:

Rigid Material	-40 to +90
Semi-rigid Material	-55 to +80
Flexible Material	-55 to +65

Water Absorption (24 hr immersion), %:

Rigid Material	0.2
Semi-rigid Material	0.5

Linear Shrinkage, cm/cm:

Rigid Material	0.001
Semi-rigid Material	0.001
Flexible Material	0.001

Electrical Properties

Volume Resistivity, ohms-cm	
Dielectric Constant / Dissipation Factor	
Dielectric Strength, kV/mm	

GENERAL INFORMATION

For safe handling information on this product, consult the Safety Data Sheet, (SDS).

DIRECTIONS FOR USE

1. Mix the entire contents of STYCAST 2741 W1 to a uniform consistency before removing material.
2. Accurately weigh STYCAST 2741 W1 and Catalyst 15 into a clean container in the recommended ratio.
3. Blend them together thoroughly.
4. Pour into mold or container. If necessary, trapped air is readily removed by vacuum evacuation..
5. MOLD RELEASE 122S should be used if piece is later to be removed.
6. NOTE: During storage at room temperature for long periods, it is possible that the viscosity of STYCAST 2741 W1 can increase and may exceed its upper specification limit. The viscosity can be brought back to the normal level by moderate mixing.

STORAGE:

Store product in the unopened container in a dry location. Storage information may be indicated on the product container labeling.

Optimal Storage : 18 to 25 °C

Once opened, containers should be purged with dry nitrogen.

Material removed from containers may be contaminated during use. Do not return product to the original container. Henkel Corporation cannot assume responsibility for product which has been contaminated or stored under conditions other than those previously indicated. If additional information is required, please contact your local Technical Service Center or Customer Service Representative.

Not for product specifications

The technical data contained herein are intended as reference only. Please contact your local quality department for assistance and recommendations on specifications for this product.

Conversions

$(^{\circ}\text{C} \times 1.8) + 32 = ^{\circ}\text{F}$
 $\text{kV/mm} \times 25.4 = \text{V/mil}$
 $\text{mm} / 25.4 = \text{inches}$
 $\text{N} \times 0.225 = \text{lb/F}$
 $\text{N/mm} \times 5.71 = \text{lb/in}$
 $\text{psi} \times 145 = \text{N/mm}^2$
 $\text{MPa} = \text{N/mm}^2$
 $\text{N} \cdot \text{m} \times 8.851 = \text{lb} \cdot \text{in}$
 $\text{N} \cdot \text{m} \times 0.738 = \text{lb} \cdot \text{ft}$
 $\text{N} \cdot \text{mm} \times 0.142 = \text{oz} \cdot \text{in}$
 $\text{mPa} \cdot \text{s} = \text{cP}$

Disclaimer**Note:**

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. The product can have a variety of different applications as well as differing application and working conditions in your environment that are beyond our control. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product.

Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

In case products are delivered by Henkel Belgium NV, Henkel Electronic Materials NV, Henkel Nederland BV, Henkel Technologies France SAS and Henkel France SA please additionally note the following:

In case Henkel would be nevertheless held liable, on whatever legal ground, Henkel's liability will in no event exceed the amount of the concerned delivery.

In case products are delivered by Henkel Colombiana, S.A.S. the following disclaimer is applicable:

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product.

Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

In case products are delivered by Henkel Corporation, Resin Technology Group, Inc., or Henkel Canada Corporation, the following disclaimer is applicable:

The data contained herein are furnished for information only and are believed to be reliable. We cannot assume responsibility for the results obtained by others over whose methods we have no control. It is the user's responsibility to determine suitability for the user's purpose of any production methods mentioned herein and to adopt such precautions as may be advisable for the protection of property and of persons against any hazards that may be involved in the handling and use thereof. In light of the foregoing, **Henkel Corporation specifically disclaims all warranties expressed or implied, including warranties of merchantability or fitness for a particular purpose, arising from sale or use of Henkel Corporation's products. Henkel Corporation specifically disclaims any liability for consequential or incidental damages of any kind, including lost profits.** The discussion herein of various processes or compositions is not to be interpreted as representation that they are free from domination of patents owned by others or as a license under any Henkel Corporation patents that may cover such processes or compositions. We recommend that each prospective user test his proposed application before repetitive use, using this data as a guide. This product may be covered by one or more United States or foreign patents or patent applications.

Trademark usage: [Except as otherwise noted] All trademarks in this document are trademarks and/or registered trademarks of Henkel and its affiliates in the U.S. and elsewhere.

Reference 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Loctite:](#)

[1188084](#) [1187989](#) [1187990](#)