

LOCTITE STYCAST 5952-1

November 2016

PRODUCT DESCRIPTION

LOCTITE STYCAST 5952-1 provides the following product characteristics:

Technology	Silicone
Components	Two components - requires mixing
Appearance - Part A	Red
Appearance - Part B	White
Mix Ratio, Part A:Part B	1 : 1
Product Benefits	<ul style="list-style-type: none">Electrically non-conductiveGood elongation strengthModerate tear strengthHigh thermal conductivity
Cure	Heat cure
Application	Potting or Encapsulant
Typical Assembly Applications	Transformers, Rectifiers, Thyristors, Power supplies and Heat generating modules
Other Application Areas	Thermally conductive roll coatings, Heat sinks and Thermal pads

LOCTITE STYCAST 5952-1 is designed for encapsulation of heat generating devices. It is also recommended for applications requiring a non-corrosive casting and coating.

TYPICAL PROPERTIES OF UNCURED MATERIAL

Part A Properties

Viscosity @ 25 °C, mPa·s (cP)	60,000
Density, g/cm ³	2.05
Storage Life @ 18 to 25°C (from date of manufacture), days	183
Flash Point - See SDS	

Part B Properties

Viscosity @ 25 °C, mPa·s (cP)	25,000
Density, g/cm ³	2.125
Storage Life @ 18 to 25°C (from date of manufacture), days	183
Flash Point - See SDS	

Mixed Properties

Mixed Viscosity @ 25°C, mPa·s (cP)	30,000
Density, g/cm ³	2.05
Mixed Pot Life @ 100 °C, minutes	100
Flash Point - See SDS	

TYPICAL CURING PERFORMANCE

Cure Schedule

1 hour @ 100°C

LOCTITE STYCAST 5952-1 may be cured over a broad range of temperatures. After 24 hours at room temperature, it will be hard enough to handle. Optimum properties will be achieved after 7days.

LOCTITE STYCAST 5952-1 can be cured rapidly at elevated temperatures, even in thick sections.

For optimum performance, follow the initial cure with a post cure of 2 hours at 175°C.

Cure may be inhibited through contact with certain contaminants. Common materials which should be avoided include sulfur, sulfur containing materials, nitrogen containing materials, RTV silicone catalysts and heavy metal salts. Molds, mixing equipment, ovens and other apparatus used in the preparation and curing of LOCTITE STYCAST 5952-1 should be free of inhibiting contaminants.

The above cure profiles are guideline recommendations. Cure conditions (time and temperature) may vary based on customers' experience and their application requirements, as well as customer curing equipment, oven loading and actual oven temperatures.

TYPICAL PROPERTIES OF CURED MATERIAL

Physical Properties

Hardness, Shore A	75
Coefficient of Linear Thermal Expansion, 10 ⁻⁴ K ⁻¹	2
Elongation, %	45
Thermal Conductivity, W/(m·K)	0.8

Electrical Properties

Volume Resistivity @ 25°C, ohm-cm	1×10 ¹⁴
Dielectric Constant / Loss@ 1 MHz	5.0/0.01
Dielectric Strength, ASTM D149, kV/mm	17

TYPICAL PERFORMANCE OF CURED MATERIAL

Miscellaneous:

Tensile Strength	N/mm ²	4
	(psi)	(580)

GENERAL INFORMATION

For safe handling information on this product, consult the Safety Data Sheet, (SDS).

DIRECTIONS FOR USE

1. Mix thoroughly.
2. Power mixing is preferred to ensure a homogeneous product.
3. Evacuate the resin mixture to remove entrapped air.
4. Pour mixture into cavity or mold.
5. PRIMER S 11NC is recommended for use with LOCTITE STYCAST 5952-1 to improve adhesion to non-silicone materials and to minimize the probability of cure inhibition from surface contaminants on non-silicone substrates.

Not for product specifications

The technical data contained herein are intended as reference only. Please contact your local quality department for assistance and recommendations on specifications for this product.

STORAGE:

Store in original, tightly covered containers in clean, dry areas. Storage information may be indicated on the product container labeling.

Optimal Storage: 25°C. Storage below 25°C or greater than 25°C can adversely affect product properties.

Material removed from containers may be contaminated during use. Do not return product to the original container. Henkel Corporation cannot assume responsibility for product which has been contaminated or stored under conditions other than those previously indicated. If additional information is required, please contact your local Technical Service Center or Customer Service Representative.

Conversions

$(^{\circ}\text{C} \times 1.8) + 32 = ^{\circ}\text{F}$
 $\text{kV/mm} \times 25.4 = \text{V/mil}$
 $\text{mm} / 25.4 = \text{inches}$
 $\text{N} \times 0.225 = \text{lb}$
 $\text{N/mm} \times 5.71 = \text{lb/in}$
 $\text{psi} \times 145 = \text{N/mm}^2$
 $\text{MPa} = \text{N/mm}^2$
 $\text{N}\cdot\text{m} \times 8.851 = \text{lb}\cdot\text{in}$
 $\text{N}\cdot\text{m} \times 0.738 = \text{lb}\cdot\text{ft}$
 $\text{N}\cdot\text{mm} \times 0.142 = \text{oz}\cdot\text{in}$
 $\text{mPa}\cdot\text{s} = \text{cP}$

Disclaimer**Note:**

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. The product can have a variety of different applications as well as differing application and working conditions in your environment that are beyond our control. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product.

Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

In case products are delivered by Henkel Belgium NV, Henkel Electronic Materials NV, Henkel Nederland BV, Henkel Technologies France SAS and Henkel France SA please additionally note the following:

In case Henkel would be nevertheless held liable, on whatever legal ground, Henkel's liability will in no event exceed the amount of the concerned delivery.

In case products are delivered by Henkel Colombiana, S.A.S. the following disclaimer is applicable:

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product.

Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

In case products are delivered by Henkel Corporation, Resin Technology Group, Inc., or Henkel Canada Corporation, the following disclaimer is applicable:

The data contained herein are furnished for information only and are believed to be reliable. We cannot assume responsibility for the results obtained by others over whose methods we have no control. It is the user's responsibility to determine suitability for the user's purpose of any production methods mentioned herein and to adopt such precautions as may be advisable for the protection of property and of persons against any hazards that may be involved in the handling and use thereof. In light of the foregoing, **Henkel Corporation specifically disclaims all warranties expressed or implied, including warranties of merchantability or fitness for a particular purpose, arising from sale or use of Henkel Corporation's products. Henkel Corporation specifically disclaims any liability for consequential or incidental damages of any kind, including lost profits.** The discussion herein of various processes or compositions is not to be interpreted as representation that they are free from domination of patents owned by others or as a license under any Henkel Corporation patents that may cover such processes or compositions. We recommend that each prospective user test his proposed application before repetitive use, using this data as a guide. This product may be covered by one or more United States or foreign patents or patent applications.

Trademark usage: [Except as otherwise noted] All trademarks in this document are trademarks and/or registered trademarks of Henkel and its affiliates in the U.S. and elsewhere.

Reference 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Loctite:](#)

[1188237](#)