

# LOCTITE STYCAST AE 4297

April 2019

## PRODUCT DESCRIPTION

LOCTITE STYCAST AE 4297 provides the following product characteristics:

<b>Technology</b>	Epoxy
Appearance, Resin (Component A)	Tan
Appearance, Hardener (Component B)	Tan
Appearance (cured)	Tan
Components	Two components - requires mixing
Mix Ratio by volume: Part A: Part B	100 : 39
Mix Ratio, by weight - Part A: Part B	100 : 43
<b>Cure</b>	Room temperature or Heat cure
<b>Application</b>	Component assembly, NCA

LOCTITE STYCAST AE 4297 is a general purpose, room temperature cure adhesive.

## TYPICAL PROPERTIES OF UNCURED MATERIAL

### Part A Properties LOCTITE STYCAST AE 4297

Viscosity, Brookfield - RVF, 25 °C, mPa·s (cP):	
Spindle 7, speed 2 rpm	600
Spindle 7, speed 10 rpm	250
Shelf Life @ 25°C (from date of shipment), days	356

### Part B Properties LOCTITE STYCAST HD 3477

Viscosity, Brookfield - RVF, 25 °C, mPa·s (cP):	
Spindle 7, speed 2 rpm	700
Spindle 7, speed 20 rpm	300
Shelf Life @ 25 °C, days	365
Shelf Life @ 25°C (from date of shipment), days	365

### Mixed Properties LOCTITE STYCAST AE 4297 with LOCTITE STYCAST HD 3477

Pot Life @ 25 °C, 100 gm mass, minutes	20
Flash Point - See SDS	

## TYPICAL CURING PERFORMANCE

### Recommended Cure Schedule

24 hours @ 25°C

### Alternate Cure Schedule

2 hours @ 60°C

The above cure profile is a guideline recommendation. Cure conditions (time and temperature) may vary based on customers' experience and their application requirements, as well as customer curing equipment, oven loading and actual oven temperatures.

## TYPICAL PROPERTIES OF CURED MATERIAL

### Physical Properties

Coefficient of Linear Thermal Expansion (30 to 90 °C), ppm/°C, 10 <sup>-6</sup>	30.3
Tensile Shear Strength:	
Cure 7 days @ 25°C	1,750
Cure 2 hours @ 60°C	2,300
Linear Shrinkage, %	0.125
Thermal Conductivity, cal x cm/sec x cm <sup>2</sup> x °C, 10 <sup>-4</sup>	10.4
Moisture Absorption, %:	
24 hours immersion	0.14
7 days immersion	0.45

### Electrical Properties

Dissipation Factor:	
1 kHz @ 25°C	6.11
1 kHz @ 110°C	10.6
1 kHz @ 125°C	17.4
Dielectric Constant :	
1 kHz @ 25°C	0.89
1 kHz @ 110°C	0.228
1 kHz @ 125°C	0.606
Volume Resistivity, ohm-cm :	
@ 25°C	3.52×10 <sup>14</sup>
@ 110°C	1.97×10 <sup>12</sup>
@ 125°C	1.16×10 <sup>12</sup>

## GENERAL INFORMATION

For safe handling information on this product, consult the Safety Data Sheet, (SDS).

**Not for product specifications**

The technical data contained herein are intended as reference only. Please contact your local quality department for assistance and recommendations on specifications for this product.

**STORAGE:**

Store product in the unopened container in a dry location. Storage information may be indicated on the product container labeling.

**Liquid Storage - Liquids should be stored at 25°C or below, in closed containers. If stored below 23°C, the material MUST be allowed to come to room temperature, in the sealed container, to avoid moisture contamination.**

Material removed from containers may be contaminated during use. Do not return product to the original container. Henkel Corporation cannot assume responsibility for product which has been contaminated or stored under conditions other than those previously indicated. If additional information is required, please contact your local Technical Service Center or Customer Service Representative.

**Conversions**

$(^{\circ}\text{C} \times 1.8) + 32 = ^{\circ}\text{F}$   
 $\text{kV/mm} \times 25.4 = \text{V/mil}$   
 $\text{mm} / 25.4 = \text{inches}$   
 $\text{N} \times 0.225 = \text{lb}$   
 $\text{N/mm} \times 5.71 = \text{lb/in}$   
 $\text{psi} \times 145 = \text{N/mm}^2$   
 $\text{MPa} = \text{N/mm}^2$   
 $\text{N}\cdot\text{m} \times 8.851 = \text{lb}\cdot\text{in}$   
 $\text{N}\cdot\text{m} \times 0.738 = \text{lb}\cdot\text{ft}$   
 $\text{N}\cdot\text{mm} \times 0.142 = \text{oz}\cdot\text{in}$   
 $\text{mPa}\cdot\text{s} = \text{cP}$

**Disclaimer****Note:**

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. The product can have a variety of different applications as well as differing application and working conditions in your environment that are beyond our control. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product.

Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

**In case products are delivered by Henkel Belgium NV, Henkel Electronic Materials NV, Henkel Nederland BV, Henkel Technologies France SAS and Henkel France SA please additionally note the following:**

In case Henkel would be nevertheless held liable, on whatever legal ground, Henkel's liability will in no event exceed the amount of the concerned delivery.

**In case products are delivered by Henkel Colombiana, S.A.S. the following disclaimer is applicable:**

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product.

Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

**In case products are delivered by Henkel Corporation, Resin Technology Group, Inc., or Henkel Canada Corporation, the following disclaimer is applicable:**

The data contained herein are furnished for information only and are believed to be reliable. We cannot assume responsibility for the results obtained by others over whose methods we have no control. It is the user's responsibility to

determine suitability for the user's purpose of any production methods mentioned herein and to adopt such precautions as may be advisable for the protection of property and of persons against any hazards that may be involved in the handling and use thereof. In light of the foregoing, **Henkel Corporation specifically disclaims all warranties expressed or implied, including warranties of merchantability or fitness for a particular purpose, arising from sale or use of Henkel Corporation's products. Henkel Corporation specifically disclaims any liability for consequential or incidental damages of any kind, including lost profits.** The discussion herein of various processes or compositions is not to be interpreted as representation that they are free from domination of patents owned by others or as a license under any Henkel Corporation patents that may cover such processes or compositions. We recommend that each prospective user test his proposed application before repetitive use, using this data as a guide. This product may be covered by one or more United States or foreign patents or patent applications.

**Trademark usage:** [Except as otherwise noted] All trademarks in this document are trademarks and/or registered trademarks of Henkel and its affiliates in the U.S. and elsewhere.

Reference 1

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Loctite:](#)

[2222521](#)