

LOCTITE STYCAST US 5002

April 2015

PRODUCT DESCRIPTION

LOCTITE STYCAST US 5002 provides the following product characteristics:

Technology	Polyurethane
Components	Two components - requires mixing
Appearance - Part A	Black
Appearance - Part B	Off-white
Appearance (Mixed)	Black
Mix Ratio by volume: Part A: Part B	1 : 1
Cure	Room temperature cure
Mix Ratio by weight: Part A: Part B	100 : 92
Product Benefits	<ul style="list-style-type: none"> Unfilled Non-sag on mixing Tack-free in only 1.5 hours
Application	Potting and Encapsulating

LOCTITE STYCAST US 5002 is formulated for high speed sealing and potting applications.

TYPICAL PROPERTIES OF UNCURED MATERIAL

Part A Properties

Viscosity @ 25 °C, mPa·s (cP)	8,000
Density, lbs/gal	9.5

Part B Properties

Viscosity @ 25 °C, mPa·s (cP)	4,000
Density, lbs/gal	8.7

Mixed Properties

Mixed Viscosity, mPa·s (cP) :	
@ 2 minutes	17,000
@ 8 minutes	90,000
Density, lbs/gal	9.1
Shelf Life, stored in cool, dry conditions, from date of manufacture, days	183

TYPICAL CURING PERFORMANCE

Recommended Curing Conditions

16 hours @ 25°C

Gel Time

Gel @ 25°C, 100 gram mass, minutes 20

Gel time is longer (@ 30 minutes) in static gel tubes.

The above cure profiles are guideline recommendations. Cure conditions (time and temperature) may vary based on customers' experience and their application requirements, as well as customer curing equipment, oven loading and actual oven temperatures.

TYPICAL PROPERTIES OF CURED MATERIAL

Physical Properties

Hardness, Shore A	90
-------------------	----

GENERAL INFORMATION

For safe handling information on this product, consult the Safety Data Sheet, (SDS).

This product is not recommended for use in pure oxygen and/or oxygen rich systems and should not be selected as a sealant for chlorine or other strong oxidizing materials.

Not for product specifications

The technical data contained herein are intended as reference only. Please contact your local quality department for assistance and recommendations on specifications for this product.

DIRECTIONS FOR USE

1. This material is susceptible to moisture contamination. After opening a container, a nitrogen blanket should be applied over the material and the container should be resealed immediately after use to help minimize the chance of water ingress.

STORAGE:

Store product in the unopened container in a dry location. Storage information may be indicated on the product container labeling.

Liquid Storage - Liquids should be stored at 25°C or below, in closed containers. If stored below 25°C, the material MUST be allowed to come to room temperature, in the sealed container, to avoid moisture contamination.

Material removed from containers may be contaminated during use. Do not return product to the original container. Henkel Corporation cannot assume responsibility for product which has been contaminated or stored under conditions other than those previously indicated. If additional information is required, please contact your local Technical Service Center or Customer Service Representative.

Conversions

(°C x 1.8) + 32 = °F
 kV/mm x 25.4 = V/mil
 mm / 25.4 = inches
 N x 0.225 = lb
 N/mm x 5.71 = lb/in
 psi x 145 = N/mm²
 MPa = N/mm²
 N·m x 8.851 = lb·in
 N·m x 0.738 = lb·ft
 N·mm x 0.142 = oz·in
 mPa·s = cP

Disclaimer

Note

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. The product can have a variety of different applications as well

as differing application and working conditions in your environment that are beyond our control. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product.

Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

In case products are delivered by Henkel Belgium NV, Henkel Electronic Materials NV, Henkel Nederland BV, Henkel Technologies France SAS and Henkel France SA please additionally note the following:

In case Henkel would be nevertheless held liable, on whatever legal ground, Henkel's liability will in no event exceed the amount of the concerned delivery.

In case products are delivered by Henkel Colombiana S.A.S. the following disclaimer is applicable:

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product.

Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

In case products are delivered by Henkel Corporation Resin Technology Group, Inc., or Henkel Canada, Inc. the following disclaimer is applicable:

The data contained herein are furnished for information only and are believed to be reliable. We cannot assume responsibility for the results obtained by others over whose methods we have no control. It is the user's responsibility to determine suitability for the user's purpose of any production methods mentioned herein and to adopt such precautions as may be advisable for the protection of property and of persons against any hazards that may be involved in the handling and use thereof. In light of the foregoing, **Henkel Corporation specifically disclaims all warranties expressed or implied, including warranties of merchantability or fitness for a particular purpose, arising from sale or use of Henkel Corporation's products. Henkel Corporation specifically disclaims any liability for consequential or incidental damages of any kind, including lost profits.** The discussion herein of various processes or compositions is not to be interpreted as representation that they are free from domination of patents owned by others or as a license under any Henkel Corporation patents that may cover such processes or compositions. We recommend that each prospective user test his proposed application before repetitive use, using this data as a guide. This product may be covered by one or more United States or foreign patents or patent applications.

Trademark usage

Except as otherwise noted, all trademarks in this document are trademarks of Henkel Corporation in the U.S. and elsewhere. ® denotes a trademark registered in the U.S. Patent and Trademark Office.

Reference 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Loctite:](#)

[881086](#) [881087](#)