

LOCTITE TC 4

June 2014

PRODUCT DESCRIPTION

LOCTITE TC 4 provides the following product characteristics:

Technology	Silicone grease
Appearance	white
Product Benefits	<ul style="list-style-type: none"> • High thermal conductivity • High insulation resistance • High dielectric strength
Application	Thermal management
Typical Applications	<ul style="list-style-type: none"> • Heat sinks in semiconductor devices • Thermoelectric devices in radiators • Thermostats in mounting surfaces • Power resistors on chassis
Operating Temperature	-40 to +200 °C

LOCTITE TC 4 is recommended for high temperature heat transfer in normal applications. It is used to provide a conductive heat path between heat generating electronic components and heat dissipating structures. This material retains its paste-like consistency, and will not harden, after long exposure to elevated temperatures.

TYPICAL PROPERTIES

Density , g/cm ³	2.35
Shelf Life @ 18 to 25°C, days	365

TYPICAL PROPERTIES AFTER APPLICATION

Physical Properties :

Hardness, Shore A	20 to 25
Thermal Conductivity , W/(m-K)	0.6

Electrical Properties:

Dielectric Strength, kV/mm	19.7
Volume Resistivity, ohms-cm	1×10 ¹³

GENERAL INFORMATION

For safe handling information on this product, consult the Material Safety Data Sheet, (MSDS).

DIRECTIONS FOR USE

1. For best results parts to be covered should be clean and free of oil and debris.
2. LOCTITE TC 4 may be dispensed from syringes, cartridges, automatic dispensing equipment or other similar devices.
3. Application of LOCTITE TC 4 is made with a small, stiff brush.
4. Squeeze out excess material when surfaces are mated. Keep film thickness to a minimum. Mating surfaces are lubricated and also protected from corrosion by the compound.
5. Storage for long periods of time at elevated temperatures may result in slight separation of the conductive fillers from the silicone oil. If this condition is seen to exist, the fillers may be easily redispersed by hand or mechanical mixing.

6. In order to obtain the optimal thermal conductivity of LOCTITE TC 4, any entrained air should be removed in a vacuum chamber. In thin films, this is generally unnecessary.

Storage

Store product in the unopened container in a dry location. Storage information may be indicated on the product container labeling.

Optimal Storage : 18 to 25 °C

Material removed from containers may be contaminated during use. Do not return product to the original container. Henkel Corporation cannot assume responsibility for product which has been contaminated or stored under conditions other than those previously indicated. If additional information is required, please contact your local Technical Service Center or Customer Service Representative.

Not for product specifications

The technical data contained herein are intended as reference only. Please contact your local quality department for assistance and recommendations on specifications for this product.

Conversions

(°C x 1.8) + 32 = °F
 kV/mm x 25.4 = V/mil
 mm / 25.4 = inches
 N x 0.225 = lb
 N/mm x 5.71 = lb/in
 N/mm² x 145 = psi
 MPa = N/mm²
 MPa x 145 = psi
 N·m x 8.851 = lb·in
 N·m x 0.738 = lb·ft
 N·mm x 0.142 = oz·in
 mPa·s = cP

Disclaimer

Note:

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. The product can have a variety of different applications as well as differing application and working conditions in your environment that are beyond our control. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product.

Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

In case products are delivered by Henkel Belgium NV, Henkel Electronic Materials NV, Henkel Nederland BV, Henkel Technologies France SAS and Henkel France SA please additionally note the following:

In case Henkel would be nevertheless held liable, on whatever legal ground, Henkel's liability will in no event exceed the amount of the

concerned delivery.

In case products are delivered by Henkel Colombiana, S.A.S. the following disclaimer is applicable:

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product.

Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

In case products are delivered by Henkel Corporation, Resin Technology Group, Inc., or Henkel Canada, Inc. the following disclaimer is applicable:

The data contained herein are furnished for information only and are believed to be reliable. We cannot assume responsibility for the results obtained by others over whose methods we have no control. It is the user's responsibility to determine suitability for the user's purpose of any production methods mentioned herein and to adopt such precautions as may be advisable for the protection of property and of persons against any hazards that may be involved in the handling and use thereof. In light of the foregoing, **Henkel Corporation specifically disclaims all warranties expressed or implied, including warranties of merchantability or fitness for a particular purpose, arising from sale or use of Henkel Corporation's products. Henkel Corporation specifically disclaims any liability for consequential or incidental damages of any kind, including lost profits.** The discussion herein of various processes or compositions is not to be interpreted as representation that they are free from domination of patents owned by others or as a license under any Henkel Corporation patents that may cover such processes or compositions. We recommend that each prospective user test his proposed application before repetitive use, using this data as a guide. This product may be covered by one or more United States or foreign patents or patent applications.

Trademark usage

Except as otherwise noted, all trademarks in this document are trademarks of Henkel Corporation in the U.S. and elsewhere. ® denotes a trademark registered in the U.S. Patent and Trademark Office.

Reference 0.1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Loctite:

[1189081](#) [1189222](#)