


CGWMJ8-POE-C6



- UL497B LISTED
- Hybrid SAD-GDT technology
- Surge Rating - 16kA 8/20us
- Data transmission speed to 5Gbps
- IEEE 802.3bt POE++, UPoE to 90W
- IP66 Enclosure



Electrical Characteristics

VOLTS	(V)	48
AC/DC/DC PV/RF		DC
WIRES		8W+Shield+Ground
LINE CURRENT MAX	(A)	1.6
POWER RATING	(W)	95
AMBIENT MIN	(C)	-35
AMBIENT MAX	(C)	+85
MODES		DC+-DC-,DC+-G,DC--G,SH-G
RESIDUAL VOLTAGE	(V)	70
MCOV	(V)	60/72/72
IN(10 impulses 8/20μs)	(kA)	10.0000
IMAX(8/20μs)	(kA)	16
DATA SPEED	(bps)	10/100/1000/10000

Mechanical Characteristics

TECHNOLOGY		SAD-GDT
NETWORK CONFIGURATION		Single POE Line
CONNECTION METHOD		Shielded RJ45
MOUNTING		FLANGE MOUNT/POLE MOUNT KIT
MATERIAL		Polycarbonate
FLAMMABILITY RATING		UL94-V0
NEMA RATING (IP RATING)		6 (IP66)
DIMENSIONS		See diagram (mm)

Standards

UL CATEGORY		QVGQ
UL FILE NUMBER		E184939
STANDARDS		NOM-003-SCFI-2014, NOM-001-SCFI-1993
ENVIRONMENTAL STANDARDS		ROHS

Part number

890191

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Citel:

[CWMJ8-POE-C6A](#)