

**Customer Part:**

**Description**

- Industry standard SMD crystal  
Resistance welded, hermetically sealed in an inert atmosphere,  
glass to metal seals on leads  
Lead wires are mounted onto a plastic former to create a gull  
wing mount
- Model HC49/4HSMX
- Model Issue number 17

**Frequency Parameters**

- Frequency 6.0MHz
- Frequency Tolerance  $\pm 30.00\text{ppm}$
- Tolerance Condition @  $25^{\circ}\text{C} \pm 2^{\circ}\text{C}$
- Frequency Stability  $\pm 50.00\text{ppm}$
- Operating Temperature Range  $0.00$  to  $50.00^{\circ}\text{C}$
- Overtone Order Fundamental
- Ageing  $\pm 5\text{ppm typ per year @ } 25^{\circ}\text{C}$

**Electrical Parameters**

- Load Capacitance (CL)  $20.00\text{pF}$
- Shunt Capacitance (C0)  $7\text{pF max}$
- Drive Level  $500\mu\text{W max}$
- ESR  $60.00\Omega \text{ max}$

**Environmental Parameters**

- Shock:  $981\text{m/s}^2$ , 6ms, 3 times in each of 3 mutually perpendicular planes
- Vibration: 10Hz-60Hz, 0.75mm amplitude, 60Hz-500Hz,  $98.1\text{m/s}^2$ , 30mins in 3 mutually perpendicular planes
- Storage Temperature Range:  $-55$  to  $125^{\circ}\text{C}$
- RoHS Terminations
- RoHS Reflow Temp  $260^{\circ}\text{C max for 10s max}$

**Compliance**

- RoHS Status (2015/863/EU) Compliant
- REACH Status Compliant
- MSL Rating (JDEC-STD-033): Not Applicable

**Packaging Details**

- Pack Style: Reel Tape & reel in accordance with EIA-481-D  
Pack Size: 1,000
- Alternative packing option available



**Outline (mm)**



**Typical Frequency vs Temperature Curves**



**Sales Office Contact Details:**

UK: +44 (0)1460 270200  
Germany: 0800 1808 443

France: 0800 901 383  
USA: +1.760.318.2824

Email: [info@iqdfrequencyproducts.com](mailto:info@iqdfrequencyproducts.com)  
Web: [www.iqdfrequencyproducts.com](http://www.iqdfrequencyproducts.com)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[IQD Frequency Products:](#)

[LFX TAL032868Reel](#)