






NOTES:

CRIMPING:

USE CRIMP TOOL: 360X10409X

WITH TOOL INSERT: 360X20029X


SELECTOR SETTINGS: 7 FOR AWG 10

6 FOR AWG 12

(b)

plating	part no.
GOLD FLASH over NICKEL	131A11039X
30µin HARD GOLD over min. 50µin NICKEL	131C11039X
50µin HARD GOLD over min. 50µin NICKEL	131J11039X

STRIPPING DIMENSIONS



3	1	RETAINING RING	COPPER ALLOY	NICKEL PLATED			
2	1	REAR SIDE	COPPER ALLOY	GOLD FLASH over NICKEL			
1	1	MATING SIDE	COPPER ALLOY	see table			
pos	qty	description	material	plating			
partlist							
THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH	DO NOT ALTER CAD DRAWING BY HAND	tolerance		scale: 8:1			
		 dim. in mm		material: see partlist			
			date	name	title: HIGH POWER CONTACT MALE CRIMP VERSION 30A FOR AWG 10-12 D-SUB COMBINATION		
			drawn	12.07.12		Schmidt	
			appd.	12.07.12		Koch	
			norm				
			d-old	13K1ID3A / 13K2ID3A		dwg no: 13K1A4010	DIN-A3 sh: 1
		1 x b	A4380	12.07.12	HS		
		a	Original			part no: see table	
		rev.	description	date	name		
							

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CONEC:](#)

[131C11039X](#)