





Part no.	Finish Pos.1	Finish Pos.2	Finish Pos.3	Finish Pos.4
132A24019X	GOLD FLASH over NICKEL	GOLD FLASH over NICKEL	NICKEL PLATED	GOLD FLASH over NICKEL
132J24019X	min. 50µin HARD GOLD over min. 50µin NICKEL	GOLD FLASH over NICKEL	NICKEL PLATED	min. 30µin HARD GOLD over min. 50µin NICKEL



(b) MOUNTING HOLES



Directive 2002/95/EC RoHS compliant

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH	DO NOT ALTER CAD DRAWING BY HAND				tolerance		 dim. in mm	scale: 8:1	
								material: COPPER ALLOY (Pos. 1 - 4) (b)	
					date	name	title: COAXIAL CONTACT SOCKET 50 OHM Straight PCB termination, (76) with 3 Pins for D-SUB COMBINATION		
					drawn 08.12.06	Schwenkler			
					appd. 08.12.06	Lehmenkühler			
					norm				
					d-old		dwg no: 13K2IARA DIN-A3 sh: 1		
	7 x b	Ä5188	30.04.14	HS					
	a	Original							
	rev.	description	date	name			part no: see table (b)		

CONEC

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

CONEC:

132J24019X