





used for: D-SUB HD

POS.	A -0.76	B +0.25	C	D -0.3	PART NO.
15	31.19	16.79	25.00 ^{+0.12} _{-0.13}	6.12	163A17849X
26	39.52	25.12	33.30 ^{+0.15} _{-0.1}	6.12	163A17859X
44	53.42	38.84	47.04 ^{+0.13}	5.99	163A17869X
62	69.70	55.30	63.50 ^{+0.13}	5.99	163A17879X



NOTES:

- METALSHELLS: STEEL; min. 320µ" TIN
- INSULATORS: PBT GF UL 94 V-0, BLACK
- CONTACTS: COPPER ALLOY
PLATING: 8µ" HARD GOLD OVER min. 50µ" NICKEL
- METAL BRACKET: DIE-CASTING; min. 320µ" TIN over 80µ" NICKEL
- THREADED LOCK: COPPER ALLOY; min. 200µ" TIN over 80µ" NICKEL
- PCB-SNAP: COPPER ALLOY; min. 200µ" TIN over 80µ" NICKEL
PCB-HOLE: Ø3.1±0.1; PCB THICKNESS 1.6mm
- FIXING-PLATE: PBT GF UL 94 V-0, BLACK
- P.C.B. HOLE DRILLINGS ON SHEET 2
- MAXIMUM TORQUE VALUE FOR THREAD: 6" LBS
- CONNECTOR IS PART MARKED: PART-NO. CONEC ABC
- = CHECK DIMENSION

Directive 2002/95/EC
RoHS
Compliant

APPROVAL * FREIGABE * DEBLOCAGE * AUTOR/ZACON * APPROVAL	
CUSTOMER APPROVAL DATE:	
NAME:	TITLE:
COMPANY NAME:	
APPROVAL * FREIGABE * DEBLOCAGE * AUTOR/ZACON * APPROVAL	


THIS DRAWING MAY NOT BE COPIED OR
REPRODUCED IN ANY WAY, AND MAY NOT
BE PASSED ON TO A THIRD PARTY WITHOUT
WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH
DO NOT ALTER CAD DRAWING BY HAND

rev.	description	date	name
a	Origin		


tolerance	dim. in mm
2006	date
drawn	20.02.
appd.	20.02.
norm	DIN 41652
d-old	

CONEC®


scale:	2:1 (5:1)
material:	SEE NOTES
title:	D-SUB HD MALE 90° 15-62pos. 0.350inch threaded lock, metal bracket, clip, fixing-plate
dwg no:	AutoCAD 2004 DIN-A 3 sh: 1/2
part no:	SEE TABLE




15pos.



26pos.



44pos.



62pos.

APPROVAL # FREIGABE # DEBLOCKAGE # AUTOR/ZACION # APPROVAL	APPROVAL # FREIGABE # DEBLOCKAGE # AUTOR/ZACION # APPROVAL
CUSTOMER APPROVAL DATE:	
NAME:	TITLE:
COMPANY NAME:	
APPROVAL # FREIGABE # DEBLOCKAGE # AUTOR/ZACION # APPROVAL	APPROVAL # FREIGABE # DEBLOCKAGE # AUTOR/ZACION # APPROVAL

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION.

				tolerance		 dim. in mm	
				2006	date	name	
				drawn	20.02.	Lehmenkühler	
				appd.	20.02.	Mickenbecker	
				norm			
				d-old			
a	Origin						
rev.	description		date				

scale:	2:1	
material:	SEE SHEET 1	
title:	P.C.B. HOLE DRILLINGS D-SUB HD MALE 90° 15-62pos. 0.350inch threaded lock,metal bracket,clip,fixing plate	
dwg no:	AutoCAD 2004	DIN-A
	16K1A1758	3
		sh:2/2
part no:	SEE SHEET 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CONEC:](#)

[163A17849X](#)