

used for:	D-SUB
-----------	-------

C

## B

- B

Directive 2002/95/EC RoHS compliant

A



dim. in mm

scale:	1:1
material:	SEE NOTES

title:	METAL HOOD 9-37pos. EMI/RFI SHIELDING with straight cable exit and jack screws
--------	--

dwg no:	DIN-A
16K1A714	4
	sh:1/2
part no:	SEE TABLE

3

---

1

4

3

---

2

1

4

3

2



1

used for: D-SUB

ASSEMBLY INSTRUCTION:



Use two halves of strain relief  
different sizes can be mixed

Strip cable 18mm and  
shape cable to two pigtails





Attach the strain relief around the cable

Bend cable shielding back  
on outside of strain relief





Mount connector and cable  
into the backshell

Assemble the other half  
screwing force: 100-120 Ncm.



THIS DRAWING MAY NOT BE COPIED OR  
REPRODUCED IN ANY WAY, AND MAY NOT  
BE PASSED ON TO A THIRD PARTY WITHOUT  
WRITTEN PERMISSION.  
OWNERSHIP AND COPYRIGHT OF CONEC GmbH  
DO NOT ALTER CAD DRAWING BY HAND

				tolerance		 dim. in mm
rev.	description	date	name			
				2011	date	name
				drawn	30.11.	Lehmenkühler
				appd.	30.11.	Fischer
				norm		
				d-old		
a	Original					

scale:	
material:	
title:	ASSEMBLY INSTRUCTION METAL HOOD 9-37pos. EMI/RFI SHIELDING with straight cable exit and jack screws
dwg no:	16K1A714
part no:	SEE SHEET 1

DIN-A  
4  
sh:2/2

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CONEC:](#)

[165X02619X](#)