








NOTES:

- METAL SHELLS: STEEL; min. 320 μ " TIN
- INSULATORS: PBT GF UL 94 V-0, GREEN
- THREADED INSERT: COPPER ALLOY; min. 200 μ " TIN over 80 μ " NICKEL
- COLLAR: COPPER ALLOY; min. 200 μ " TIN over 80 μ " NICKEL
- MAXIMUM TORQUE VALUE FOR THREAD: 6" LBS
- ☐ = CRITICAL DIMENSION: SPC

Directive 2002/95/EC
"RoHS"
Compliant



THIS DRAWING MAY NOT BE COPIED OR
REPRODUCED IN ANY WAY, AND MAY NOT
BE PASSED ON TO A THIRD PARTY WITHOUT
WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GMBH
DO NOT ALTER CAD DRAWING BY HAND

tolerance		scale:	
		2:1 (5:1)	
material:		SEE NOTES	
title:		D-SUB COMBINATION FEMALE	
name		8W8S	
date		with threaded insert	
drawn		17.05.	
appd.		E. Mickenbecker	
norm			
d-old			
rev.		description	
name		date	

CONEC®

dwg no: 13K1A253A
DIN-A 3
sh: 1/1
part no: 3008W8SXX99A30X

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

CONEC:

[3008W8SXX99A30X](#)