


Technical specification:

Rated voltage: IEC 60664-1	300 V
Overvoltage category: IEC 60664-1	2
Overvoltage: IEC 60664-1	2,7 kV
Current rating: IEC 60512-3 at 40°C	0,75mm ² 1,5mm ² 8 A 10 A
Insulation resistance: IEC 60512	>=100 MΩ
Pollution degree: IEC 60664-1	3/2
Degree of protection: IEC 60529	IP 68, in mated condition
Temperature range: IEC 60664-1	-30°C ... +80°C
Mating cycles: IEC 60512-9a	>=100
Termination:	crimped

Materials:


Contact:	CuZn
Contact plating:	Nickel, gold plated
Contact carrier:	TPU, UL 94
Coupling screw:	CuZn, nickel plated
Moulding body:	TPU, UL 94, grey

Contact assignment:

1	black
2	blue
PE	green-yellow
4	brown
5	white

Part no:	Description:	Length L:	Cable:
41-01076	SAL - 7/8 - RS4PE - 2 / K1	2m	TPU, UL 20549, black, 5x0,75mm ² , Cable: 781-K17500
41-01077	SAL - 7/8 - RS4PE - 3 / K1	3m	
41-01078	SAL - 7/8 - RS4PE - 5 / K1	5m	
41-01079	SAL - 7/8 - RS4PE - 10 / K1	10m	
41-xxxxx	SAL - 7/8 - RS4PE - ... / K1	x	
41-01173	SAL - 7/8 - RS4PE - 2 / K1 / 150	2m	TPU, UL 20549, black, 5x1,50mm ² , Cable: 781-K18500
41-01174	SAL - 7/8 - RS4PE - 3 / K1 / 150	3m	
41-01175	SAL - 7/8 - RS4PE - 5 / K1 / 150	5m	
41-01176	SAL - 7/8 - RS4PE - 10 / K1 / 150	10m	
41-xxxxx	SAL - 7/8 - RS4PE - ... / K1 / 150	x	

D see data sheet cable

DO NOT ALTER CAD DRAWING BY HAND Directive 2002/95/EC RoHS compliant	Index: b 01.09.10 KH Ä3736 technical specification changed, part no. cable in table added, neutrale line added		 dim. in mm		title: Male connector 7/8" axial	
			date	name		
	tolerance of cable: L <= 4m: L + 40mm L > 4m: L + 1%		drawn	19.10.07	Mankopf	dwg no: 41K1A324
			appd.	19.10.07	Franz	
	general tolerance: 0 ± 0,50mm 0,0 ± 0,25mm 0,00 ± 0,10mm					part no: see table
THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH						

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CONEC:](#)

[41-01077](#)