









NOTES:

- METALSHELLS: STEEL; min. 315µin TIN over 40-80µin NICKEL
- INSULATORS: HIGH TEMPERATURE PLASTIC UL 94 V-0, BLACK
- CONTACTS: COPPER ALLOY
PLATING: 8µin HARD GOLD over min. 50µin NICKEL
CONTACT TAILS PRETINNED
- METAL BRACKETS: ZINC DIE CAST; min. 300µin COPPER/40-120µin NICKEL/120-200µin TIN
- THREADED INSERTS: COPPER ALLOY; min. 200µin TIN over 80µin NICKEL
- CAPACITANCE: 2 x 830pF ± 20%
- DIELECTRIC WITHSTANDING VOLTAGE: 300 VDC
- P.C.B. HOLE DRILLINGS ON SHEET 2
- MAXIMUM TORQUE VALUE FOR THREAD: 6 in.LB
- CONNECTOR IS PART MARKED: 24-500663 CONEC ABC

Directive 2002/95/EC
RoHS
Compliant

APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL	
CUSTOMER APPROVAL DATE:	
NAME:	TITLE:
COMPANY NAME:	
APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL	

Customer Specific Product				tolerance		dim. in mm		scale: 2:1 (5:1)		
				material: SEE NOTES		title:				
DO NOT ALTER CAD DRAWING BY HAND				date	name	D-SUB π Filter Male 90° 15pos. 0,590inch threaded insert and metal bracket				
				drawn	04.05.09					Sonnenberg
				appd.	04.05.09					Koch
				norm	DIN 41652					
a Origin				d-old		dwg no:		Inventor 10	DIN-A3	
				rev. description date name		24K1A1175		sh: 1		
						part no:		24-500663		



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CONEC:](#)

[24-500663](#)