






NOTES:

CRIMPING:
USE CRIMP TOOL: 360X10409X
WITH TOOL INSERT: 360X20029X
SELECTOR SETTINGS: 5 FOR AWG 12
4 FOR AWG 14

plating	part no.
GOLD FLASH over NICKEL	132A11029X
30µin HARD GOLD over min. 50µin NICKEL	132C11029X
50µin HARD GOLD over min. 50µin NICKEL	132J11029X

RoHS compliant

STRIPPING DIMENSIONS



3	1	RETAINING RING	COPPER ALLOY	NICKEL PLATED
2	1	REAR SIDE	COPPER ALLOY	GOLD FLASH over NICKEL
1	1	MATING SIDE	COPPER ALLOY	see table
pos	qty	description	material	plating
partlist				
tolerance			dim. in mm	scale: 5:1
				material: see notes
			date	name
			drawn	26.07.06 Lehmenkühler
			appd.	26.07.06 Kühle
			norm	
4 x c	Ä5997	22.02.16	K.H.	d-old 13K1IE8A/13K1A188A
2 x b	Ä3554	19.01.11	K.H.	
a	Origin			
rev.	description	date	name	
title: HIGH POWER CONTACT FEMALE CRIMP VERSION 20A D-SUB COMBINATION				
dwg no: 13K1A1836				DIN-A3
part no: see table				sh: 1

CONEC

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CONEC:](#)

[132A11029X](#)