






P.C.B. HOLE DRILLINGS



(b) INCLUDED IN DELIVERY: 2 x SCREW
2 x WASHER

NOTES:

- METALSHELLS: STEEL; min. 320µ" TIN
- INSULATORS: PBT GF UL 94 V-0, BLACK
- HIGH POWER PRESS-FIT CONTACTS 30A: COPPER ALLOY
PCB HOLE Ø3.111 max. / Ø2.959 min.
PCB-THICKNESS min. 2mm
PLATING-MATING SIDE: min. 30µ" HARD GOLD OVER min. 50µ" NICKEL
PLATING-REAR SIDE: min. 80µ" TIN OVER min. 50µ" NICKEL
- THREADED REAR SPACER/FRONT THREADED LOCK:
COPPER ALLOY; min. 200µ" TIN over 80µ" NICKEL
- SLEEVE: COPPER ALLOY; min. 200µ" TIN over 80µ" NICKEL
- SCREW: STEEL, NICKEL PLATED
- SPRING RING: STEEL, NICKEL PLATED
- CAPACITANCE: 100nF ±20%
- DIELECTRIC WITHSTANDING VOLTAGE: 707 VDC
- MAXIMUM TORQUE VALUE FOR THREAD: 6" LBS
- CONNECTOR IS PART MARKED: 3F3SPC28SP1S90B CONEC Y/WW
- () = CHECK DIMENSION

APPROVAL * FREIGABE * DEBLOCAGE * AUTOR/ZACON * APPROVAL	
CUSTOMER APPROVAL DATE:	
NAME:	TITLE:
COMPANY NAME:	
APPROVAL * FREIGABE * DEBLOCAGE * AUTOR/ZACON * APPROVAL	

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH
DO NOT ALTER CAD DRAWING BY HAND

rev.	description	date	name
3 x b	Ä 1904	18.12.2003	Lehmen

tolerance	dim. in mm
2003	date
drawn	09.12. Lehmenkübler
appd.	09.12. Mickenbecker
norm	
d-old	

scale:	2:1 (5:1)
material:	SEE NOTES
title:	D-SUB FILTER COMBINATION MALE 3W3P threaded rear spacer, front threaded lock
dwg no:	AutoCAD 2000 DIN-A 24K1A492 3 sh: 1/1
part no:	3F3SPC28SP1S90B

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CONEC:](#)

[3F3SPC28SP1S90B](#)