


D see data sheet cable

Technical specification:

Rated voltage: IEC 61076-2-101	5pos 60 V
Current rating: IEC 61076-2-101	4 A at 40°C
Insulation resistance: IEC 60512	$\geq 100 \text{ M}\Omega$
Pollution degree: IEC 60664-1	3/2
Degree of protection: DIN 40050-9	IP 69K, in mated condition
Temperature range: IEC 60664-1	-30°C ... +105°C
Mating cycles: IEC 60512-9a	≥ 100

Materials:

Contact:	CuZn
Contact plating:	Nickel, gold plated
Contact carrier:	Thermoplastic GF, UL 94
Coupling screw:	1.4404 stainless steel
Moulding body:	Thermoplastic elastomere, grey

Installation specification:


Recommended torque:	0,6 Nm
---------------------	--------

Contact assignment:

1	brown
2	white
3	blue
4	black
5	green-yellow

Part no:	Description:	Length L:	Cable:
43-14828	SAL - FB - 12 - RSW5 - 2 / P1 / A1090	2m	PP, orange, 5x0,34mm ² Cable: 781-P13500
43-14829	SAL - FB - 12 - RSW5 - 3 / P1 / A1090	3m	
43-14830	SAL - FB - 12 - RSW5 - 5 / P1 / A1090	5m	
43-14831	SAL - FB - 12 - RSW5 - 10 / P1 / A1090	10m	
43-xxxxx	SAL - FB - 12 - RSW5 - ... / P1 / A1090	x	

DO NOT ALTER CAD DRAWING BY HAND
Directive 2002/95/EC RoHS compliant

		 dim. in mm		title: Male connector M12x1 angled, FB	
		date	name		
tolerance of cable: L <= 4m: L + 40mm L > 4m: L + 1%		drawn 28.02.11	Franz		
		appd. 28.02.11	Mankopf	dwg no:	
general tolerance: 0 ± 0,50mm 0,0 ± 0,25mm 0,00 ± 0,10mm				43K1A1322	
THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH				part no: see table	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CONEC:](#)

[43-14831](#)