


D see data sheet cable

Technical specification :

Rated voltage: IEC 61076-2-101	3pos 250 V
Current rating: IEC 61076-2-101	4 A at 40°C
Insulation resistance: IEC 60512	$\geq 100 \text{ M}\Omega$
Pollution degree: IEC 60664-1	3/2
Degree of protection: IEC 60529	IP 67, in mated condition
Temperature range: IEC 60664-1	-30°C ... +80°C
Mating cycles: IEC 60512-9a	≥ 100

Materials:

Contact:	CuZn
Contact plating:	Nickel, gold plated
Contact carrier:	TPU GF, UL 94
Sealing:	FPM
Coupling nut:	GD-Zn, nickel plated
Moulding body:	TPU, UL 94, grey

Installation specification:

Recommended torque:	0,6 Nm
Conec installation tool:	Torque wrench: 36-000200 Insert across flats 13: 36-000220

Contact assignment:

1)	brown
3)	blue
4)	black

Part no:	Description:	Length L:	Cable:
43-10016	SAL - 12 - RK3 - 2 / J1	2m	TPU, UL 20549, orange, 3x0,34mm ² Cable: 781-J13300
43-10017	SAL - 12 - RK3 - 3 / J1	3m	
43-10018	SAL - 12 - RK3 - 5 / J1	5m	
43-10019	SAL - 12 - RK3 - 10 / J1	10m	
43-xxxxx	SAL - 12 - RK3 - ... / J1	x	

DO NOT ALTER CAD DRAWING BY HAND Directive 2002/95/EC RoHS compliant	Index: b 11.01.11 VF Ä3767 Coupling nut modified, spanner flats added, data sheet modified	dim. in mm	
	tolerance of cable: L ≤ 4m: L + 40mm L > 4m: L + 1%	drawn	08.03.07 Fromm
	general tolerance: 0 ± 0,50mm 0,0 ± 0,25mm 0,00 ± 0,10mm	appd.	08.03.07 Mankopf
	THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH		
	CONEC®		

title:
Female connector M12x1 axial

dwg no:
43K1A383

part no: see table

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

CONEC:

[43-10016](#) [43-10018](#) [43-10019](#) [43-10017](#)