





Technical specification:

Rated voltage: IEC 61076-2-101	6pos 30 V
Current rating: IEC 61076-2-101	2 A at 40°C
Insulation resistance: IEC 60512	>=100 MΩ
Pollution degree: IEC 60664-1	3/2
Degree of protection: IEC 60529	IP 67, in mated condition
Temperature range: IEC 60664-1	-30°C ... +80°C
Mating cycles: IEC 60512-9a	>=100
Materials:	
Contact:	CuZn
Contact plating:	Nickel, gold plated
Contact carrier:	TPU GF, UL 94
Sealing:	FPM
Coupling nut/ screw:	GD-Zn, nickel plated
Moulding body:	TPU, UL 94, grey
Installation specification:	
Recommended torque:	0,6 Nm
Conec installation tool:	Torque wrench: 36-000200 Insert across flats 13: 36-000220




Contact assignment:

1) brown	4) black
2) white	6) grey
3) blue	7) pink



D see data sheet cable

Part no:	Description:	Length L:	Cable:
43-14629	SAL - 12 - RK6 - RSW6 - 0,3 / A1 / A1090	0,3m	PVC, grey, 6x0,25mm ² Cable: 781-A12600
43-14630	SAL - 12 - RK6 - RSW6 - 0,6 / A1 / A1090	0,6m	
43-14631	SAL - 12 - RK6 - RSW6 - 1,5 / A1 / A1090	1,5m	
43-14632	SAL - 12 - RK6 - RSW6 - 3,0 / A1 / A1090	3m	
43-xxxxx	SAL - 12 - RK6 - RSW6 - ... / A1 / A1090	x	

DO NOT ALTER CAD DRAWING BY HAND Directive 2002/95/EC RoHS compliant	 dim. in mm	title: Connecting cable M12x1, female connector axial - male connector angled	
	tolerance of cable: L ≤ 4m: L + 40mm L > 4m: L + 1%	drawn	17.01.11 Franz
	THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH	appd.	17.01.11 Mankopf
		dwg no: 43K1A1283	
		part no: see table	



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

CONEC:

[43-14631](#) [43-14632](#) [43-14629](#) [43-14630](#)