




Technical specification:

Rated voltage: IEC 61076-2-101	60 V
Current rating: IEC 61076-2-101	4 A at 40°C
Insulation resistance: IEC 60512	>=100 MΩ
Pollution degree: IEC 60664-1	3/2
Degree of protection: IEC 60529	IP 67, in mated condition
Temperature range:	-30°C ... +80°C
Mating cycles: IEC 60512-9a	>=100

Materials:


Contact:	CuZn
Contact plating:	Nickel, gold plated
Contact carrier:	PA, UL 94
Sealing:	FPM
Coupling nut/ screw:	GD-Zn, nickel plated
Moulding body:	TPU, UL 94, grey

Installation specification:

Recommended torque:	0,6 Nm
Conec installation tool:	Torque wrench: 36-000200 Insert across flats 13: 36-000220

Contact assignment:

1) brown	■
2) white	■
3) blue	■
4) black	■
5) green-yellow	■



D see data sheet cable

Part no:	Description:	Length L:	Cable:
43-14625	SAL - 12 - RK5 - RSW5 - 0,3 / J1 / A1090	0,3m	TPU, UL 20549, orange, 5x0,34mm ² Cable: 781-J13500
43-14626	SAL - 12 - RK5 - RSW5 - 0,6 / J1 / A1090	0,6m	
43-14627	SAL - 12 - RK5 - RSW5 - 1,5 / J1 / A1090	1,5m	
43-14628	SAL - 12 - RK5 - RSW5 - 3,0 / J1 / A1090	3m	
43-xxxxx	SAL - 12 - RK5 - RSW5 - ... / J1 / A1090	x	

DO NOT ALTER CAD DRAWING BY HAND Directive 2011/65/EU RoHS compliant	Index a: 11.09.14 rbo Ä5343 Data sheet modified. contact carrier was PBT.	 dim. in mm		title: Connecting cable M12x1, female connector axial - male connector angled		
		date	name			
	tolerance of cable: L <= 4m: L + 40mm L > 4m: L + 1%	drawn	17.01.11	Franz	dwg no:	
		appd.	17.01.11	Mankopf		
	general tolerance: 0 ± 0,50mm 0,0 ± 0,25mm 0,00 ± 0,10mm				43K1A1282	
THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH	part no: see table					

CONEC®

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

CONEC:

[43-14626](#) [43-14625](#) [43-14627](#) [43-14628](#)