


Technical specification :

Rated voltage: IEC 61076-2-104	60 V
Current rating: IEC 61076-2-104	3 A at 40°C
Insulation resistance: IEC 60512	$\geq 100 \text{ M}\Omega$
Pollution degree: IEC 60664-1	3/2
Degree of protection: IEC 60529	IP 67, in mated condition
Temperature range: IEC 60664-1	-30°C ... +80°C
Mating cycles: IEC 60512-9a	≥ 100

Materials:

Contact:	CuZn
Contact plating:	Nickel, gold plated
Contact carrier:	TPU GF, UL 94
Coupling screw:	GD-Zn, nickel plated
Moulding body:	TPU, UL 94, grey

Installation specification:

Recommended torque:	0,4 Nm
Conec installation tool:	Torque wrench: 36-000200 Insert across flats 9: 36-000210

Contact assignment:

1	brown
3	blue
4	black

Part no:	Description:	Length L:	Cable:
42-10008	SAL - 8 - RS3 - 2 / A1	2m	PVC, grey, 3x0,25mm ² Cable: 781-A12300
42-10009	SAL - 8 - RS3 - 3 / A1	3m	
42-10010	SAL - 8 - RS3 - 5 / A1	5m	
42-10011	SAL - 8 - RS3 - 10 / A1	10m	
42-xxxxx	SAL - 8 - RS3 - ... / A1	x	

D see data sheet cable

DO NOT ALTER CAD DRAWING BY HAND Directive 2002/95/EC RoHS compliant	Index: a 16.03.2011 VF Ä3945 Coupling screw modified, spanner flats added, data sheet modified				dim. in mm		title: Male connector M8x1 axial		
				date	name				
	tolerance of cable:	L <= 4m: L + 40mm L > 4m: L + 1%		drawn	02.10.07	Franz		dwg no: 42K1A003	
				appd.	02.10.07	Mankopf			
	general tolerance:	0 ± 0,50mm 0,0 ± 0,25mm 0,00 ± 0,10mm					part no: see table		
		THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH							

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

CONEC:

[42-10011](#) [42-10009](#) [42-10008](#) [42-10010](#)