



SEE NOTE 4



No. of pos.	A	B	C	Part-NO.
2x 9	30.80	16.30	25.00	164A07039A
2x15	39.20	24.60	33.30	
2x25	53.10	38.30	47.10	
2x37	69.40	54.80	63.50	

## P.C.B. HOLE DRILLINGS






**NOTES:**

1. MATERIAL:  
SHELL: STEEL  
INSULATOR: PBT, RATED UL 94 V-0  
CONTACTS: COPPER ALLOY  
RIVET, BOARDLOCK: COPPER ALLOY
2. CONTACT PLATING:  
G = GOLD FLASH OVER 40pin NICKEL ON ALL AREA  
CONTACT AREA: GOLD FLASH (SEE PART NO.)
- ② SOLDER TAILS: GOLD FLASH OVER 40pin NICKEL
3. ELECTRICAL:  
OPERATION VOLTAGE: 250 V AC max.  
CURRENT RATING: 3 A max.  
CONTACT RESISTANCE: 25 M Ohm max.  
INSULATION RESISTANCE: 3000 M Ohm min. @ 500 V DC  
DIELECTRIC WITHSTANDING VOLTAGE: 1000 V AC / MINUTE  
OPERATING TEMPERATURE: -55°C TO +105°C
4. CONNECTOR IS PART MARKED: 

PART-NO.	CONEC	ABC
----------	-------	-----

APPROVAL # FREIGABE # DEBLOCKAGE # AUTOTRACION # APPROVAL	
CUSTOMER APPROVAL DATE:	
NAME:	TITLE:
COMPANY NAME:	
APPROVAL # FREIGABE # DEBLOCKAGE # AUTOTRACION # APPROVAL	

THIS DRAWING MAY NOT BE COPIED OR  
REPRODUCED IN ANY WAY, AND MAY NOT  
BE PASSED ON TO A THIRD PARTY WITHOUT  
WRITTEN PERMISSION.  
OWNERSHIP AND COPYRIGHT OF CONEC GmbH  
NOT ALTER CAD DRAWING BY HAND

				tolerance		 	
				2002	date	name	
				drawn	26.08.	Parei	
				appd.	27.08.	Resonnek	
				norm			
				d-old			
1 x b	Ä 3364	28.05.2009	Petker				
a	Origin						
rev.	description	date	name				



scale:	2:1	
material:	SEE NOTES	
title:	<p><b>D-SUB DUAL-PORT</b></p> <p>Female / Female 2x9pos. - 2x37pos.</p>	
dwg no:	AutoCAD 2000	DIN-A
16K1A738		3
		sh: 1/1
part no:	SEE TABLE	

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

CONEC:

164A07039A