



1. RoHS COMPLIANT
2. FOR WAVESOLDERING (SOLDER BATH TEMPERATURE 260 °C FOR 5 SEC.
AND SOLDER PREHEAT 100 °C FOR 30 SEC.)
3. METALSHELLS: STEEL; min. 315µin TIN over 40-80µin NICKEL
4. INSULATOR: HIGH TEMPERATURE PLASTIC UL 94 V-0; BLACK
5. CONTACTS: COPPER ALLOY
PLATING: GOLD FLASH over NICKEL
6. THREADED SPACER CLIPS: COPPER ALLOY; min. 200µin TIN over 80µin NICKEL
PCB-HOLE: $\varnothing 3,1 \pm 0,1$; PCB-THICKNESS 2,3mm
7. COLLARS: COPPER ALLOY; min. 200µin TIN over 80µin NICKEL
8. SEALING COMPOUND: PUR; BLUE
9. CAPACITANCE: 830pF $\pm 20\%$
10. DIELECTRIC WITHSTANDING VOLTAGE: 707 VDC

(b) 11. CONNECTOR IS PART MARKED: HFC3XSRAA19H831X CONEC ABC



Directive 2002/95/EC RoHS compliant

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION.

DO NOT ALTER CAD DRAWING BY HAND

				tolerance		 dim. in mm	
					date	name	
				drawn	22.11.10	Henneboel	
				appd.	22.11.10	Koch	
				norm			
				d-old			
1 x b	Ä3958	31.03.2011	K.H.				
a	Origin						
rev.	description	date	name				



scale:	2:1 (5:1)		
material:	see notes		
title: D-SUB HD C-FILTER FEMALE 44pos. SOLDER PIN STRAIGHT with threaded spacer clip			
dwg no:		Inventor 10	DIN- A3
24K1A1283		sh: 1	
part no:		HFC3XSRAA19H831X	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

CONEC:

[HFC3XSRAA19H831X](#)