



The easy Radio Intelligent Controller (eRIC) radio transceiver module is based on the Texas Instruments CC430F5137 System-on-Chip device to provide an intelligent radio sub-system that combines a high performance RF transceiver, RF band pass filters (BPF), an MSP430 microcontroller, 32Kb flash memory, non-volatile flash storage, temperature sensor, and a low drop voltage regulator. The device operates on the International licence exempt Industrial, Scientific and Medical (ISM) radio bands.

eRIC thus extends the proven easyRadio product line by offering a low cost RF transceiver intended for high volume applications. The compact form factor, surface mount packaging and external antenna connector simplify product design and manufacture and provide for

flexible placement of the module within an end product.

Features	Benefits
<ul style="list-style-type: none">• Default 'easyRadio' Protocol Embedded• ISM Frequency Bands• Radio Compliance• Small 15x20x2.2mm Surface Mount Device (SMD)• Low power operation modes• eROS Operating System & Application partitions• Configurable & programmable User I/O• AES 128 bit data encryption• Built in Temperature Sensor	<ul style="list-style-type: none">Simple serial data in/data out user interface and configuration433 & 868MHz (UK & Europe) & 915MHz (USA)Meets ETSI (Europe) & FCC Certified (USA) requirementsSimplifies product design and manufactureBattery powered applicationsCan eliminate need for external application processorMinimises external hardware requirements for custom applicationsSecure communicationsEnvironment monitor

easyRadio Operating System (eROS)

eRIC's processor memory is partitioned and embedded with a protected version of the easyRadio Operating System (eROS) that handles all the complex radio functions and thus eliminates the need for the user to program multiple control registers and understand their interaction. The other partition provides an optional user accessible application code area.

Radio parameters such as frequency, channel, output power and data rate are passed by the application code and radio data is sent and received in the background by simply calling predefined functions.

Also provided is a simple to use API that replaces low level chip specific code with intuitive pin commands that allow the multiple general purpose I/O pins and internal function blocks to be configured and interfaced to external hardware. These built in functions make customisation easy for the novice and powerful for advanced programmers. This architecture can eliminate the need for a separate application microcontroller and thus minimises cost and power consumption for simple 'sense and control' RF nodes such as might be employed within the 'Internet of Things'.

By default (factory settings) the application code area is pre-programmed with a subset of the familiar easyRadio command and communication software that allows key operating parameters such as operating frequency, RF power output and host communication settings to be (optionally) pre-configured using the 'easyRadio Companion' software or to be dynamically changed using simple serial commands sent from the host processor. This allows multiple eRIC devices to communicate free from interference with each other and other local RF devices.

In the default application mode, data is sent to and received from host processors or devices using 3.3V logic level serial data (inverted) with packet sizes up to 250 bytes.




Figure 1 eRIC Transceiver Block Diagram

Pin/Pad Description

Pad No	Name	Description	Notes
1	CD	Carrier Detect Digital output	Indicates presence of any RF carrier within the receiver bandwidth Idle – Low, Carrier Present – High Optional A-D Input
2	Busy	Clear to Send (CTS) function Digital output	Indicates that transceiver is ready to receive serial data from the Host. Low – Transceiver Ready, High – Transceiver not Ready Optional A-D Input
2 (Option)	RF Rx Data	Demodulated receiver data Digital output	Only active when RAW Data mode is enabled
3	SDO	Rx Serial Data Out (Default)	Digital output - Connect to Host serial input
4	SDI	Tx Serial Data In (Default)	Digital input - Connect to Host serial output
5	Host Ready	Request to Send (RTS) function Digital input	Used to indicate that Host is ready to receive serial data from the Transceiver Low – Host Ready, High – Host Not Ready Weak (35k) pull down enabled. Optional A-D Input
6	Vcc	Operating Supply Voltage	+2.4V to +6V. Supply should be 'clean', noise and ripple free
7	Gnd	Power Ground	0V Ground
8	JTAG	JTAG pins	Reserved Use – Do not connect
8	Bootloader Recovery	Using a specific sequence on Pin8, module can be recovered and set into bootloader mode using LPRS BSL (Boot Strap Loader).	Only available on modules manufactured in 2015 or on old modules which were upgraded using easyRadio Companion software 4.0.4 onwards. Connect Pin11 and Pin12 together first. On holding module in reset or holding Pin9 (Reset) low, toggle Pin8 4 times. After 4 toggles, hold Pin8 high and release reset or unground Pin9. This will set the module in recovery bootloader mode which is indicated by Pin17 going high. From this state module can be re-flashed or repaired with eROS and eRIC.
9	Reset	Reset & JTAG use	Restricted Use – Internal pull-up. Connect to Gnd for Reset
10	GPIO	General purpose digital I/O	
11, 12	GPIO	Bootloader & General purpose digital I/O	When connected together invokes the bootloader function on reset. Do not connect for normal operation.
11	Temporary Recovery	Resets module temporarily to UART 19200 and CPU 4500000Hz.	Only available in V1.5 onwards. If the module fails to respond, it can be temporarily recovered by holding Pin11 high on reset. This will temporarily reset module to UART 19200 and CPU 4500000Hz. At this point sending ER_CMD#R0 will reset the module to default settings and fix it.
13	GPIO	General purpose digital I/O	
14	GPIO	General purpose digital I/O	eRIC4 only – See variant below:
	Input	Frequency Select EU/US	eRIC9 only. Pin High - 869.75 MHz, Pin Low - 915.00MHz Internal pull-up enabled
15 - 21	GPIO	General purpose digital I/O	Mappable secondary function
22	GPIO	General purpose digital I/O	Optional A-D Input. Mappable secondary function



22	Interupt (Low to High)		Exit Low power modes
23	RF Gnd	RF Ground – 0V	Connect to antenna ground and local ground plane. Internally connected to Power Ground 0V
24	RF	50R RF Input/Output	Connect to suitable antenna via 50R PCB trace or use the alternative UFL connector

Notes

GPIO Pins/pads are configured (by default) on power up or Reset as Inputs with internal weak pull downs. Therefore, exercise caution when connecting to any external circuitry.

Pins/pad 1-7 are physically (pin/pad sequence) and electrically compatible with easyRadio eRA400/900 Transceivers.
Interrupt function available on Pins/pad 1, 2, 3, 4, 5, 22

Mappable functions are UART, SPI, I2C, TimerA, , Compare/Capture I/O, GD0.
See the eROS Developers Manual for further details and description of these functions.

**Absolute Maximum Ratings**

Operating Temperature Range	-40° C to +85° C
Storage Temperature Range	-40° C to +85° C
Supply Voltage - Vcc	-0.3 to +6.0 Volts
All Other Pins/Pads w.r.t 0V Gnd	-0.3 to +3.3 Volts
Antenna	50V p-p @ < 10MHz

Performance Data: Supply +3.6 Volt \pm 5%, Temperature 20° C

DC Parameters	Pin	Min	Typical	Max	Units	Notes
Supply Voltage (Vcc)	6	2.4	3.6	6.0	Volts	
Internal Regulator (Vreg)		2.95	3.3	3.65	Volts	
Transmit supply current	6		32	33	mA	+10dBm RF power output
Receive supply current	6		15		mA	Continuous mode @ 250kbps
Sleep Mode current	6		1.8		uA	TBA
Initial Power Up Time			5	50	mS	
Logic Levels						
Data Output Logic 1	All		3.1		Volts	10k load to 0V Gnd
Data Output Logic 0			0.1		Volts	10k load to internal +Vreg supply
Data Output Current		6		15	mA	Under software control Hi/Lo drive
Data Input Logic 1		2.0		3.6	Volts	
Data Input Logic 0		0		0.2	Volts	
Input Pull-ups/Downs			100		kΩ	Under software control To internal +Vreg or 0V Gnd
RF Parameters						
Antenna Impedance	24		50		Ohms	Via UFL connector or pads
Operating Frequency		389	434.00	470	MHz	See Configuration Command set
		779	869.75	902	MHz	
		902	915.00	928	MHz	
Modulation	FSK Wideband MSK at 500kbps					
Transmitter						
RF Power Output 434MHz	24	-30	Set by user	+12	dBm	50Ω load – 434MHz
RF Power Output 869MHz	24	-30	Set by user	+7	dBm	50Ω load – 869MHz
RF Power Output 915MHz	24	-30	Set by user	-3	dBm	50Ω load – 915MHz
Frequency Accuracy			±10	±15	ppm	Overall
FSK Deviation (Min)			±5.2		kHz	1.2kbps 58kHz filter bandwidth
FSK Deviation (Max)			±127		kHz	250kbps, 540kHz Filter bandwidth
Harmonics & Spurious Emissions	24		-47	< -36	dBm	Meets EN 300 220-3
Over Air Data Rate		1.2	38.4	500	Kbps	Configurable
Receiver						
Receive Sensitivity 433MHz	24		-111		dBm	At 1.2kbps Over Air data rate
868/915MHz	24		-109		dBm	At 1.2kbps Over Air data rate
434MHz	24		-91		dBm	At 500kbps Over Air data rate
868/915MHz	24		-81		dBm	At 500kbps Over Air data rate
Host Serial Data Rate	3, 4	2.4	19.2	115.2	Kbps	Host interface
Mechanical						
Size	15 x 20 x 2.2				mm	
Pin/Pad Pitch	2.54				mm	Standard 0.1 Inch
Weight	1.5				grams	
*All Specifications are subject to change without notice						



Notes

When power is first applied to the module the processor retrieves 'calibration' data for the RF section that compensates for temperature and power supply voltage variations. The transceiver will then be ready to transmit or receive (default) and would normally be left in this state, ready to receive data.

The internal Vreg is not brought out to a specific pin/pad. Should there be need to connect external pull up resistors then connection should be made to a spare GPIO pin/pad configured as a 'High' output.

Power Supply

The supply used to power the transceiver should be 'clean' and free from ripple and noise (<20mV p-p total). It is suggested that 100nF ceramic capacitors be used to de-couple the supply close to the power pins of the transceiver. The use of 'switch mode' power supplies should generally be avoided as they can generate both conducted and radiated high frequency noise that can be very difficult to eliminate. This noise may considerably reduce the performance of any radio device that is connected or adjacent to such a supply.

Antennas

The eRIC transceiver can be used with the various common types of antenna that match the 50Ω RF Input/Output such as a monopole (whip), a tuned helical antenna, a PCB loop antenna or a ceramic 'chip' antenna.

Monopole antennas are resonant with a length corresponding to one quarter of the electrical wavelength ($\lambda/4$). They are very easy to implement and can simply be a 'piece of wire' or PCB track which at 434MHz should be 16.4cms in length. This should be kept straight, in 'free space' and well away from all other circuitry, conducting objects and metalwork and should preferably be connected directly to the Antenna pin (24) of the eRIC transceiver.

If the antenna needs to be remote it should be connected via a 50Ω coaxial feeder cable or transmission line. A 50Ω transmission line can be constructed on FR4 board material by using a 3mm wide PCB track over a ground plane and this should be kept as short as possible.

The eRIC transceiver is also fitted with UFL (U.FL) RF Connector wired in parallel with pin 23 (RF Gnd) and pin 24 (RF In/Out). LPRS can supply suitable antennas fitted with matching connectors and low loss cable assemblies.


Helical antennas are also resonant and generally chosen for their more compact dimensions. They are more difficult to optimise than monopole antennas and are critical with regard to any surrounding conducting objects that can easily 'de-tune' them. They operate most efficiently when there is a substantial ground plane for them to radiate against.

PCB loop antennas are the most compact antennas but are less effective than the other types. They are also more difficult to design and must be carefully 'tuned' for best performance.

Chip antennas are attractive as they are compact and if used in accordance with the manufacturer's specifications can provide very good performance.

The Internet can provide much useful information on the design of Short Range Device (SRD) Antennas.


Please Note: To meet US FCC requirements the modules must be used with the specified antennas (TBA) that were used for testing.

**Mechanical****Figure 2 Mechanical Drawing****PCB Layout Notes**


Pitch of the castellated connection pads is 2.54mm. Pads 4 & 16 and 10 & 22 are on centre line (C/L) of module

It is recommended that the module is mounted on a double sided PCB and that the area below the module be flooded with additional copper ground plane. This should be connected to pad 23 (RF Ground) and pad 7 (Power Gnd).

The recommended pad layout is shown below. Pads should be solid with no hole.



eRIC is designed for reflow soldering. Please contact LPRS Technical Department for further details and the suggested thermal profiles.

**Interface to Microcontroller****Figure 3 Connection to Host UART and I/O Protection**

The transceiver module is powered internally by an on board 3.3V low drop voltage regulator. Any eRIC pin/pad configured as an input should not be connected directly to a voltage greater than 3.3V or less than -0.3V otherwise damage may occur to the module due to excess current flowing through the IC internal protection diodes. To prevent such damage this current should be limited by the use of a suitable (10k typical) series resistor (as shown above).

eRIC output pins can only provide a maximum high voltage of 3.3V (Vreg) and whilst not strictly necessary to use a series resistor in series with outputs it may afford protection under some fault conditions.

The serial data input (or any other pin) must NOT be directly connected to any RS232 level ($\pm 15V$) devices.

Serial data is inverted i.e. Start Bit is logic low. This allows direct connection to a microcontroller UART (Inverted data) or to RS232 devices via a voltage level translator device such as a Maxim MAX232, which invert the logic of the RS232 signals. Data is sent and received in standard serial 'RS232' format (logic level only) and there is no restriction on the characters (Hex 00 – FF) that may be sent or received.

The host should provide serial data input and output lines. The optional 'handshaking' lines can be used to control the flow of data between the host and eRIC. If handshaking is not being used then Pin5 (Host Ready) should either be left floating (internal pull down) or held low. The 'Host Ready Input' Pin5 should be tied to 0 Volt (Ground) if not used, only when handshaking is enabled.

The 'Busy' output line, when active, indicates that the transceiver is undertaking an internal task and is not ready to receive serial data. The 'Host Ready' input is used to indicate that the host is ready to receive the data held in the buffer of the easyRadio Transceiver. The host should check before sending data that the 'Busy' line is not high, as this would indicate that the transceiver is unable to reliably receive further data. It should also pull the 'Host Ready' line to receive data.

The 'Busy' output is active all the time regardless of handshaking setting. The 'Host Ready' is enabled by the handshaking setting.



Serial Data Timing




Figure 4 System Block Diagram




Figure 5 Timing Diagram

Parameter	Values	Notes
Host Serial Data Rate	1200, 2400, 4800, 9600, 19200, 38400 & 115200 baud	Configurable – Default = 19200 baud
Host Character Format	1 Start bit, 8 Data bits, No Parity, 1 Stop bit	10 bits @ 104uS/bit = 0.52mS/character at 19200 baud
'End of Data' Delay	2 x Baud Byte duration	Twice character time
RF Transmit Duration	Depends on over air RF data rate Default - 38400 bps	See drawing. Between 2 & 4 bytes of Preamble and other internal data are automatically added to every packet
Buffer Size	1-250 bytes maximum	

Notes

The serial data internal buffer size is limited to a maximum of 250 bytes. Data will be lost if more than 250 bytes are sent in any one transmission. RF transmission begins automatically when the buffer is full or when 'End of Data' (no data for twice the character time) is detected.

- Host (A) sends serial data to eRIC (A). The data must be continuously streamed (no breaks) at the selected host baud rate and is loaded into an internal transmit buffer.
- After detecting either the 'End of Data' gap or the 'Buffer Full' condition the controller enables the RF transmitter circuitry of the transceiver and sends the data within the buffer together with preamble and other internal data across the RF link. Any eRIC transceiver operating in receive mode and within range that 'hears' the transmission will receive and decode the data, check for data integrity and place it into their receive buffers.
- Data within the receive buffer of eRIC (B) will be sent to Host (B) at the selected baud rate.

Host (A) must allow time for the complete 'Over Air' transmission and for the receiving Host (B) to unload (and process) the data before sending new data. (See Figure 5). There is no automatic 'RF handshaking' provided by the eRIC transceivers. Radio transmission and reception is bi-directional (half duplex) i.e. transmit OR receive (but not simultaneously) and there is no automatic confirmation of the satisfactory reception of the data.

The user application should therefore, either send the data repetitively to provide some redundancy or devise a scheme of acknowledgements (ACKs) and re-tries to increase the security and reliability of the transmitted data should need be.



easyRadio eRIC Configuration Command Set

Key operating parameters of eRIC can be changed and configured by sending the 'text' (ASCII character) commands detailed below. These commands can be executed using 'easyRadio Companion' software, any 'Terminal' software operating on a PC or from the host microcontroller.

The commands should be sent exactly as shown: i.e. case sensitive with no spaces between characters. Commands are not executed until the Acknowledgement (ACK) sequence is sent to and processed by the module.

To send the commands follow this procedure:

1. Send Command from host: e.g. ER_CMD#U5 (Set UART BAUD to 38400)
2. Wait for the completion of the echo of the Command from the module. e.g. ER_CMD#U5
3. Send the ACK command as the three upper case ASCII characters 'A' 'C' 'K' in sequence with no spaces

Host Serial Communication Settings							
Command	UART Data Rate						Note
ER_CMD#U1	2400						
ER_CMD#U2	4800						
ER_CMD#U3	9600						
ER_CMD#U4	19200	✓	Tick indicates Factory Default setting				
ER_CMD#U5	38400						
ER_CMD#U8	115200						
ER_CMD#U?	Get UART Value		Returns the current UART value E.g. ER_CMD#U2 - No 'ACK' is required				
Transmit RF Power Settings							
			eRIC4 433MHz	eRIC9 869.75 – 870MHz	eRIC9 902 – 928 MHz	eRIC9 Other frequencies	Units
ER_CMD#P0	Minimum Power		0	-2	-12	0	dBm
ER_CMD#P1			1	-1	-11	1	dBm
ER_CMD#P2			2	0	-10	2	dBm
ER_CMD#P3			3	1	-9	3	dBm
ER_CMD#P4			4	2	-8	4	dBm
ER_CMD#P5			5	3	-7	5	dBm
ER_CMD#P6			6	4	-6	6	dBm
ER_CMD#P7			7	5	-5	7	dBm
ER_CMD#P8			8	6	-4	8	dBm
ER_CMD#P9	Maximum Power	✓	9	7	-3	9	dBm
ER_CMD#P?	Get RF Power output value		Returns the current RF power output value E.g. ER_CMD#P9 No ACK is required				
RF Channel Settings							
ER_CMD#Cx	Where x = Channel Number in Decimal. Only channels (0-9) implemented at present.		E.g. For Channel 5 – 434.500MHz For Channel 5 – 870.250MHz For Channel 5 – 915.500MHz				
ER_CMD#C0		✓	Sets base frequency to: 434.000MHz, 869.75MHz, 915.000MHz				
ER_CMD#C1-8			Set intermediate frequency values at 100kHz steps				
ER_CMD#C9			Sets frequency to 434.900MHz (434.000 + 900KHz)				
ER_CMD#C?	Get Channel Value		Returns the current channel setting E.g. ER_CMD#C9 - No ACK is required				
RF Frequency Settings							
ER_CMD#F xxxxxxxx	Set Absolute Frequency		Sets the absolute frequency to xxxxxxxx in Hex E.g. ER_CMD#F1B4C8680 sets the radio frequency to 458000000Hz.				
ER_CMD#F?	Get current Frequency value		Returns the current frequency value as 8 bytes of Hex E.g. ER_CMD#F? Returns 1B4C8680 which is 458MHz				
CPU Frequency Settings							
ER_CMD#f xxxxxxxx	Set Absolute CPU Frequency		Sets the absolute CPU frequency to xxxxxxxx in Hex E.g. ER_CMD#f0044AA20 sets the CPU frequency to 4500000Hz. Frequencies can be 10kHz, 20kHz, 32768Hz, 40kHz, 50kHz, 60kHz and anything from 70kHz-20Mhz				
ER_CMD#f?	Get current CPU Frequency value		Returns the current frequency value as 8 bytes of Hex E.g. ER_CMD#f? Returns 0044AA20 which is 4.5MHz				
Over-Air Data Rate							
ER_CMD#B0			1200 bps				
ER_CMD#B1			2400 bps				



ER_CMD#B2			4800 bps	
ER_CMD#B3			9600 bps	
ER_CMD#B4			19200 bps	
ER_CMD#B5		✓	38400 bps (Default)	
ER_CMD#B6			76800 bps	
ER_CMD#B7			100000 bps	
ER_CMD#B8			250000 bps	
ER_CMD#B9			500000 bps	
ER_CMD#B?	Get the Over-Air Data Rate value		Returns the current Over-Air data rate value as command setting value E.g. ER_CMD#B5 - not the integer bps value No ACK is required	
Radio Receive - Power Saving				
	On Time		Typical Average Receiver Current	
ER_CMD#D0	100%	✓	16mA (Default)	VI.1
ER_CMD#D1	12.50%		2mA	VI.1
ER_CMD#D2	6.25%		1mA	VI.1
ER_CMD#D3	3.33%		500uA	VI.1
ER_CMD#D4	1.56%		250uA	VI.1
ER_CMD#D5	0.78%		125uA	VI.1
ER_CMD#D6	0.39%		63uA	VI.1
ER_CMD#D7	0.20%		32uA	VI.1
ER_CMD#D8	0%		Radio receiver is completely disabled and turned off. Radio stays in Idle and Sleep mode and only turns on to transmit data when requested	VI.5
Radio Transmit - Power Saving				
ER_CMD#d0		✓	This setting must be used in conjunction with the receive power saving setting: ER_CMD#dx >= ER_CMD#Dx N.B. If the receiver is set by command ER_CMD#D4, the communication would fail if transmitter is set with command less than ER_CMD#d4. It will only work if the transmitter is set with command ER_CMD#d4 or above	VI.1
ER_CMD#d8			Radio goes into Idle and Sleep mode even if ER_CMD#D7 is set	VI.5
Group ID Settings				
ER_CMD#L7 xxxx	Enable Group ID (2 bytes)		E.g. ER_CMD#L74578 sets the group ID as 0x4578	VI.1
ER_CMD#L7 0000	Disable Group ID			VI.1
ER_CMD#L7?	Get Group ID value		Returns the 4 byte Group ID number in Hex	VI.1
EEPROM Settings				
ER_CMD#L8?	Get the Serial Number of the module		Returns the unique 4 byte module Serial Number in Hex E.g. 40000056	VI.1
ER_CMD#L4 xxxx	Writes data to EEPROM at location xx		E.g. ER_CMD#L4FE2A - Write the data 0x2A at EEPROM address 0xFE Where xxxx is the address followed by the data in hexadecimal	VI.1
ER_CMD#L4 xx?	Returns the data located at EEPROM address xx		E.g. ER_CMD#L4FE? Returns data as 0x2A Where xx is the EEPROM address in hexadecimal from 0-FF EEPROM is only 256Bytes and ranges from 0x00-0xFF	VI.1
Miscellaneous Settings				
ER_CMD#R0	Reset Radio		Reset all the radio settings and retrieve all the (Default) radio settings P9, C0, D0, d0, U5, B5, L70000, A10, A20, Z00,	
ER_CMD#R1	Power On Reset(POR)		Software Power On Reset (POR) and restart the radio with previously stored settings	VI.5
ER_CMD#R2	Bootloader Mode		Enables bootloader mode and firmware can be upgraded using UART on Pin3 and Pin4	VI.5
Test Modes				
ER_CMD#T0	Upper FSK		Transmit continuous upper FSK Carrier	
ER_CMD#T1			Transmit continuous modulated Carrier at selected Over Air data rate.	
ER_CMD#T1U			Transmit continuous Un-calibrated modulated Carrier at selected Over Air data rate.	VI.4
ER_CMD#T2	Lower FSK		Transmit continuous lower FSK Carrier	
ER_CMD#T3	Get Firmware Revision		Returns firmware revision string in ASCII e.g. eRIC400xxxx	
ER_CMD#T4	RAW Data mode		Output the demodulated received data on Pin 2	
ER_CMD#T5	Packet Mode		Set the radio into normal packet data mode	VI.1



ER_CMD#T6	Carrier Off		End any continuous transmit modes	
ER_CMD#T7	Get Temperature		Returns internal chip temperature in decimal Degrees C. e.g. 20.5°C	
ER_CMD#T8	Last Packet RSSI		Returns the Received Signal Strength Indication (RSSI) of the last packet in dBm with sign (only in Packet Mode) e.g. -74dBm	VI.1
ER_CMD#T9	Get live RSSI		Returns the live RSSI value in dBm with sign e.g. -102dBm	
AES Encryption Settings				
ER_CMD#A1xy xxxxxxxxxxxx xxxxxxxxxxxx y	Set AES command		Where; x = 0 AES disabled x = 1 AES enabled with both encryption and decryption x = 2 AES encryption only enabled x = 3 AES decryption only enabled y = 32 character encryption key For example to set AES as encryption with key (0123456789ABCDEF0123456789ABCDEF) the command should be: ER_CMD#A110123456789ABCDEF0123456789ABCDEF (AES is enabled with both encryption and decryption) ER_CMD#A120123456789ABCDEF0123456789ABCDEF (AES is enabled with only encryption) ER_CMD#A130123456789ABCDEF0123456789ABCDEF (AES is enabled with only decryption) ER_CMD#A10. (AES encryption and decryption Off)	VI.5
ER_CMD#A1?	Returns the current AES settings		Returns with ER_CMD#A1x where x = 0, 1, 2, or 3	VI.5
Low Power Mode Settings				
ER_CMD#A21			eRIC_LPM_Level0() is enabled. Clock is set to 1048576Hz and D7 (RxPower level) is enabled. Pin22 is set as Interrupt to exit this mode. All other interrupts are disabled except UART, Pin22 and Radio. eRIC can send data, receive data and update settings. Current consumption ~180uA	VI.5
ER_CMD#A22			eRIC_LPM_Level1() is enabled. Clock is set to 32768Hz and D7 (RxPower level) is enabled. Pin22 is set as Interrupt to exit this mode. All other interrupts are disabled except UART, Pin22 and Radio. eRIC can send data and receive data. Can also update settings but may struggle to update EEPROM and other settings as clock is on low speed. Current consumption ~37uA. If ER_CMD#D8 (Radio receiver Off) and ER_CMD#d8 is used (Can send data but not receive data) Current consumption ~6uA	VI.5
ER_CMD#A23			eRIC_LPM_Level2() is enabled. All clocks are turned off. Radio is off. Pin22 interrupt is enabled to exit this mode. Current consumption ~2uA	VI.5
ER_CMD#A2?	Returns the current low power mode			VI.5
Handshake Settings				
ER_CMD#A50	Handshaking Off	✓	(Default)	VI.5
ER_CMD#A51	Handshaking On		(Pin2 CTS, Pin5 RTS) See notes	VI.5
ER_CMD#A5?	Returns current Handshake setting			VI.5
Carrier Mode Settings				
ER_CMD#Z01	High side Carrier Mode On		On start up or reset Used mainly for FCC testing purposes	VI.5
ER_CMD#Z02	Modulated Carrier Mode On		On start up or reset Used mainly for FCC testing purposes	VI.5
ER_CMD#Z03	Low side Carrier Mode On		On start up or reset Used mainly for FCC testing purposes	VI.5
ER_CMD#Z00	No Carrier Mode	✓	On start up or reset. (Default)	VI.5
ER_CMD#Z0?	Returns Carrier Mode		Returns with ER_CMD#Z00 or 1, 2, 3	VI.5
eRIC EEPROM Locations and Data Stored				
Address 0	Reset parameters		If this data is less than 2 or 0xFF then the eRIC module is reset to default settings	VI.5
Address 1	CurrentDataRate		0-9 0 = 1200 and 9 = 500000bps	VI.5
Address 2	CurrentChannel		0-9	VI.5
Address 3	CurrentPowerLevel		0-9	VI.5
Address 4	CurrentUartBaud		0-9 0 = 1200 and 8 = 115200bps	VI.5



Address 5	CurrentRxPowerLevel	0-8 0 = Radio completely On 8 = Radio completely Off	V1.5
Address 6	CurrentTxPowerLevel	0-8	V1.5
Address 7, 8, 9, 10	CurrentFrequency	In hex. 43400000hz(0x19DE5080) will be stored as 19,DE,50,80 at these locations	V1.5
Address 11, 12	CurrentGroupID	In hex	V1.5
Address 13	CurrentAESHasEnabled	0 - if AES is disabled 1 - if both AES encryption and decryption are enabled 2 - if only AES encryption is enabled 3 - if only AES decryption is enabled	V1.5
Address 14, 15, 16, 17	CurrentCpuFrequency	In hex 4500000hz(0x0044AA20) will be stored as 00,44,AA,20	V1.5
Address 18	CurrentLPMLevel	0 - Low power mode off 1 - Cpu set at 1048676Hz, eRIC_RxPowerLevel = 7 Total current consumption \approx 180uA 2 - Cpu set at 32768Hz, eRIC_RxPowerLevel = 7 Total current consumption \approx 37uA If eRIC_RxPowerLevel = 8 is set Total current consumption \approx 6uA 3 - Clocks all Off, Radio Off, UART Off Total current consumption \approx 2uA	V1.5
Address 19	CurrentCarrierMode	0 - No carrier On, on reset. 1 - High side carrier On, on reset 2 - Modulated carrier On, on reset 3 - Low side carrier On, on reset	V1.5
Address 20-29	CurrentPowerLevel	Power levels 0-9 in exact dBm which are selected by EEprom Address 3 For example: If EEprom Address 3 is set as 9 and if we modify Address 29(0x1D) to -30dBm which is 0xE2 then Powerlevel 9 will be at -30dBm I.e. ER_CMD#P9 will set radio to -30dBm	V1.5
Address 30	CurrentHandshaking	0 - Handshaking disabled 1 - Handshaking enabled	V1.5

Notes

**Product Order Codes**

Name	Description	Frequency	Order Code
eRIC400	UK/European Transceiver Module (Can Marked '4')	433MHz	eRIC4
eRIC900	Europe/US Transceiver Module (Can Marked '9')	868/915MHz	eRIC9
eRIC Dev Kit	eRIC Development Kit including two eRIC400 modules	433MHz	eRIC4-DK
eRIC Dev Kit	eRIC Development Kit including two eRIC900 modules	868/915MHz	eRIC9-DK

Document History

Issue	Date	Notes/Comments
Preliminary 0.1 to 0.2	July 2013	Preliminary internal drafts
Preliminary 0.30 to 0.36	July/August 2013	Additions, amendments and minor corrections
VI.0	January 2014	First release
VI.1	June 2014	Additions and minor corrections
VI.2	May 2015	Additions, low power modes, EEprom data added

Copyright

The information contained in this data sheet is the property of Low Power Radio Solutions Ltd and copyright is vested in them with all rights reserved. Under copyright law this documentation may not be copied, photocopied, reproduced, translated or reduced to any electronic medium or machine readable form in whole or in part without the written consent of Low Power Radio Solutions Ltd.
The circuitry and design of the modules are also protected by copyright law.

Disclaimer

Low Power Radio Solutions Ltd has an on-going policy to improve the performance and reliability of their products; we therefore reserve the right to make changes without notice. The information contained in this data sheet is believed to be accurate however we do not assume any responsibility for errors or any liability arising from the application or use of any product or circuit described herein. This data sheet neither states nor implies warranty of any kind, including fitness for any particular application.

easyRadio modules are a component part of an end system product and should be treated as such. Testing to fitness and field testing is the sole responsibility of the manufacturer of the device into which easyRadio products are fitted. Any liability from defect or malfunction is limited to the replacement of product ONLY, and does not include labour or other incurred corrective expenses. Using or continuing to use these devices hereby binds the user to these terms.



Low Power Radio Solutions Ltd.
Two Rivers Industrial Estate
Station Lane, Witney
Oxon, OX28 4BH
England

Tel: +44 (0)1993 709418
Fax: +44 (0)1993 708575
Web: <http://www.lprs.co.uk>
Email: info@lprs.co.uk
Technical: technical@lprs.co.uk

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[LPRS:](#)
[eRIC4](#)