




(c) (d)




(d) (b) NOTES:

CRIMPING:
USE CRIMP TOOL: 360X10409X
WITH TOOL INSERT: 360X20029X
SELECTOR SETTINGS: 7 FOR AWG 10
6 FOR AWG 12

plating	part no.
GOLD FLASH over NICKEL	132A11039X
30µin HARD GOLD over min. 50µin NICKEL	132C11039X
50µin HARD GOLD over min. 50µin NICKEL	132J11039X

(b) STRIPPING DIMENSIONS



RoHS compliant

(d)

3	1	RETAINING RING	COPPER ALLOY	NICKEL PLATED
2	1	REAR SIDE	COPPER ALLOY	GOLD FLASH over NICKEL
1	1	MATING SIDE	COPPER ALLOY	see table
pos	qty	description	material	plating
partlist				
tolerance			dim. in mm	scale: 5:1
			material:	see partlist
			title:	HIGH POWER CONTACT FEMALE
				CRIMP VERSION 30A
				D-SUB COMBINATION
			dwg no:	13K11E9A
			part no:	see table
			DIN-A3	sh: 1

4 x d	Å5877	09.11.2015	K.H.	norm	
1 x c	Å2197	01.04.2005	Lehm.	d-old	13K21E9A
2 x b	Å2177	02.03.2005	Lehm.		
a	Original				
rev.	description	date	name		

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH

DO NOT ALTER CAD DRAWING BY HAND

CONEC®

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CONEC:](#)

[132A11039X](#)