



Features

- * Universal Input 90~305VAC or 127-420Vdc
- * High Efficiency up to 90%
- * Meets EN55015, EN61000-3-2 Class C
- * Meets EN61347-1, EN61347-2-13
- * Meets UL8750
- * Meets UL1310 Class 2
- * Dimming Input Range 1%-100%
- * Active PFC Function
- * IP67 Design for Indoor or Outdoor Installations (note7)
- * Max. Output power 60W
- * Dimming function: 1-10Vdc and Resistance or DALI (Optional)
- * Protections: Short Circuit, Over Current Over Voltage and Over Temperature
- * Constant Voltage and Constant Current
- * No Load Power Consumption < 0.5W (note10)
- * 3 Years Warranty

LDM60 Series

LDM60S SERIES 60 WATT SINGLE OUTPUT AC-DC LED DRIVER



MODEL	Output Voltage	Output Current Note.6	Ripple (mV p-p) Note.1	Voltage Accuracy Note.2	Line Regulation Note.3	Load Regulation Note.4	Constant Current Region	Current Adj. Rang (Optional) Note.5	Voltage Adj. Rang (Optional) Note.5	%EFF. (Typ.) Note.8
LDM60S120	12V	5.00A	120mV	±1%	±1%	±2%	6.5V~11.5V	3A~5A	10.8V~13.2V	87%
LDM60S240	24V	2.50A	120mV	±1%	±1%	±2%	13V~23.5V	1.5A~2.5A	21.6V~26.4V	88%
LDM60S360	36V	1.67A	120mV	±1%	±1%	±2%	19V~35.5V	1.0A~1.67A	32.4V~39.6V	89%
LDM60S480	48V	1.25A	120mV	±1%	±1%	±2%	26V~47.5V	0.75A~1.25A	43.2V~52.8V	90%

Ordering information

Model No. Optional type

LDM60SXXX -XX

Optional type:

01: Constant Current Mode (IP67)

- No dimming
- No adjustment for output voltage and output current

02: Constant Current Mode (IP65)

- No dimming
- With adjustment for output voltage and output current

03: Constant Current Mode (IP67)

- Dimming: 1~10Vdc and Resistance
- No adjustment for output voltage and output current

04: Constant Current Mode (IP67)

- Dimming: DALI
- No adjustment for output voltage and output current

03A: Constant Current Mode (IP65)

- Dimming: 1~10Vdc and Resistance
- With adjustment for output voltage and output current

04A: Constant Current Mode (IP65)

- Dimming: DALI
- With adjustment for output voltage and output current

Specifications are subject to change without notice

Specifications

INPUT SPECIFICATIONS:

Voltage	90~305Vac or 127~420Vdc
Frequency	47 to 63Hz
Inrush Current	60A max. @240Vac, Cold Start @25°C
Conducted EMI	CISPR/FCC Class B
Power Factor	PF> = 0.9
Leakage Current	0.75mA max.@277Vac
Input Current	0.6A typ. @110Vac, Pout=59W 0.31A typ. @230Vac, Pout=59W

OUTPUT SPECIFICATIONS:

Holdup Time	16ms typ. @115Vac
Short Circuit Protection	Hiccup Mode (Auto Recover)
Temperature Coefficient	±0.05% / °C
Over Voltage Protection	TVS Component to Clamp
Over current Limit	constant current mode (note 9)
Over Temperature Protection	110°C typ
Altitude	2000m
Startup time	2.5s typ.
Rise time	50ms typ.
MTBF	MIL-HDBK-217F, GB, at 25°C /115VAC ...150Khrs typ.
Vibration	15~2000Hz 4G period for 60min, each along X Y Z axes

SAFETY AND EMC :



Emission and Immunity	EN55015, CISPR22 EN61547, EN61000-3-2, EN61000-3-3
Isolation Voltage	I/P-O/P 3750VAC
Surge	4KV
Safety	UL8750, UL1310 Class 2, EN61347-1, EN61347-2-13
Harmonic Current	EN61000-3-2 Class C (>60% load)
Isolation Resistance	100MQ min.

GENERAL SPECIFICATIONS:

Operating Temperature - 40 ~ 70°C (see Derating Curve)
Storage Temperature -40~85°C
Cooling Natural Convection

MECHANICAL CHARACTERISTICS:


Dimensions 8.149x1.5748x1.1023 Inches (207.00x40.00x28.00mm)
Weight 454g typ.



NOTE:

1. Add a 0.1uF ceramic capacitor and a 10uF E.L. capacitor to output for ripple noise measuring @20MHz BW and 95% rated current.
2. Line accuracy is set of 90% rated current.
3. Line regulation is measured from high line to low line with 90% rated current.
4. Load regulation is measured from 90% to 10% rated current.
5. Can be adjusted by internal potentiometer.
6. Output constant current accuracy $\pm 5\%$.
7. IP67 for model: LDM60SXXX-01, LDM60SXXX-03, LDM60SXXX-04
IP65 for model: LDM60SXXX-02, LDM60SXXX-03A, LDM60SXXX-04A
8. Efficiency is measured 95% rated power at $V_{in}=230VAC$.
9. Less than 50% (typ.) of the rated output voltage will enter hiccup mode.
10. No load power consumption<0.5W for LDM60SXXX-01,-02
No load power consumption<1.5W for LDM60SXXX-03, -03A, -04, -04A
Stand by power consumption<0.5W for LDM0SXXX-03, -03A, -04, -04A

Mechanical Specification



Typical at 25°C, nominal line and 75% load, unless otherwise Specified

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Cincon:

[LDM60S480-03](#) [LDM60S360-02](#) [LDM60S480-01](#) [LDM60S480-04](#) [LDM60S120-03](#) [LDM60S240-01](#) [LDM60S240-04](#)
[LDM60S240-03A](#) [LDM60S120-02](#) [LDM60S120-04](#) [LDM60S360-03A](#) [LDM60S360-01](#) [LDM60S120-01](#) [LDM60S480-](#)
[03A](#) [LDM60S360-04A](#) [LDM60S360-03](#) [LDM60S480-02](#) [LDM60S120-04A](#) [LDM60S240-04A](#) [LDM60S240-02](#)
[LDM60S480-04A](#) [LDM60S240-03](#) [LDM60S120-03A](#) [LDM60S360-04](#)