




TRE25RD SERIES

25W SWITCHING ADAPTER



Features

- * Miniature Size
- * Universal Input: 90~264Vac
- * Interchangeable AC Plugs
- * EMI Meets EN55032 Class B and CISPR/FCC Class B
- * Continuous Short Circuit Protection
- * Over Voltage Protection
- * No Load Power Consumption < 75mW
- * Approved IEC/EN/UL62368-1
- * Meet CoC V5 Tier 2 & DoE Level VI
(Output Cable Length $\leq$ 1800mm)
(TRE25RD050: Output Cable Length $\leq$ 1220mm)



Ordering Information

TRE25RDXXX -	X	XX	G	XX
Model No.	AC Plug Type	DC Plug Type	UL 1571 WITH OVP	DC Cable Length and Type
	A: USA 2 Pin			01: 720mm
	E: Europe 2 Pin			02: 1220mm
	U: British 3 Pin			03: 1800mm
	S: Australia 2 Pin			11: 720mm with Ferrite Core
				12: 1220mm with Ferrite Core
				13: 1800mm with Ferrite Core
				* 20AWG/UL1571 or Equivalent
				* 16AWG/UL1571 for Vo: 5V or Equivalent
				* 18AWG/UL1571 for Vo: 9V or Equivalent

MODEL	OUTPUT VOLTAGE	OUTPUT CURRENT	RIPPLE & NOISE NOTE 1	VOLTAGE ACCURACY NOTE 2	LINE REGULATION NOTE 3	LOAD REGULATION NOTE 4	AVG.ERAGE EFF. min.
TRE25RD050	5V	4A	50mVp-p	±2%	±1%	±6%	83.7%
TRE25RD090	9V	2.5A	1%	±2%	±1%	±5%	86.52%
TRE25RD120	12V	2.1A	1%	±2%	±1%	±5%	87.0%
TRE25RD150	15V	1.67A	1%	±2%	±1%	±3%	87.0%
TRE25RD180	18V	1.4A	1%	±2%	±1%	±2%	87.0%
TRE25RD240	24V	1.05A	1%	±2%	±1%	±2%	87.0%

Specifications

INPUT SPECIFICATIONS:

Voltage	90~264Vac 120~370Vdc
Frequency	47 to 63Hz
Input Current	0.7A max.
Inrush Current	60A max. @240Vac
Conducted EMI	CISPR/FCC Class B
Leakage Current	0.25mA max.


OUTPUT SPECIFICATIONS:

Holdup Time	10ms typ. @115Vac
Short Circuit Protection	Continuous(Auto Recovery)
Over Voltage Protection	IC Component to Clamp
Temperature Coefficient	±0.05%/°C

GENERAL SPECIFICATIONS:

Isolation	Input to output = 3,000VAC
Operating Temperature	-20~60°C (see derating curve)
Storage Temperature	-20~85°C
Humidity	93% RH max. Non condensing
Cooling	Natural Convection
Switching Frequency	65KHz typ.
MTBF	MIL-HDBK-217F, GB, 25°C/115VAC 300K hrs min.
Altitude	3000m
Life time	Ambient 40degC 75% Load >3years
Dimensions	2.835x2.244x1.299Inches (72.00x57.0x33.00mm)
Weight	140g(0.31 Pounds)

TRE25RD Series Derating Curve



SAFETY AND EMC:


Emission and Immunity	EN55022 Class B, FCC Part 15 Class B EN61000-6-3, EN61000-3-2, EN61000-3-3 EN55024, EN61204-3, EN61000-6-1
Safety	Class II, IEC62368-1/60950-1, UL62368-1/60950-1 EN62368-1/60950-1

NOTE:

1. Add a 0.1uF ceramic capacitor and a 10uF E.L. capacitor to output for ripple & noise measuring @20MHz BW.
2. Voltage setpoint at 60% full load.
3. Line regulation measured from 100Vac to 240Vac, full load.
4. Load regulation measured from 60% to 100% full load and from 60% to 20% load (60% +/- 40% full load).

Mechanical Specification

All Dimensions are in inches(mm)
Tolerance:Inches:X.XXX±0.02
Millimeters:X.XX±0.5
UNIT: inches[mm]



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Cincon:

[TRE25RD240-49G01-Level-VI](#) [TRE25RD150-01G03-Level-VI](#) [TRE25RD050-39G01-Level-VI](#) [TRE25RD150-02G03-Level-VI](#) [TRE25RD240-11G12-Level-VI](#) [TRE25RD120-35G01-Level-VI](#) [TRE25RD240-01G11-Level-VI](#) [TRE25RD180-11G02-Level-VI](#) [TRE25RD150-02G11-Level-VI](#) [TRE25RD240-12G11-Level-VI](#) [TRE25RD240-40G03-Level-VI](#) [TRE25RD240-39G12-Level-VI](#) [TRE25RD240-11G11-Level-VI](#) [TRE25RD120-48G12-Level-VI](#) [TRE25RD050-39G02-Level-VI](#) [TRE25RD120-12G03-Level-VI](#) [TRE25RD120-49G12-Level-VI](#) [TRE25RD050-49G11-Level-VI](#) [TRE25RD240-02G02-Level-VI](#) [TRE25RD240-35G01-Level-VI](#) [TRE25RD050-35G03-Level-VI](#) [TRE25RD120-35G13-Level-VI](#) [TRE25RD120-39G13-Level-VI](#) [TRE25RD050-40G13-Level-VI](#) [TRE25RD120-02G11-Level-VI](#) [TRE25RD050-40G12-Level-VI](#) [TRE25RD240-40G11-Level-VI](#) [TRE25RD120-36G11-Level-VI](#) [TRE25RD150-11G12-Level-VI](#) [TRE25RD240-49G02-Level-VI](#) [TRE25RD150-01G11-Level-VI](#) [TRE25RD150-02G01-Level-VI](#) [TRE25RD050-39G12-Level-VI](#) [TRE25RD240-12G12-Level-VI](#) [TRE25RD050-39G13-Level-VI](#) [TRE25RD050-40G02-Level-VI](#) [TRE25RD240-39G13-Level-VI](#) [TRE25RD120-40G13-Level-VI](#) [TRE25RD050-35G01-Level-VI](#) [TRE25RD180-11G03-Level-VI](#) [TRE25RD240-11G03-Level-VI](#) [TRE25RD180-12G11-Level-VI](#) [TRE25RD120-39G12-Level-VI](#) [TRE25RD050-12G03-Level-VI](#) [TRE25RD240-12G01-Level-VI](#) [TRE25RD150-12G12-Level-VI](#) [TRE25RD120-36G01-Level-VI](#) [TRE25RD240-39G11-Level-VI](#) [TRE25RD050-02G02-Level-VI](#) [TRE25RD150-01G12-Level-VI](#) [TRE25RD050-49G12-Level-VI](#) [TRE25RD150-12G11-Level-VI](#) [TRE25RD050-12G11-Level-VI](#) [TRE25RD180-01G01-Level-VI](#) [TRE25RD120-11G11-Level-VI](#) [TRE25RD050-39G11-Level-VI](#) [TRE25RD240-49G11-Level-VI](#) [TRE25RD240-12G02-Level-VI](#) [TRE25RD050-40G03-Level-VI](#) [TRE25RD240-48G13-Level-VI](#) [TRE25RD050-11G01-Level-VI](#) [TRE25RD120-11G01-Level-VI](#) [TRE25RD150-11G02-Level-VI](#) [TRE25RD120-12G01-Level-VI](#) [TRE25RD120-02G02-Level-VI](#) [TRE25RD180-12G01-Level-VI](#) [TRE25RD180-02G01-Level-VI](#) [TRE25RD120-40G01-Level-VI](#) [TRE25RD050-11G02-Level-VI](#) [TRE25RD120-11G12-Level-VI](#) [TRE25RD120-39G03-Level-VI](#) [TRE25RD240-12G13-Level-VI](#) [TRE25RD050-40G01-Level-VI](#) [TRE25RD120-01G12-Level-VI](#) [TRE25RD050-02G01-Level-VI](#) [TRE25RD050-02G11-Level-VI](#) [TRE25RD240-48G03-Level-VI](#) [TRE25RD050-36G03-Level-VI](#) [TRE25RD150-12G03-Level-VI](#) [TRE25RD240-01G02-Level-VI](#) [TRE25RD120-49G03-Level-VI](#) [TRE25RD050-36G11-Level-VI](#) [TRE25RD120-01G01-Level-VI](#) [TRE25RD240-36G13-Level-VI](#) [TRE25RD120-40G03-Level-VI](#) [TRE25RD180-01G03-Level-VI](#) [TRE25RD120-40G02-Level-VI](#) [TRE25RD150-02G02-Level-VI](#) [TRE25RD240-39G03-Level-VI](#) [TRE25RD150-12G13-Level-VI](#) [TRE25RD240-49G12-Level-VI](#) [TRE25RD050-49G03-Level-VI](#) [TRE25RD180-11G11-Level-VI](#) [TRE25RD050-11G12-Level-VI](#) [TRE25RD240-02G03-Level-VI](#) [TRE25RD240-01G13-Level-VI](#) [TRE25RD120-39G11-Level-VI](#) [TRE25RD120-39G01-Level-VI](#) [TRE25RD120-49G13-Level-VI](#) [TRE25RD120-48G03-Level-VI](#)