



- Universal Input Range 90~264Vac
- High Efficiency up to 89%
- Class II
- No Load Power Consumption < 75mW
- Approved IEC/EN/UL 62368-1
- Meets EN55032 Class B and CISPR/FCC Class B
- Operating Altitude 5000m
- Over Voltage Protection
- Continuous Short Circuit Protection
- Meets CoC Tier 2 & DoE Level VI



Note:

1. Voltage accuracy is set at 60% full load.
2. Add a 0.1uF ceramic capacitor and a 10uF E.L. capacitor to output for ripple & noise measuring @20MHz BW.
3. Line regulation is measured from 100V_{ac} to 240V_{ac} with 100% full load.
4. Load regulation is measured from 60% to 100% full load and from 60% to 20% full load (60%±40% full load).
5. Typical efficiency at 230 V_{ac} and 75% full load at 25°C.

PART NUMBER

Part Number Example:

TRE36A120-01G03, 12V_{dc} Output, DC Jack Type, Cable Length 1800mm



TRE36 Series

TECHNICAL SPECIFICATIONS

(All specifications are typical at nominal input, full load at 25°C unless otherwise noted.)

ABSOLUTE MAXIMUM RATINGS

PARAMETER	NOTES and CONDITIONS	Device	Min.	Typ.	Max.	Units
Input Voltage	See Derating Curve	All	90		264	V _{ac}
			120		370	V _{dc}
Operating Temperature	See Derating Curve	All	-30		60	°C
Storage Temperature		All	-30		85	°C
Operating Altitude		All			5000	m

INPUT CHARACTERISTICS

PARAMETER	NOTES and CONDITIONS	Device	Min.	Typ.	Max.	Units
Operating Voltage Range		All	100		240	V _{ac}
Input Frequency Range		All	47		63	Hz
Maximum Input Current	100% Full load, V _{in} =100V _{ac}	All			0.9	A
Leakage Current		All			250	uA
Inrush Current	V _{in} =240V _{ac} , Cold start at 25°C	All			100	A

OUTPUT CHARACTERISTICS

PARAMETER	NOTES and CONDITIONS	Device	Min.	Typ.	Max.	Units
Output Voltage Set Point	V _{in} =115V _{ac} and 230V _{ac} , I _o =60% Full load T _c =25°C	TRE36A050	4.9	5	5.1	V _{dc}
		TRE36A090	8.82	9	9.18	
		TRE36A120	11.76	12	12.24	
		TRE36A135	13.23	13.5	13.77	
		TRE36A150	14.7	15	15.3	
		TRE36A180	17.64	18	18.36	
		TRE36A240	23.52	24	24.48	
		TRE36A360	35.28	36	36.72	
		TRE36A480	47.04	48	48.96	
Operating Output Current Range	V _{in} =115V _{ac} and 230V _{ac} , T _c =25°C	TRE36A050			5	A
		TRE36A090			3.3	
		TRE36A120			2.5	
		TRE36A135			2.4	
		TRE36A150			2.4	
		TRE36A180			2	
		TRE36A240			1.5	
		TRE36A360			1	
		TRE36A480			0.75	
Holdup Time	V _{in} =115V _{ac}	All		10		ms
Output Voltage Regulation						
Load Regulation	60%±40% Full load change	TRE36A050			±6	%
		TRE36A090			±4	
		TRE36A120			±2	
		TRE36A135			±2	
		TRE36A150			±2	
		TRE36A180			±2	
		TRE36A240			±2	
		TRE36A360			±2	
		TRE36A480			±2	
Line Regulation	V _{in} =100V _{ac} to 240V _{ac}	All			±1.0	%



TRE36 Series

PARAMETER	NOTES and CONDITIONS	Device	Min.	Typ.	Max.	Units
Over Voltage Protection	IC component to clamp (auto recovery)	TRE36A050 TRE36A090 TRE36A120 TRE36A135 TRE36A150 TRE36A180 TRE36A240 TRE36A360 TRE36A480			7.44 13.6 15.9 16.5 21.5 24.8 31.5 45.2 59.6	V _{dc}
Over Current Protection	Auto recovery	All	110		160	%
Short Circuit Protection	Auto recovery	All				
Output Ripple and Noise	1. Add a 0.1uF ceramic capacitor and a 10uF aluminum electrolytic capacitor to output 2. Oscilloscope is 20MHz band width 3. Ambient temperature=25°C	TRE36A050 TRE36A090 TRE36A120 TRE36A135 TRE36A150 TRE36A180 TRE36A240 TRE36A360 TRE36A480			100 120 120 130 150 180 240 360 480	mV
Load Capacitance	1. V _{in} =115V _{ac} and 230V _{ac} 2. Output is max. load 3. Ambient temperature=25°C	TRE36A050 TRE36A090 TRE36A120 TRE36A135 TRE36A150 TRE36A180 TRE36A240 TRE36A360 TRE36A480			5000 3300 2500 2400 2400 2000 1500 1000 750	uF
Efficiency	1. V _{in} =230V _{ac} 2. Output is 75% full load 3. Ambient temperature=25°C	TRE36A050 TRE36A090 TRE36A120 TRE36A135 TRE36A150 TRE36A180 TRE36A240 TRE36A360 TRE36A480		83 87 88 89 88 88 88 89 89		%

ISOLATION CHARACTERISTICS

PARAMETER	NOTES and CONDITIONS	Device	Min.	Typ.	Max.	Units
Input to Output	1 minute	All			4000	V _{ac}
Isolation Resistance	Input to output	All	100			MΩ

FEATURE CHARACTERISTICS

PARAMETER	NOTES and CONDITIONS	Device	Min.	Typ.	Max.	Units
Switching Frequency	P _{out} =max. rated power	All		65		kHz



TRE36 Series

GENERAL SPECIFICATIONS


PARAMETER	NOTES and CONDITIONS	Device	Min.	Typ.	Max.	Units
MTBF	$I_o=100\%$; $T_a=25^{\circ}\text{C}$ per MIL-HDBK-217F	All	400			k hours
Humidity	Non-condensing	All			93	% RH
Shock	Meet MIL-STD-810F Table 516.5, Table 516.5-I 10ms, each axis 3 times($\pm X$ 、 $\pm Y$ 、 $\pm Z$ axis)	All		75		g
Vibration	Meet MIL-STD-810F Table 514.5C-VIII, 15~2000Hz, X、Y、Z axis, 1 hour (each axis),. Total 3 hrs.	All		4		g
Weight		All		150		g
Dimensions		All	3.937x1.771x0.886 inches (100.00x45.00x22.50 mm)			
Safety	Class II, IEC/EN/UL 62368-1					Ed.3.0
EMC Emission	EN 55032:2015+A1:2020, EN 55032:2015+A11:2020, CISPR PUB. 22, FCC Part 15 Subpart B, EN 61000-6-3:2021, EN 61000-6-4:2019, EN 61000-3-2:2019+A1:2021, EN 61000-3-3:2013+A2:2021					Class B
Conducted Disturbance	EN 55032:2015+A1:2020, EN 55032:2015+A11:2020, CISPR PUB. 22, FCC Part 15 Subpart B, EN 61000-6-3:2021, EN 61000-6-4:2019					Class B
Radiated Disturbance	EN 55032:2015+A1:2020, EN 55032:2015+A11:2020, CISPR PUB. 22, FCC Part 15 Subpart B, EN 61000-6-3:2021, EN 61000-6-4:2019					Class B
Harmonic Current Emissions	EN 61000-3-2:2019+A1:2021					
Voltage Fluctuations & Flicker	EN 61000-3-3:2013+A2:2021					
EMC Immunity	EN 55035:2017+A11:2020, EN 61000-6-1:2019, EN 61000-6-2:2019、IEC 61000-4-2, 3, 4, 5, 6, 11					
Electrostatic Discharge (ESD)	IEC 61000-4-2:2008、Air Discharge: $\pm 8\text{kV}$, Contact Discharge: $\pm 4\text{kV}$					Criteria A
Radio-Frequency, Continuous Radiated Disturbance	IEC 61000-4-3:2020					Criteria A
Electrical Fast Transient (EFT)	IEC 61000-4-4:2012, $\pm 1\text{kV}$, $\pm 2\text{kV}$					Criteria A
Surge	IEC 61000-4-5:2014+A1:2017, L-N: $\pm 0.5\text{kV}$, $\pm 1\text{kV}$					Criteria A
Conducted Disturbances, Induced by RF Fields	IEC 61000-4-6:2013+COR1:2015					Criteria A
Voltage Dips	IEC 61000-4-11:2020, Dip: 30% Reduction, Dip >95% Reduction					Criteria A
Voltage Interruptions	IEC 61000-4-11:2020, >95% Reduction					Criteria B
Application Note Link			TRE36 Series App Notes			









TRE36 Series

CHARACTERISTIC CURVE

Power Derating Curve




Performance Data






TRE36 Series


TRE36A240 (Eff Vs Io)



TRE36A360 (Eff Vs Io)






TRE36A480 (Eff Vs Io)



MECHANICAL SPECIFICATION







All Dimensions are in inches[mm]
Tolerance: Inches: X.XXX±0.02
Millimeters: X.XX±0.5





TRE36 Series

STANDARD OUTPUT PLUG

DC Plug Type	Cable Number-XXXXX	A	B	C	Cable Type	Cable Length	Cable AWG
		OD (mm)	ID (mm)	L (mm)			
 Straight/Inner+Outer- + ● -	11G02	Φ5.5	Φ2.1	12	UL1571	1220mm without Core	16AWG for Vo: 5V
	12G02	Φ5.5	Φ2.5	12			
	23G02	Φ5.5	Φ2.1	9.5			
	26G02	Φ5.5	Φ2.5	9.5			
 Right Angle/Inner+Outer- + ● -	01G02	Φ5.5	Φ2.1	12			
	02G02	Φ5.5	Φ2.5	12			
	21G02	Φ5.5	Φ2.5	9.5			
	24G02	Φ5.5	Φ2.1	9.5			
 Straight/Inner+Outer- + ● -	11G03	Φ5.5	Φ2.1	12	UL1571	1800mm without Core	18AWG for Vo: 9V, 12V, 13.5V 20AWG for Vo: 15V, 18V, 24V
	12G03	Φ5.5	Φ2.5	12			
	23G03	Φ5.5	Φ2.1	9.5			
	26G03	Φ5.5	Φ2.5	9.5			
 Right Angle/Inner+Outer- + ● -	01G03	Φ5.5	Φ2.1	12			
	02G03	Φ5.5	Φ2.5	12			
	21G03	Φ5.5	Φ2.5	9.5			
	24G03	Φ5.5	Φ2.1	9.5			
 Straight/Inner+Outer- + ● -	11E03	Φ5.5	Φ2.1	12	UL1185	1800mm without Core	20AWG for Vo: 36V, 48V
	12E03	Φ5.5	Φ2.5	12			
	23E03	Φ5.5	Φ2.1	9.5			
	26E03	Φ5.5	Φ2.5	9.5			
 Right Angle/Inner+Outer- + ● -	01E03	Φ5.5	Φ2.1	12			
	02E03	Φ5.5	Φ2.5	12			
	21E03	Φ5.5	Φ2.5	9.5			
	24E03	Φ5.5	Φ2.1	9.5			

※Other DC Plug Type please refer to the link: <https://www.cincon.com/productdownload/TRE36-cable--DC-Plug.pdf>

CINCON Electronics Co. Ltd.
 Add: 14F, No. 306, Sec.4, Hsin Yi Rd., Taipei, Taiwan
 Tel: 886-2-27086210
 Fax: 886-2-27029852
 E-mail: sales@cincon.com.tw
 Web: www.cincon.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Cincon:](#)

[TRE36A120-12G03 LEVEL VI](#) [TRE36A240-01G03 LEVEL VI](#) [TRE36A150-12G03 VI](#) [TRE36A150-01G03 VI](#)
[TRE36A480-12E03 VI](#) [TRE36A360-12E03 VI](#) [TRE36A135-12G03 VI](#) [TRE36A360-01E03 LEVEL VI](#) [TRE36A240-](#)
[02E03 VI](#) [TRE36A480-01G03 VI](#)